

ELR H5-IS-SC- 24DC/500AC-9-P - Hybrid motor starter



2908697

<https://www.phoenixcontact.com/us/products/2908697>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Hybrid motor starter as an alternative to a conventional reversing contactor. Reverses 3~ AC motors up to 9 A, provides motor protection and emergency stop up to SIL 3 / PL e. Group shut-down, supply, and relay extension possible via DIN rail connector.

Product description

The modular 3-phase hybrid motor starter with reversing function and current monitoring provides the following functions: - Forward running - Reverse running - Motor overload protection - Emergency stop to performance level PLe (TÜV certified) Additional advantages are provided by using the DIN rail connector adapter (Item No. 2203861): - Emergency stop of the enable signal is also possible via the DIN rail connector, e.g. via a safety relay (PSR DC38...) - Power can also be supplied via the DIN rail connector by a system power supply (e. g., QUINT4-SYS...) or via the PCB connector IMC 1,5/ 5-ST-3,81, Item No. 1857919 - Optional relay module (e. g., EM-2RSC/21AU-R/L-P, Item No. 2908701) provides additional status information Thanks to the internal interlocking circuit and load wiring, wiring expense is reduced to a minimum.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2908697 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C470 |
| Product key | DK7414 |
| GTIN | 4055626323114 |
| Weight per piece (including packing) | 329.7 g |
| Weight per piece (excluding packing) | 306 g |
| Customs tariff number | 85371098 |
| Country of origin | DE |

ELR H5-IS-SC- 24DC/500AC-9-P - Hybrid motor starter



2908697

<https://www.phoenixcontact.com/us/products/2908697>

Technical data

Product properties

| | |
|----------------|-----------------------|
| Product type | Hybrid motor starters |
| Product family | CONTACTRON |
| Operating mode | 100% operating factor |

Electrical properties

| | |
|---------------------------|-------------------------|
| Number of phases | 3 |
| Motor starter type | Reversing starter |
| Switching frequency | ≤ 2 Hz (Load-dependent) |
| Switching frequency | ≤ 2 Hz (Load-dependent) |
| Maximum power dissipation | 7 W |
| Minimum power dissipation | 0.88 W |
| Coordination type | 1 |

Supply

| | |
|--|---|
| Rated control circuit supply voltage U_S | 24 V DC |
| Control supply voltage range | 19.2 V DC ... 30 V DC |
| Rated control supply current I_S | 60 mA |
| Protective circuit | Surge protection Reverse polarity protection; Parallel polarity protection diode |

Insulation characteristics

| | |
|--|--|
| Rated insulation voltage | 550 V |
| Rated surge voltage | 6 kV |
| Overvoltage category | III |
| Degree of pollution | 2 |
| Insulation characteristics between the control input and control supply voltage, and auxiliary circuit to the main circuit | Safe isolation (IEC 60947-1) |
| Isolation characteristics between the control input and control supply voltage to auxiliary circuit | Safe isolation (IEC 60947-1) in the auxiliary circuit ≤ 300 V AC |

Emergency tripping

| | |
|-------------------|---------|
| Operate threshold | > 60 A |
| Response time | < 0.5 s |

Input data

Control

| | |
|-------------------------------|---|
| Input name | Control input: right/left and enable input |
| Note | The enable input is compatible with signals with blanking (semiconductor output signals with test pulse with max. 3 ms duration), unblanking pulses of max. 4 ms are tolerated without adversely affecting the safety function. |
| Rated actuating voltage U_C | 24 V DC |

ELR H5-IS-SC- 24DC/500AC-9-P - Hybrid motor starter



2908697

<https://www.phoenixcontact.com/us/products/2908697>

| | |
|-------------------------------|-------------------------------|
| Triggering voltage range | 19.2 V DC ... 30 V DC |
| Rated actuating current I_C | 7 mA |
| Switching threshold | 9.6 V ("0" signal) |
| | 19.2 V ("1" signal) |
| Switching level | < 5 V DC (For EMERGENCY STOP) |
| Typical turn-off time | < 30 ms |
| Protective circuit | Reverse polarity protection |

Output data

AC output

| | |
|---|-------------------------|
| Rated operating voltage U_e | 500 V AC |
| Operating voltage range | 42 V AC ... 550 V AC |
| Rated operating current I_e | 9 A (AC-51) |
| | 7 A (AC-53a) |
| Mains frequency | 50/60 Hz |
| Load current range | 1.5 A ... 9 A |
| Trigger characteristic in acc. with IEC 60947-4-2 | Class 10 (≤ 3 A) |
| | Class 10A (> 3 A) |
| Cooling time | 20 min (for auto reset) |
| Leakage current | 0 mA |

Acknowledge output

| | |
|---|--|
| Note | Confirmation: floating change-over contact, signal contact |
| Contact switching type | 1 changeover contact |
| Switching capacity in accordance with IEC 60947-5-1 | 2 A (24 V (DC13)) |

Connection data

Control circuits

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 14 |
| Tightening torque | 0.5 Nm ... 0.6 Nm |
| | 5 lb _f -in. ... 7 lb _f -in. |

Load circuit

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 14 |

ELR H5-IS-SC- 24DC/500AC-9-P - Hybrid motor starter



2908697

<https://www.phoenixcontact.com/us/products/2908697>

| | |
|-------------------|---|
| Tightening torque | 0.5 Nm ... 0.6 Nm |
| | 5 lb _F -in. ... 7 lb _F -in. |

Signaling

| | |
|---------------------------|--------------|
| Status display | LED (yellow) |
| Operating voltage display | Green LED |
| Error indication | Red LED |

Dimensions

| | |
|--------|---------|
| Width | 22.5 mm |
| Height | 107 mm |
| Depth | 114 mm |

Material specifications

| | |
|--|--------------|
| Flammability rating according to UL 94 (Housing) | V0 (Housing) |
|--|--------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|-------------------------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -25 °C ... 70 °C (observe derating) |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Altitude | ≤ 2000 m |

Approvals

UL approval

| | |
|-------------|--------------|
| Certificate | NLDX.E228652 |
| | NRNT.E172140 |

Safety Integrity Level (SIL, IEC 61508)

| | |
|----------------|---------------|
| Identification | ≤ 3 |
| Note | Safe shutdown |

Safety Integrity Level (SIL, IEC 61508)

| | |
|----------------|------------------|
| Identification | 2 |
| Note | Motor protection |

Performance Level (ISO 13849)

| | |
|----------------|---------------|
| Identification | ≤ e |
| Note | Safe shutdown |

Category (ISO 13849)

| | |
|----------------|---------------|
| Identification | ≤ 3 |
| Note | Safe shutdown |

UL data

| | |
|------|---|
| SCCR | 100 kA (480 V AC (fuse: 30 A class CC/30 A class J (high fault))) |
|------|---|

ELR H5-IS-SC- 24DC/500AC-9-P - Hybrid motor starter



2908697

<https://www.phoenixcontact.com/us/products/2908697>

| | |
|---------------------------------|--|
| | 5 kA (480 V AC (fuse: 20 A RK5 (standard fault))) |
| FLA | 7.6 A (480 V AC) |
| Group installation | 20 A (class RK5, SCCR 5kA (480 V AC), #24 - 14 AWG max. solid and stranded) 30 A (class CC or J, SCCR 100kA (480 V AC), #24 - 14 AWG max, solid and stranded) |
| Category code | NLDX / NRNT |
| Horsepower ratings | 2 hp (208 V AC) 2 hp (230 V AC) 2 hp (240 V AC) 5 hp (480 V AC) |
| Ambient temperature (operation) | -25 °C ... 55 °C |

Standards and regulations

Standards/regulations

| | |
|-----------------------|--------------|
| Standards/regulations | EN 60947-1 |
| | EN 60947-4-2 |
| | EN ISO 13849 |
| | IEC 62061 |
| | IEC 61508 |

Mounting

| | |
|-------------------|--|
| Mounting type | DIN rail mounting |
| Assembly note | alignable, for spacing see derating |
| Mounting position | vertical (horizontal DIN rail, motor output below) |

ELR H5-IS-SC- 24DC/500AC-9-P - Hybrid motor starter




2908697

<https://www.phoenixcontact.com/us/products/2908697>

Drawings

Block diagram



ELR H5-IS-SC- 24DC/500AC-9-P - Hybrid motor starter



2908697

<https://www.phoenixcontact.com/us/products/2908697>

Classifications

ECLASS

ECLASS-13.0

27370905

ETIM

ETIM 9.0

EC001037

UNSPSC

UNSPSC 21.0

25173900

ELR H5-IS-SC- 24DC/500AC-9-P - Hybrid motor starter



2908697

<https://www.phoenixcontact.com/us/products/2908697>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | bc9aa0d6-8058-458a-b967-da7a59baee85 |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com