

# UMK-16RM/KSR-G24/21/E/TVFKC - Relay module



2908734

<https://www.phoenixcontact.com/us/products/2908734>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE output extension module, with 16 miniature relays, 1 changeover contact each, plugged, for 24 V DC (including relays)

## Commercial data

Item number	2908734
Packing unit	1 pc
Minimum order quantity	20 pc
Product key	DK2A9A
GTIN	4055626324500
Weight per piece (including packing)	650 g
Country of origin	DE

## Technical data

### Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

### Product properties

Product type	Relay Module
Mechanical service life	3x 10 <sup>7</sup> cycles

#### Insulation characteristics: Air clearances and creepage distances, input/output

Insulation	Reinforced insulation
Overvoltage category	III
Pollution degree	2

#### Insulation characteristics: Air and creepage distances, output/output

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

### Electrical properties

#### Air clearances and creepage distances, input/output

Rated insulation voltage	260 V
Rated surge voltage	6 kV (1.2/50 μs)

#### Air and creepage distances, output/output

Rated insulation voltage	260 V
Rated surge voltage	4 kV (1.2/50 μs)

### Input data

Nominal input voltage $U_N$	24 V DC
Input voltage range in reference to $U_N$	0.9 ... 1.1
Input voltage range	21.6 V DC ... 26.4 V DC
Typical input current at $U_N$	18 mA
Typical response time	8 ms
Typical release time	12 ms
Protective circuit	Damping diode, polarity protection; Damping diode, polarity protection diode
Operating voltage display	Green LED
Status display/channel	Yellow LED

### Output data

#### Switching

# UMK-16RM/KSR-G24/21/E/TVFKC - Relay module



2908734

<https://www.phoenixcontact.com/us/products/2908734>

Contact switching type	Single contact, 1 changeover contact
Contact material	AgNi (90/10) gold-plated
Maximum switching voltage	250 V AC/DC
Minimum switching voltage	12 V AC/DC (10 mA)
Limiting continuous current	5 A
Min. switching current	10 mA (12 V AC/DC)
Interrupting rating (ohmic load) max.	120 W (24 V DC)
	58 W (48 V DC)
	48 W (60 V DC)
	50 W (110 V DC)
	80 W (220 V DC)
	1250 VA (250 V AC)

## Connection data

### Input

Connection method	Flat-ribbon cable connector in acc. with IEC 60603-13
Number of connections	1
Number of positions	20

### Output

Connection method	Push-in spring connection
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 16

## Dimensions

Width	259 mm
Height	77 mm
Depth	59 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 50 °C
Altitude	≤ 2000 m

## Standards and regulations

### Air clearances and creepage distances, input/output

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

### Air and creepage distances, output/output

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

# UMK-16RM/KSR-G24/21/E/TVFKC - Relay module



2908734

<https://www.phoenixcontact.com/us/products/2908734>

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

# UMK-16RM/KSR-G24/21/E/TVFKC - Relay module



2908734

<https://www.phoenixcontact.com/us/products/2908734>

## Classifications

### UNSPSC

UNSPSC 21.0	39121432
-------------	----------

2908734

<https://www.phoenixcontact.com/us/products/2908734>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)