

# VIP/MSTB/D50M/BASE/16CH/CX/EX - Base module



2908788

<https://www.phoenixcontact.com/us/products/2908788>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



16-channel VIP I/O marshalling base element for universal use. Plug-in field and supply terminals available as accessories. With Push-in connection technology. Compatible with the Tricon CX DCS series (D-SUB 50).

## Your advantages

- Integrated carrier for IOA insertion and retention
- Screw and push-in (PT) plug kits available as separate part numbers
- Terminals for redundant power supply connections with fusing
- Each channel has four field-side connections (A, B, C, D)
- IOA modules sold separately

## Commercial data

Item number	2908788
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	C480
Product key	DK115A
GTIN	4055626477992
Weight per piece (including packing)	755.5 g
Weight per piece (excluding packing)	730.7 g
Customs tariff number	85366990
Country of origin	CN

2908788

<https://www.phoenixcontact.com/us/products/2908788>

## Technical data

### Product properties

Product type	Module carrier
Product family	VIP I/O-Marshalling
No. of channels	16

### Insulation characteristics

Overvoltage category	II, III
Pollution degree	2

### Electrical properties

Max. operating voltage $U_{max}$	30 V DC (field terminals)
	230 V AC (field terminals)
	30 V DC (A and B terminals)
	30 V DC (D-SUB 50 connector)
Max. permissible current	3 A (A and B terminals)
Max. permissible total current	10 A (per module)
Max. current carrying capacity per branch	3 A (field signal)
	0.5 A (control contacts)

### Connection data

#### Field level

Connection in acc. with standard	IEC / EN
Connection method	pluggable
Number of connections	4
Number of positions	16

#### Controller level

Connection method	D-SUB pin strip
Number of connections	1
Number of positions	50

### Ex data

#### Safety data

Input voltage $U_i$	30 V (per channel)
Input current $I_i$	0.5 A (per channel)
Inductance $L_i$	0 mH
Capacitance $C_i$	0 $\mu$ F
Safety-related maximum voltage $U_m$	253 V AC/DC (A and B terminals and D-SUB 50)

### Signaling

Status display	no
Status display present	no

2908788

<https://www.phoenixcontact.com/us/products/2908788>

## Dimensions

### Item dimensions

Width	250 mm
Height	142.3 mm
Depth	78 mm

## Material specifications

Color	gray (RAL 7042)
-------	-----------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Altitude	< 2000 m
Permissible humidity (operation)	0 % ... 95 % (non-condensing)

## Approvals

### ATEX

Identification	Ⓔ II 3G Ex ec IIC T4 Gc
Certificate	JSHP 24ATEX0051X

### IECEX

Identification	Ex ec IIC T4 Gc
Certificate	IECEX JSH 24.0014X

### UKEX

Identification	Ⓔ II 3G Ex ec IIC T4 Gc
Certificate	PxCIF23UKEX2908788X

### CCC/China Ex

Identification	Ex ec IIC T4 Gc
Certificate	2025122308124416

### CSA, USA/Canada

Identification	Class I, Div. 2 Groups A, B, C, D T4
	Class I, Zone 2, AEx nA IIC T4 Gc
	Ex nA IIC T4 Gc

## Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

## Mounting

# VIP/MSTB/D50M/BASE/16CH/CX/EX - Base module



2908788

<https://www.phoenixcontact.com/us/products/2908788>


Mounting type	DIN rail mounting
Mounting position	As desired on 35 mm DIN rail in acc. with EN 60715

2908788

<https://www.phoenixcontact.com/us/products/2908788>

Drawings

Dimensional drawing




Termination board including IOA and accessories

2908788

<https://www.phoenixcontact.com/us/products/2908788>

## Circuit diagram



2908788

<https://www.phoenixcontact.com/us/products/2908788>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2908788>



**IECEX**

Approval ID: IECEx JSH 24.0014X



**CSA**

Approval ID: 70167152



**CSAus**

Approval ID: 70167152



**CCC**

Approval ID: 2025122308124416

**ATEX**

Approval ID: JSHP 24ATEX 0051X

2908788

<https://www.phoenixcontact.com/us/products/2908788>

## Classifications

### ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

### ETIM

ETIM 10.0	EC002780
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

2908788

<https://www.phoenixcontact.com/us/products/2908788>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	9094823a-fcc5-4004-b761-5a5bb4b29c28

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
 586 Fulling Mill Road  
 Middletown, PA 17057, United States  
 (+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)