


# MINI MCR-EX-SD-21-48-LP-PT - Solenoid driver



2908811

<https://www.phoenixcontact.com/us/products/2908811>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ex i-Solenoid driver for controlling Ex i solenoid valves in the Ex area. number of channels: 1, open-circuit voltage: 21 V DC, current limitation: 48 mA, Standard configuration, Loop-powered, Safety Integrity Level (SIL, IEC 61508): 3, Push-in connection

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2908811       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | C430          |
| Product key                          | DK1224        |
| GTIN                                 | 4055626357584 |
| Weight per piece (including packing) | 118.5 g       |
| Weight per piece (excluding packing) | 118.5 g       |
| Customs tariff number                | 85437090      |
| Country of origin                    | DE            |

## Technical data

### Product properties

|                 |                 |
|-----------------|-----------------|
| Product type    | Solenoid driver |
| Product family  | MINI Analog Pro |
| No. of channels | 1               |

### Electrical properties

|   |     |
|---|-----|
| Electrical isolation between input and output | yes |
|---|-----|

#### Electrical isolation

|                      |                     |
|----------------------|---------------------|
| Overvoltage category | II ( $\leq 5000$ m) |
| Pollution degree     | 2 ( $\leq 5000$ m)  |

#### Electrical isolation Input/output IEC/EN 61010-1

|                          |                              |
|--------------------------|------------------------------|
| Standards/regulations    | IEC/EN 61010-1               |
| Rated insulation voltage | 300 V <sub>rms</sub>         |
| Test voltage             | 2.5 kV AC (50 Hz, 60 s)      |
| Insulation               | Double/reinforced insulation |

#### Electrical isolation Input/output IEC/EN 60079-11

|                          |                      |
|--------------------------|----------------------|
| Standards/regulations    | IEC/EN 60079-11      |
| Rated insulation voltage | 265 V <sub>rms</sub> |

#### Electrical isolation Input/output IEC/EN 60079-7

|                          |                      |
|--------------------------|----------------------|
| Standards/regulations    | IEC/EN 60079-7       |
| Rated insulation voltage | 251 V <sub>rms</sub> |

#### Supply

|                      |  |
|----------------------|--|
| Supply voltage range | loop-powered, no external supply necessary |
| Power consumption    | < 1.7 W                                    |

### Input data

#### Signal: Voltage

|                      |  |
|----------------------|--|
| Number of inputs     | 1  |
| Voltage input signal | 19.2 V DC ... 30 V DC (24 V DC, -20 % ... +25 %) |

### Output data

#### Signal: Voltage

|                      |   |
|----------------------|---|
| Number of outputs    | 1   |
| Output voltage       | $\geq 12.2$ V DC (48 mA)                                |
| Output resistor      | $\geq 181 \Omega$ (Internal resistance R <sub>i</sub> ) |
| Current limitation   | > 48 mA   |
| Response time        | < 50 ms   |
| Open-circuit voltage | > 21 V DC   |

# MINI MCR-EX-SD-21-48-LP-PT - Solenoid driver



2908811

<https://www.phoenixcontact.com/us/products/2908811>

|                     |     |
|---------------------|-----|
| Short-circuit-proof | yes |
|---------------------|-----|

## Connection data

|                                  |  |
|----------------------------------|--|
| Connection method                | Push-in connection   |
| Stripping length                 | 10 mm  |
| Conductor cross-section rigid    | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (with ferrule)<br>0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (without ferrule) |
| Conductor cross-section flexible | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>   |
| Conductor cross-section AWG      | 24 ... 12 (flexible)   |

## Ex data

|                       |          |
|-----------------------|----------|
| Ex installation (EPL) | Gc       |
|                       | Div. 2   |
| Ex i circuits (EPL)   | [Ga]     |
|                       | [Da]     |
|                       | [Ma]     |
|                       | [Div. 1] |

## Safety data

|  |                                     |
|--|-------------------------------------|
| Max. internal inductance $L_i$   | negligible                          |
| Max. internal capacitance $C_i$  | 11 nF                               |
| Max. output voltage $U_o$  | 25.1 V                              |
| Max. output current $I_o$  | 139 mA                              |
| Max. output power $P_o$  | 872 mW                              |
| Safety-related maximum voltage $U_m$   | 253 V AC ( $\leq 2000$ m)           |
|  | 125 V DC ( $\leq 2000$ m)           |
|  | 121 V AC ( $> 2000$ m ... 3000 m)   |
|  | 110 V DC ( $> 2000$ m ... 3000 m)   |
|  | 33 V AC/DC ( $> 3000$ m ... 4000 m) |
|  | 33 V AC/DC ( $> 4000$ m ... 5000 m) |
| IIA (simple circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$      | 10 mH / 2.92 $\mu$ F                |
| IIB/IIIC (simple circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$ | 5 mH / 819 nF                       |
| IIC (simple circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$      | 1.5 mH / 97 nF                      |
| I (simple circuit): Max. external inductivity $L_o$ / Max. external capacitance $C_o$        | 15 mH / 4.84 $\mu$ F                |

## Dimensions

|        |           |
|--------|-----------|
| Width  | 6.2 mm    |
| Height | 109.81 mm |
| Depth  | 119.2 mm  |

## Material specifications

|       |                 |
|-------|-----------------|
| Color | gray (RAL 7042) |
|-------|-----------------|

## Environmental and real-life conditions

### Ambient conditions

|   |                               |
|---|-------------------------------|
| Degree of protection                    | IP20                          |
| Ambient temperature (operation)         | -40 °C ... 70 °C              |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C              |
| Permissible humidity (operation)        | 5 % ... 95 % (non-condensing) |

### Altitude range (IEC/EN 61010-1)

|                                 |                                     |
|---------------------------------|-------------------------------------|
| Height range                    | > 2000 m ... 3000 m                 |
| Ambient temperature (operation) | -40 °C ... 63 °C                    |
| Rated insulation voltage        | 300 V <sub>rms</sub> (Input/output) |
| Insulation                      | Double/reinforced insulation        |

### Altitude range (IEC/EN 61010-1)

|                                 |                                     |
|---------------------------------|-------------------------------------|
| Height range                    | > 3000 m ... 4000 m                 |
| Ambient temperature (operation) | -40 °C ... 56 °C                    |
| Rated insulation voltage        | 300 V <sub>rms</sub> (Input/output) |
| Insulation                      | Double/reinforced insulation        |

### Altitude range (IEC/EN 61010-1)

|                                 |                                     |
|---------------------------------|-------------------------------------|
| Height range                    | > 4000 m ... 5000 m                 |
| Ambient temperature (operation) | -40 °C ... 49 °C                    |
| Rated insulation voltage        | 150 V <sub>rms</sub> (Input/output) |
| Insulation                      | Double/reinforced insulation        |

### Altitude range (IEC/EN 60079-11)

|                                 |                                     |
|---------------------------------|-------------------------------------|
| Height range                    | > 2000 m ... 3000 m                 |
| Ambient temperature (operation) | -40 °C ... 63 °C                    |
| Rated insulation voltage        | 150 V <sub>rms</sub> (Input/output) |

### Altitude range (IEC/EN 60079-11)

|                                 |                                    |
|---------------------------------|------------------------------------|
| Height range                    | > 3000 m ... 4000 m                |
| Ambient temperature (operation) | -40 °C ... 56 °C                   |
| Rated insulation voltage        | 60 V <sub>rms</sub> (Input/output) |

### Altitude range (IEC/EN 60079-11)

|                                 |                                    |
|---------------------------------|------------------------------------|
| Height range                    | > 4000 m ... 5000 m                |
| Ambient temperature (operation) | -40 °C ... 49 °C                   |
| Rated insulation voltage        | 60 V <sub>rms</sub> (Input/output) |

### Altitude range (IEC/EN 60079-7)

|                                 |                                     |
|---------------------------------|-------------------------------------|
| Height range                    | > 2000 m ... 3000 m                 |
| Ambient temperature (operation) | -40 °C ... 63 °C                    |
| Rated insulation voltage        | 162 V <sub>rms</sub> (Input/output) |

### Altitude range (IEC/EN 60079-7)

# MINI MCR-EX-SD-21-48-LP-PT - Solenoid driver



2908811

<https://www.phoenixcontact.com/us/products/2908811>

|                                 |                                    |
|---------------------------------|------------------------------------|
| Height range                    | > 3000 m ... 4000 m                |
| Ambient temperature (operation) | -40 °C ... 56 °C                   |
| Rated insulation voltage        | 60 V <sub>rms</sub> (Input/output) |

## Altitude range (IEC/EN 60079-7)

|                                 |                                    |
|---------------------------------|------------------------------------|
| Height range                    | > 4000 m ... 5000 m                |
| Ambient temperature (operation) | -40 °C ... 49 °C                   |
| Rated insulation voltage        | 60 V <sub>rms</sub> (Input/output) |

## Approvals

### CE

|             |              |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

### ATEX

|                |                                      |
|----------------|--------------------------------------|
| Identification | ⊕ II (1) G [Ex ia Ga] IIC            |
|                | ⊕ II (1) D [Ex ia Da] IIIC           |
|                | ⊕ II 3 (1) G Ex ec [ia Ga] IIC T4 Gc |
|                | ⊕ I (M1) [Ex ia Ma] I                |
| Certificate    | TÜV 21 ATEX 8651 X                   |

### IECEX

|                |                         |
|----------------|-------------------------|
| Identification | [Ex ia Ga] IIC          |
|                | [Ex ia Da] IIIC         |
|                | Ex ec [ia Ga] IIC T4 Gc |
|                | [Ex ia Ma] I            |
| Certificate    | IECEX TUR 21.0043 X     |

### CCC / China-Ex

|                |                         |
|----------------|-------------------------|
| Identification | [Ex ia Ga] IIC          |
|                | [Ex ia Da] IIIC         |
|                | Ex ec [ia Ga] IIC T4 Gc |
| Certificate    | 2023122310116238        |

### UL, USA/Canada

|                |   |
|----------------|---|
| Identification | UL 61010-2-201 Listed                                     |
|                | Class I, Div. 1, Groups A, B, C, D                        |
|                | Class II, Div. 1, Groups E, F, G                          |
|                | Class III, Div. 1   |
|                | Class I, Zone 0, 1, 2, Groups IIC, IIB, IIA               |
|                | Class I, Div. 2, Groups A, B, C, D T4                     |
|                | Class I, Zone 2   |
|                | AEx ec [ia Ga] IIC T4 Gc; AEx ec [ia IIIC Da] IIC T4 Gc   |
|                | Ex ec [ia Ga] IIC T4 Gc X; Ex ec [ia IIIC Da] IIC T4 Gc X |
|                | Class I, Zone 0, [AEx ia Ga] IIC, [Ex ia Ga] IIC X        |
|                | Class I, Zone 20, [AEx ia Da] IIIC, [Ex ia Da] IIIC X     |
|                | Certificate   |

# MINI MCR-EX-SD-21-48-LP-PT - Solenoid driver



2908811

<https://www.phoenixcontact.com/us/products/2908811>

## Shipbuilding approval

|             |                |
|-------------|----------------|
| Certificate | DNV TAA00003FZ |
|-------------|----------------|

## Safety Integrity Level (SIL, IEC 61508)

|                |   |
|----------------|---|
| Identification | 3 |
|----------------|---|

## INMETRO

|                |                         |
|----------------|-------------------------|
| Identification | [Ex ia Ma] I            |
|                | [Ex ia Ga] IIC          |
|                | [Ex ia Da] IIIC         |
|                | Ex ec [ia Ga] IIC T4 Gc |
| Certificate    | DNV 23.0189 X           |

## Shipbuilding data

|             |   |
|-------------|---|
| Temperature | B   |
| Humidity    | B   |
| Vibration   | A   |
| EMC         | A   |
| Enclosure   | Required protection according to the Rules shall be provided upon installation on board |

## EMC data

|                               |   |
|-------------------------------|---|
| Electromagnetic compatibility | Tested in accordance with the following standards and regulations: EN 61326-1 For industrial use, NAMUR NE 21 |
| Noise immunity                | IEC/EN 61000-6-2  |
| Noise immunity                | IEC/EN 61326-3-2  |

## Noise emission

|                       |                  |
|-----------------------|------------------|
| Standards/regulations | IEC/EN 61000-6-4 |
|-----------------------|------------------|

## Standards and regulations

### GB Standard

|                       |             |
|-----------------------|-------------|
| Standards/regulations | GB/T 3836.1 |
|                       | GB/T 3836.3 |
|                       | GB/T 3836.4 |

## Mounting

|               |                   |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

# MINI MCR-EX-SD-21-48-LP-PT - Solenoid driver




2908811

<https://www.phoenixcontact.com/us/products/2908811>

## Drawings

Block diagram



2908811

<https://www.phoenixcontact.com/us/products/2908811>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2908811>



### Functional Safety

Approval ID: 1435.IM.131623/19



### cULus Listed

Approval ID: E238705

### DNV

Approval ID: TAA00003FZ



### cULus Listed

Approval ID: E238705



### IECEX

Approval ID: IECEX TUR 21.0043X



### ATEX

Approval ID: TUV 21 ATEX 8651 X



### CCC

Approval ID: 2023122316116237



### cULus Listed

Approval ID: E196811



### cULus Listed

Approval ID: E196811

### INMETRO

Approval ID: DNV 23.0189 X

# MINI MCR-EX-SD-21-48-LP-PT - Solenoid driver



2908811

<https://www.phoenixcontact.com/us/products/2908811>

## Classifications

### ECLASS

|                   |          |
|-------------------|----------|
| ECLASS-13.0       | 27210120 |
| ECLASS-15.0       | 27210120 |
| ECLASS-15.0 ASSET | 27250101 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002653 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121008 |
|-------------|----------|

2908811

<https://www.phoenixcontact.com/us/products/2908811>

## Environmental product compliance

### EU RoHS

|   |              |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes          |
| Exemption                               | 7(a), 7(c)-I |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 021b6de6-6ba8-4025-a2e5-2b0284201a9b |

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)