

VIP-PA-PWR/36XOE/ 1,0M/1756 - Front adapter



2908859

<https://www.phoenixcontact.com/us/products/2908859>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VIP power cabling, universal front adapter with assembled shielded round cable for connection to all popular 36-pos. ControlLogix® 1756 I/O modules. 1 x 36 single wires (each ferruled and marked) can be connected (field connection, e.g., via 36 terminal blocks).

Your advantages

- Individual I/O modules lock to the controller for connection security
- Integrated lever aids in removal from I/O card
- Marking label can be attached
- 1:1 connection
- Open end at one end
- Individual wire marking: 1, 2, 3, 4, etc.
- Individual wires fitted with ferrules
- Shield connection: UL Type AWM, Style 1007 18 AWG (0.82 mm²) cable, black, 0.5 m length

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2908859 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C423 |
| Product key | DK232R |
| GTIN | 4063151467876 |
| Weight per piece (including packing) | 590 g |
| Weight per piece (excluding packing) | 590 g |
| Customs tariff number | 85444290 |
| Country of origin | US |

VIP-PA-PWR/36XOE/ 1,0M/1756 - Front adapter



2908859

<https://www.phoenixcontact.com/us/products/2908859>

Technical data

Product properties

| | |
|--------------|---------------|
| Product type | Front adapter |
|--------------|---------------|

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Pollution degree | 2 |

Electrical properties

| | |
|--------------------------------------|---------------|
| Operating voltage (AC/DC) | ≤ 250 V AC/DC |
| Current (per single-core wire, 60°C) | ≤ 3 A |
| Current (per single-core wire, 40°C) | ≤ 4 A |

Supported controller: ALLEN-BRADLEY ControlLogix

| | |
|-------------------|----------------|
| Suitable I/O card | 1756-IB16D |
| | 1756-IB16I |
| | 1756-IB32 |
| | 1756-IF16 |
| | 1756-IF8 |
| | 1756-IF8I |
| | 1756-IRT8I |
| | 1756-OB16D |
| | 1756-OB16I |
| | 1756-OB32 |
| | 1756-HSC |
| | 1756-IA16I |
| | 1756-IA32 |
| | 1756-IB16IF |
| | 1756-IB16ISOE |
| | 1756-IF16H |
| | 1756-IF4FXOF2F |
| | 1756-IF8H |
| | 1756-IF8IH |
| | 1756-IH16I |
| | 1756-IH16ISOE |
| | 1756-IM16I |
| | 1756-IR12 |
| | 1756-IT16 |
| | 1756-IV32 |
| | 1756-LSC8XIB8I |
| 1756-OA16I | |
| 1756-OB16IEF | |
| 1756-OB16IEFS | |

VIP-PA-PWR/36XOE/ 1,0M/1756 - Front adapter



2908859

<https://www.phoenixcontact.com/us/products/2908859>

| | |
|--|-------------|
| | 1756-OB16IS |
| | 1756-OB8EI |
| | 1756-OF8I |
| | 1756-OF8IH |
| | 1756-OH8I |
| | 1756-OV32E |
| | 1756-OW16I |
| | 1756-OX8I |
| | 1756-IF16IH |

Connection data

Controller level

| | |
|-------------------|---|
| Connection method | Plug-in connection |
| Note | Can be plugged onto 36-pos. I/O modules |

Field level

| | |
|-----------------------|---|
| Connection method | Single wires |
| Number of connections | 36 |
| Number of positions | 1 |
| Note | The wires are marked and fitted with ferrules |

Dimensions

Cable

| | |
|--------|-----|
| Length | 1 m |
|--------|-----|

Cable/line

| | |
|---|--------------------------------|
| Number of positions | 36 |
| Shielded | yes |
| Conductor type | Assembled shielded round cable |
| AWG signal line | 18 |
| Conductor cross-section | 36x 0.82 mm ² |
| Wire diameter incl. insulation | 1.7 mm ±0.0254 |
| External cable diameter | 15.88 mm ±0.3 mm |
| Outer sheath, material | PVC |
| External sheath, color | gray |
| Conductor material | Tin-plated Cu litz wires |
| Cable resistance | ≤ 40 Ω/km (20 °C) |
| Insulation resistance | ≥ 20 MΩ*km (20 °C) |
| Smallest bending radius, fixed installation | 109.5 mm |
| Smallest bending radius, movable installation | 156.2 mm |
| Halogen-free | no |
| Flame resistance | UL VW-1 CSA FT-1 |

VIP-PA-PWR/36XOE/ 1,0M/1756 - Front adapter



2908859

<https://www.phoenixcontact.com/us/products/2908859>

1X1.0 [PVC]

| | |
|------------|---|
| Cable type | 1X1.0 [PVC] |
| Cable type | Front adapter with cable and 36 open cable ends |

Color code: Single-core wire

| | |
|--------------|--|
| black | ControlLogix [®] plug (1) = () |
| brown | ControlLogix [®] plug (2) = () |
| red | ControlLogix [®] plug (3) = () |
| orange | ControlLogix [®] plug (4) = () |
| yellow | ControlLogix [®] plug (5) = () |
| green | ControlLogix [®] plug (6) = () |
| blue | ControlLogix [®] plug (7) = () |
| violet | ControlLogix [®] plug (8) = () |
| gray | ControlLogix [®] plug (9) = () |
| white | ControlLogix [®] plug (10) = () |
| white-black | ControlLogix [®] plug (11) = () |
| white-brown | ControlLogix [®] plug (12) = () |
| white-red | ControlLogix [®] plug (13) = () |
| white-orange | ControlLogix [®] plug (14) = () |
| white-yellow | ControlLogix [®] plug (15) = () |
| white-green | ControlLogix [®] plug (16) = () |
| white-blue | ControlLogix [®] plug (17) = () |
| white-violet | ControlLogix [®] plug (18) = () |
| white-gray | ControlLogix [®] plug (19) = () |
| brown-black | ControlLogix [®] plug (20) = () |
| brown-red | ControlLogix [®] plug (21) = () |
| brown-orange | ControlLogix [®] plug (22) = () |
| brown-yellow | ControlLogix [®] plug (23) = () |
| brown-green | ControlLogix [®] plug (24) = () |
| brown-blue | ControlLogix [®] plug (25) = () |
| brown-violet | ControlLogix [®] plug (26) = () |
| brown-gray | ControlLogix [®] plug (27) = () |
| brown-white | ControlLogix [®] plug (28) = () |
| green-black | ControlLogix [®] plug (29) = () |
| green-brown | ControlLogix [®] plug (30) = () |
| green-red | ControlLogix [®] plug (31) = () |
| green-orange | ControlLogix [®] plug (32) = () |
| green-blue | ControlLogix [®] plug (33) = () |
| green-violet | ControlLogix [®] plug (34) = () |
| green-gray | ControlLogix [®] plug (35) = () |
| green-white | ControlLogix [®] plug (36) = () |

Environmental and real-life conditions

VIP-PA-PWR/36XOE/ 1,0M/1756 - Front adapter



2908859

<https://www.phoenixcontact.com/us/products/2908859>

Ambient conditions

| | |
|---|------------------|
| Degree of protection (IP20) | IP20 |
| Ambient temperature (operation) | 0 °C ... 60 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Altitude | < 2000 m |

Approvals

UL data

| | |
|--|--------|
| Max. permissible relative humidity (operation) | < 95 % |
|--|--------|

Standards and regulations

| | |
|-----------------------|----------------|
| Standards/regulations | UL 61010-2-201 |
|-----------------------|----------------|

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

2908859

<https://www.phoenixcontact.com/us/products/2908859>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2908859>



UL classified

Approval ID: FILE E238705



cUL Classified

Approval ID: FILE E238705



cUL Recognized

Approval ID: FILE E196811



UL Recognized

Approval ID: FILE E196811

VIP-PA-PWR/36XOE/ 1,0M/1756 - Front adapter



2908859

<https://www.phoenixcontact.com/us/products/2908859>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27242292 |
| ECLASS-15.0 | 27242292 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002584 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 32151600 |
|-------------|----------|

VIP-PA-PWR/36XOE/ 1,0M/1756 - Front adapter



2908859

<https://www.phoenixcontact.com/us/products/2908859>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com