

# QUINT-DIODE/40 - Redundancy module



2938963

<https://www.phoenixcontact.com/us/products/2938963>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Redundancy module QUINT-DIODE/40



## Commercial data

Item number	2938963
Packing unit	1 pc
Sales key	NULL
Product key	CMRP43
GTIN	4017918929534
Weight per piece (including packing)	683 g
Weight per piece (excluding packing)	600 g
Customs tariff number	85049090
Country of origin	CN

# QUINT-DIODE/40 - Redundancy module



2938963

<https://www.phoenixcontact.com/us/products/2938963>

## Technical data

### Input data

#### DC operation

Input voltage	24 V DC
Nominal input voltage range	24 V DC
Input voltage range	0 V DC ... 30 V DC
Input voltage range DC	0 V DC ... 30 V DC
Voltage type of supply voltage	DC
Reverse polarity protection	yes, < 60 V
Nominal input current ( $I_N$ )	2x 20 A 1x 40 A
Maximum current $I_{max}$	2x 19 A (6 mm <sup>2</sup> at 40°C) 1x 39 A (6 mm <sup>2</sup> at 40°C) 2x 16 A (6 mm <sup>2</sup> at 60°C) 1x 32 A (6 mm <sup>2</sup> at 60°C) 2x 27 A (10 mm <sup>2</sup> at 40°C) 1x 54 A (10 mm <sup>2</sup> at 40°C) 2x 21 A (10 mm <sup>2</sup> at 60°C) 1x 43 A (10 mm <sup>2</sup> at 60°C) 2x 30 A (16 mm <sup>2</sup> at 40 °C) 1x 60 A (16 mm <sup>2</sup> at 40 °C) 2x 24 A (16 mm <sup>2</sup> at 60°C) 1x 48 A (16 mm <sup>2</sup> at 60°C)
Transient surge protection	Transil diode
Voltage drop, input/output	0.5 V

### Output data

Efficiency	> 97 %
Nominal output voltage	24 V DC
Nominal output current ( $I_N$ )	40 A
Power loss nominal load max.	20 W
Connection in series	no

### Connection data

#### Input

Connection method	Screw connection
Conductor cross-section, rigid min.	0.5 mm <sup>2</sup>
Conductor cross-section, rigid max.	16 mm <sup>2</sup>
Conductor cross-section flexible min.	0.5 mm <sup>2</sup>
Conductor cross-section flexible max.	10 mm <sup>2</sup>
Conductor cross-section AWG min.	20

# QUINT-DIODE/40 - Redundancy module



2938963

<https://www.phoenixcontact.com/us/products/2938963>

Conductor cross-section AWG max.	6
Stripping length	10 mm
Screw thread	M4

## Output

Connection method	Screw connection
Conductor cross-section, rigid min.	0.5 mm <sup>2</sup>
Conductor cross-section, rigid max.	16 mm <sup>2</sup>
Conductor cross-section flexible min.	0.5 mm <sup>2</sup>
Conductor cross-section flexible max.	10 mm <sup>2</sup>
Conductor cross-section AWG min.	20
Conductor cross-section AWG max.	6
Stripping length	10 mm
Screw thread	M4

## Electrical properties

Insulation voltage output / PE	1 kV
Insulation voltage input / PE	1 kV
Insulation voltage input, output / housing	1 kV

## Product properties

Product type	Redundancy module
Product family	QUINT DIODE
MTBF (IEC 61709, SN 29500)	28571428 h (40 °C)
LED	no

## Insulation characteristics

Protection class	II (in closed control cabinet)
Degree of pollution	2

## Dimensions

Width	62 mm
Height	84 mm
Depth	102 mm
Horizontal pitch	3.4 Div.

## Installation dimensions

Installation distance right/left	5 mm / 5 mm
Installation distance top/bottom	50 mm / 50 mm

## Mounting

Mounting type	DIN rail mounting
Assembly note	alignable: horizontal 20 mm, vertical 50 mm
Mounting position	horizontal and vertical DIN rail NS 35, EN 60715

## Material specifications

# QUINT-DIODE/40 - Redundancy module



2938963

<https://www.phoenixcontact.com/us/products/2938963>

Housing material	Metal
Type of housing	AlMg (hood), GD-ZnAlCu (cooling unit)

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 70 °C (> 60 °C derating,
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Max. permissible relative humidity (operation)	≤ 95 % (at 25 °C, non-condensing)

## Standards and regulations

Standard – Electronic equipment for use in electrical power installations and their assembly into electrical power installations	EN 50178/VDE 0160 (PELV)
Standard - Electrical safety	EN 60950-1/VDE 0805 (SELV)
Standards/specifications	EN 60079-0

## Approvals

Shipbuilding approval	DNV GL (EMC A), ABS
UL approvals	UL/C-UL listed UL 508
	UL/C-UL Recognized UL 60950-1
	UL/C-UL Listed UL 1604 Class I, Division 2, Groups A, B, C, D

### Conformity/Approvals

ATEX	II 3G Ex nA IIC T4 Gc
	KEMA 03 ATEX 1197X

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
EMC requirements for noise emission	EN 61000-6-3
	EN 61000-6-4
EMC requirements for noise immunity	EN 61000-6-1
	EN 61000-6-2

### Noise emission

Standards/regulations	EN 55011
-----------------------	----------

# QUINT-DIODE/40 - Redundancy module




2938963

<https://www.phoenixcontact.com/us/products/2938963>

## Drawings

Block diagram



# QUINT-DIODE/40 - Redundancy module

2938963

<https://www.phoenixcontact.com/us/products/2938963>



## Classifications

### UNSPSC

UNSPSC 21.0	32151504
-------------	----------

# QUINT-DIODE/40 - Redundancy module



2938963

<https://www.phoenixcontact.com/us/products/2938963>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)