

CM-SI-2AF - Fuse



2939027

<https://www.phoenixcontact.com/us/products/2939027>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Output fuse (5x20 mm) acc. to IEC 127-2/EN 60127-2, 2 A fast blow

Commercial data

Item number	2939027
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	CM11
Product key	CMPLZ9
GTIN	4017918099459
Weight per piece (including packing)	1.4 g
Weight per piece (excluding packing)	1.21 g
Customs tariff number	85361010
Country of origin	CN

CM-SI-2AF - Fuse

2939027

<https://www.phoenixcontact.com/us/products/2939027>



Technical data

Product properties

Product type	Fuse
--------------	------

Electrical properties

Rated voltage	250 V
Fuse	fast blow

Signaling

Optical fault display	No
-----------------------	----

Dimensions

Dimensions	5 x 20 mm
------------	-----------

CM-SI-2AF - Fuse



2939027

<https://www.phoenixcontact.com/us/products/2939027>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2939027>



EAC

Approval ID: RU C-DE.BL08.B.00724

CM-SI-2AF - Fuse



2939027

<https://www.phoenixcontact.com/us/products/2939027>

Classifications

ECLASS

ECLASS-13.0	27142002
ECLASS-15.0	27142002

ETIM

ETIM 10.0	EC002704
-----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

CM-SI-2AF - Fuse



2939027

<https://www.phoenixcontact.com/us/products/2939027>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com