

# EMG 17-REL/SDS- 24/21-21/SO 95 - Relay module



2940854

<https://www.phoenixcontact.com/us/products/2940854>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Customer-specific relay module, 2 changeover contacts, input voltage 24 V AC/DC

## Commercial data

Item number	2940854
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C460
Product key	DK61Y1
GTIN	4017918341862
Weight per piece (including packing)	51.77 g
Weight per piece (excluding packing)	51.77 g
Customs tariff number	85364190
Country of origin	DE

## Technical data

### Product properties

Product type	Relay Module
Mechanical service life	1x 10 <sup>8</sup> switching cycles

#### Insulation characteristics: Air clearances and creepage distances, input/output

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

#### Insulation characteristics: Air and creepage distances, output/output

Insulation	Functional insulation
Overvoltage category	II
Degree of pollution	2

#### Data management status

Date of last data management	12.09.2025
------------------------------	------------

### Electrical properties

#### Air clearances and creepage distances, input/output

Rated insulation voltage	260 V
Rated surge voltage	4 kV (1.2/50 µs)

#### Air and creepage distances, output/output

Rated insulation voltage	230 V
Rated surge voltage	2.1 kV (1.2/50 µs)

### Input data

#### Coil side

Nominal input voltage $U_N$	24 V AC/DC
Input voltage range	20.4 V AC/DC ... 26.4 V AC/DC (20 °C)
Typical input current at $U_N$	11 mA
Typical response time	8 ms
Typical release time	5 ms
Protective circuit	Bridge rectifier; Bridge rectifier
Operating voltage display	Yellow LED

### Output data

#### Switching

Contact switching type	Double contact, 2 changeover contacts
Type of switch contact	Double contact
Contact material	AgNi
Maximum switching voltage	230 V AC/DC

# EMG 17-REL/SDS- 24/21-21/SO 95 - Relay module



2940854

<https://www.phoenixcontact.com/us/products/2940854>

Limiting continuous current	3 A
-----------------------------	-----

## Connection data

### Coil side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

### Contact side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

## Dimensions

Width	17.5 mm
Height	75 mm
Depth	47.5 mm

## Material specifications

Color	green (RAL 6021)
-------	------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 40 °C
Altitude	≤ 2000 m

## Standards and regulations

### Air clearances and creepage distances, input/output

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

### Air and creepage distances, output/output

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

# EMG 17-REL/SDS- 24/21-21/SO 95 - Relay module



2940854

<https://www.phoenixcontact.com/us/products/2940854>

## Classifications

### UNSPSC

UNSPSC 21.0	39122300
-------------	----------

2940854

<https://www.phoenixcontact.com/us/products/2940854>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)