


DEK-REL- 5/O/1 - Relay module



2941170

<https://www.phoenixcontact.com/us/products/2941170>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay terminal block, with soldered-in miniature relays, contact (AgNi+Au): small to medium loads, 1 N/O contact, input voltage 5 V AC/DC, for assembly on NS 35/7.5, terminal width 6.2 mm, design rotated

Your advantages

- Reduced costs as N terminal block is no longer required
- Up to 73 % more space
- Wiring reduced to a minimum
- Integrated input circuit
- 2-layer contact with hard gold plating for universal applications from 1 mA to 5 A continuous current
- 2 kV_{rms} electrical isolation between input and output

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2941170 |
| Packing unit | 10 pc |
| Minimum order quantity | 1 pc |
| Sales key | C460 |
| Product key | DK61A2 |
| GTIN | 4017918080327 |
| Weight per piece (including packing) | 23.012 g |
| Weight per piece (excluding packing) | 23.012 g |
| Customs tariff number | 85364190 |
| Country of origin | CN |

DEK-REL- 5/O/1 - Relay module



2941170

<https://www.phoenixcontact.com/us/products/2941170>

Technical data

Notes

| | |
|---------------------|---|
| Note on application | Use of EB 80-DIK... bridges in the DEK terminal blocks: Absorption of humidity from the ambient air as well as an unfavorable tolerance between a larger number of DEK terminal blocks and the EB 80-DIK... bridge may cause (minor) expansion of the DEK housing. When the EB 80-DIK... bridges are used, therefore, it is recommended that these be disconnected after about 10 to 12 DEK terminal blocks and a wire bridge to the next DEK terminal block be inserted in their place. |
|---------------------|---|

Product properties

| | |
|-------------------------|--------------------------------|
| Product type | Relay Module |
| Product family | DEK |
| Application | Input function |
| Operating mode | 100% operating factor |
| Mechanical service life | approx. 2×10^7 cycles |

Insulation characteristics

| | |
|----------------------|------------------|
| Insulation | Basic insulation |
| Overvoltage category | III |
| Pollution degree | 2 |

Data management status

| | |
|------------------------------|------------|
| Date of last data management | 01.04.2026 |
|------------------------------|------------|

Electrical properties

| | |
|---|--|
| Maximum power dissipation for nominal condition | 0.12 W |
| Test voltage (Winding/contact) | 2 kV AC (50 Hz, 1 min., winding/contact) |

Input data

Coil side

| | |
|--------------------------------|-------------------------------------|
| Nominal input voltage U_N | 5 V AC/DC |
| Input voltage range | 4.5 V AC/DC ... 5.5 V AC/DC (20 °C) |
| Drive and function | monostable |
| Drive (polarity) | polarized |
| Typical input current at U_N | 23 mA |
| Typical response time | 8 ms |
| Typical release time | 15 ms |
| Protective circuit | Bridge rectifier; Bridge rectifier |
| Operating voltage display | Yellow LED |

Output data

Switching

| | |
|------------------------|---------------|
| Contact switching type | 1 N/O contact |
|------------------------|---------------|

DEK-REL- 5/O/1 - Relay module



2941170

<https://www.phoenixcontact.com/us/products/2941170>

| | |
|---------------------------------------|---------------------------------|
| Type of switch contact | Double contact |
| Contact material | AgNi, hard gold-plated |
| Maximum switching voltage | 250 V AC |
| | 125 V DC |
| Minimum switching voltage | 0.1 V |
| Limiting continuous current | 3 A (5 A up to 35°C at 24 V DC) |
| Maximum inrush current | 5 A |
| Min. switching current | 1 mA |
| Interrupting rating (ohmic load) max. | 72 W (at 24 V DC) |
| | 60 W (at 48 V DC) |
| | 50 W (at 60 V DC) |
| | 50 W (at 110 V DC) |
| | 750 VA (for 250 V AC) |
| | 120 W (at 24 V DC - up to 35°) |

Connection data

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 14 |
| Tightening torque | 0.4 Nm ... 0.5 Nm |

Dimensions

Item dimensions

| | |
|--------|--------|
| Width | 6.2 mm |
| Height | 80 mm |
| Depth | 56 mm |

Material specifications

| | |
|-------|------------------|
| Color | green (RAL 6021) |
|-------|------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

Standards and regulations

| | |
|-----------------------|---------------|
| Standards/regulations | IEC 60947-5-1 |
|-----------------------|---------------|

Mounting

| | |
|---------------|---------------------------|
| Mounting type | DIN rail mounting |
| Assembly note | in rows with zero spacing |

DEK-REL- 5/O/1 - Relay module



2941170

<https://www.phoenixcontact.com/us/products/2941170>

Mounting position

any

DEK-REL- 5/O/1 - Relay module




2941170

<https://www.phoenixcontact.com/us/products/2941170>

Drawings

Circuit diagram



DEK-REL- 5/O/1 - Relay module



2941170

<https://www.phoenixcontact.com/us/products/2941170>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2941170>



EAC

Approval ID: RU*C-DE.*08.B.00010

DEK-REL- 5/O/1 - Relay module



2941170

<https://www.phoenixcontact.com/us/products/2941170>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27371601 |
| ECLASS-15.0 | 27371601 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001437 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39122300 |
|-------------|----------|

2941170

<https://www.phoenixcontact.com/us/products/2941170>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 5b839385-52ee-4a00-be30-3a0a914ea8b1 |

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com