

# EMG 10-REL/KSR-G 60/ 1-LC - Relay module



2941303

<https://www.phoenixcontact.com/us/products/2941303>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay module, with soldered-in miniature switching relay, contacts (AgNi): Medium to large loads, 1 N/O contact, input voltage 60 V DC

## Your advantages

- Integrated input circuit and interference suppression circuit

## Commercial data

Item number	2941303
Packing unit	10 pc
Minimum order quantity	1 pc
Product key	DK6142
GTIN	4017918080365
Weight per piece (including packing)	35.3 g
Weight per piece (excluding packing)	35.3 g
Country of origin	DE

# EMG 10-REL/KSR-G 60/ 1-LC - Relay module



2941303

<https://www.phoenixcontact.com/us/products/2941303>

## Technical data

### Product properties

Product type	Relay Module
Application	Universal
Operating mode	100% operating factor
Mechanical service life	approx. $2 \times 10^7$ cycles

### Insulation characteristics

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

### Data management status

Date of last data management	01.04.2026
------------------------------	------------

### Electrical properties

Maximum power dissipation for nominal condition	0.6 W
Test voltage (Winding/contact)	4 kV AC (50 Hz, 1 min., winding/contact)
Rated insulation voltage	260 V AC
Rated surge voltage	4 kV

### Input data

#### Coil side

Nominal input voltage $U_N$	60 V DC
Input voltage range	48 V DC ... 66 V DC
Input voltage range in reference to $U_N$	0.8 ... 1.1
Drive and function	monostable
Typical input current at $U_N$	10 mA
Typical response time	7 ms
Typical release time	11 ms
Protective circuit	Reverse polarity protection; Polarity protection diode Freewheeling diode; Freewheeling diode
Operating voltage display	Yellow LED

### Output data

#### Switching

Contact switching type	Single contact, 1 N/O contact
Type of switch contact	Single contact
Contact material	AgNi
Maximum switching voltage	250 V AC/DC
Minimum switching voltage	12 V
Limiting continuous current	6 A

# EMG 10-REL/KSR-G 60/ 1-LC - Relay module



2941303

<https://www.phoenixcontact.com/us/products/2941303>

Maximum inrush current	8 A
Min. switching current	100 mA
Interrupting rating (ohmic load) max.	140 W (at 24 V DC)
	60 W (at 48 V DC)
	45 W (at 60 V DC)
	35 W (at 110 V DC)
	55 W (at 220 V DC)
	1500 VA (for 250 V AC)

## Connection data

### Coil side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

### Contact side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

## Dimensions

Width	10.6 mm
Height	75 mm
Depth	53.5 mm

## Material specifications

Color	green (RAL 6021)
-------	------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 40 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

## Standards and regulations

Standards/regulations	IEC 60664
	EN 50178

# EMG 10-REL/KSR-G 60/ 1-LC - Relay module



2941303

<https://www.phoenixcontact.com/us/products/2941303>

## Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

# EMG 10-REL/KSR-G 60/ 1-LC - Relay module

2941303

<https://www.phoenixcontact.com/us/products/2941303>



## Drawings

Connection diagram



# EMG 10-REL/KSR-G 60/ 1-LC - Relay module

2941303

<https://www.phoenixcontact.com/us/products/2941303>



Circuit diagram




# EMG 10-REL/KSR-G 60/ 1-LC - Relay module

2941303

<https://www.phoenixcontact.com/us/products/2941303>



Circuit diagram



# EMG 10-REL/KSR-G 60/ 1-LC - Relay module



2941303

<https://www.phoenixcontact.com/us/products/2941303>

## Classifications

### UNSPSC

UNSPSC 21.0	39122334
-------------	----------

# EMG 10-REL/KSR-G 60/ 1-LC - Relay module



2941303

<https://www.phoenixcontact.com/us/products/2941303>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)