

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Relay Module
Product family	EMG
Application	high inrush currents
Operating mode	100% operating factor
Mechanical service life	3x 10 ⁷ cycles

Insulation characteristics

Insulation	safe isolation
Overvoltage category	III
Pollution degree	2

Data management status

Date of last data management	01.04.2026
------------------------------	------------

Electrical properties

Maximum power dissipation for nominal condition	0.55 W
Test voltage (Winding/contact)	4 kV AC (50 Hz, 1 min., winding/contact)

Input data

Coil side

Nominal input voltage U_N	24 V DC
Input voltage range	21.6 V DC ... 26.4 V DC (20 °C)
Drive and function	monostable
Drive (polarity)	polarized
Typical input current at U_N	23 mA
Typical response time	9 ms
Typical release time	10 ms
Protective circuit	Freewheeling diode; Freewheeling diode Reverse polarity protection; Polarity protection diode
Operating voltage display	Automatic: Yellow LED, Manual: Red LED

Output data

Switching

Contact switching type	1 N/O contact
Type of switch contact	Single contact

EMG 17-REL/KSR-G 24/2E/SO38 - Relay



2941646

<https://www.phoenixcontact.com/us/products/2941646>

Contact material	AgSnO
Maximum switching voltage	250 V AC/DC
Limiting continuous current	10 A
Maximum inrush current	120 A (20 ms)
Interrupting rating (ohmic load) max.	240 W (at 24 V DC)
	120 W (at 48 V DC)
	85 W (at 60 V DC)
	70 W (at 110 V DC)
	90 W (at 220 V DC)
	100 W (for 250 V DC)
Interrupting rating (lamp load) max.	2500 VA (for 250 V AC)
Interrupting rating (lamp load) max.	on request

Connection data

Coil side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm

Contact side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Dimensions

Item dimensions

Width	17.5 mm
Height	75 mm
Depth	62.5 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

EMG 17-REL/KSR-G 24/2E/SO38 - Relay



2941646

<https://www.phoenixcontact.com/us/products/2941646>

Ambient temperature (storage/transport)	-20 °C ... 70 °C
---	------------------

Standards and regulations

Standards/regulations	IEC 60664
	EN 50178

Mounting

Mounting type	DIN rail mounting
Mounting position	any

EMG 17-REL/KSR-G 24/2E/SO38 - Relay




2941646

<https://www.phoenixcontact.com/us/products/2941646>

Drawings

Circuit diagram



EMG 17-REL/KSR-G 24/2E/SO38 - Relay



2941646

<https://www.phoenixcontact.com/us/products/2941646>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2941646>



EAC

Approval ID: RU*DE*08.B.01841/19

EMG 17-REL/KSR-G 24/2E/SO38 - Relay



2941646

<https://www.phoenixcontact.com/us/products/2941646>

Classifications

ECLASS

ECLASS-13.0	27371601
ECLASS-15.0	27371601

ETIM

ETIM 10.0	EC001437
-----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

2941646

<https://www.phoenixcontact.com/us/products/2941646>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f5e99c25-03b1-4069-bba7-3ed2d025fbd6

EF3.1 Climate Change

CO2e kg	1.386 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com