

# ELR 3/ 9-500 - Load relay

2941714

<https://www.phoenixcontact.com/us/products/2941714>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electronic load relay, for direct driving of equipment in the 3-phase network, with light indicator and protection circuit, output: 110-550 V AC/3 x 9 A

The figure shows the version ELR 3/9-400

## Your advantages

- Noise and wear-free switching up to 500 V AC/9 A
- High switching frequency
- Protective circuit in input and output
- Status display

## Commercial data

Item number	2941714
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C472
Product key	DK7212
GTIN	4017918104559
Weight per piece (including packing)	737.77 g
Weight per piece (excluding packing)	731 g
Customs tariff number	85364900
Country of origin	DE

# ELR 3/ 9-500 - Load relay



2941714

<https://www.phoenixcontact.com/us/products/2941714>

## Technical data

### Product properties

Product type	Solid-state contactor
Operating mode	100% operating factor

Insulation characteristics: Air clearances and creepage distances between the power circuits

Insulation	Basic insulation
------------	------------------

### Electrical properties

Number of phases	3
Switching frequency	max. 10 Hz (at $\cos \varphi = 0.5$ )
Maximum power dissipation for nominal condition	43 W
Mains type	3-phase
Test voltage (Input/output)	2.5 kV (50 Hz, 60 s)
Switching frequency	max. 10 Hz (at $\cos \varphi = 0.5$ )

### Input data

#### Control

Input name	Control input right/left
Rated actuating voltage $U_C$	24 V DC
Triggering voltage range	19.2 V DC ... 28.8 V DC
Voltage range with reference to $U_C$	0.8 ... 1.2
	0.8 ... 1.2
Rated actuating current $I_C$	16 mA
Reaction time in normal load operation	20 ms
	20 ms
Protective circuit	Reverse polarity protection; Polarity protection diode
	Surge protection
Status display	LED (yellow)
Transmission frequency	1 Hz (at $\cos \varphi = 0.5$ )

### Output data

#### AC output

Rated operating voltage $U_e$	500 V AC
Operating voltage range	110 V AC ... 550 V AC
Peak offstate voltage	1200 V
Mains frequency	50 Hz
	60 Hz
Load current range	150 mA ... 9 A (see to derating)
Leakage current	typ. 7 mA
Residual voltage	typ. 1.5 V
Surge current	230 A ( $t_p = 10$ ms, at 25 °C)

# ELR 3/ 9-500 - Load relay



2941714

<https://www.phoenixcontact.com/us/products/2941714>

Protective circuit	RC element; RC element
	Surge protection
Surge voltage protection	> 750 V

## Connection data

### Control circuits

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 10

### Load circuit

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 6 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 10

## Dimensions

Width	62 mm
Height	84 mm
Depth	110 mm

## Material specifications

Color	green (RAL 6021)
-------	------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

## Standards and regulations

### Air clearances and creepage distances between the power circuits

Standards/regulations	EN 50178
-----------------------	----------

### EMC regulations

Standards/regulations	EN 61000-6-2
	EN 61000-6-4

## Mounting

# ELR 3/ 9-500 - Load relay




2941714

<https://www.phoenixcontact.com/us/products/2941714>


Mounting type	DIN rail mounting
Assembly note	can be aligned with spacing > 20 mm
Mounting position	Vertical (horizontal DIN rail)

## Drawings

Diagram




Diagram



# ELR 3/ 9-500 - Load relay

2941714

<https://www.phoenixcontact.com/us/products/2941714>



# ELR 3/ 9-500 - Load relay

2941714

<https://www.phoenixcontact.com/us/products/2941714>



## Classifications

### UNSPSC

UNSPSC 21.0	39122333
-------------	----------

# ELR 3/ 9-500 - Load relay



2941714

<https://www.phoenixcontact.com/us/products/2941714>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead(CAS: 7439-92-1)
SCIP	59dc1f4a-919f-48e0-b287-4c46764def6e

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)