

# EMG 22-REL/KSR-G 24/TRN24/SO62 - Relay module



2944407

<https://www.phoenixcontact.com/us/products/2944407>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay module, with miniature switching relay, with integrated n-p-n transistor control, for low control currents, contact (AgNi 90/10): Medium to large loads, two N/O contacts, nominal control voltage 24 V DC

## Commercial data

Item number	2944407
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	C460
Product key	DK61Y1
GTIN	4017918278922
Weight per piece (including packing)	83.555 g
Weight per piece (excluding packing)	83.55 g
Customs tariff number	85364190
Country of origin	DE

2944407

<https://www.phoenixcontact.com/us/products/2944407>

## Technical data

### Notes

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

### Product properties

Product type	Relay Module
Mechanical service life	3x 10 <sup>7</sup> cycles

#### Insulation characteristics: Air clearances and creepage distances, input/output

Insulation	Reinforced insulation
Overvoltage category	III
Pollution degree	2

#### Insulation characteristics: Air and creepage distances, output/output

Insulation	Functional insulation
------------	-----------------------

#### Data management status

Date of last data management	01.04.2026
------------------------------	------------

### Electrical properties

Maximum power dissipation for nominal condition	0.6 W
---	-------

#### Air clearances and creepage distances, input/output

Rated insulation voltage	260 V
Rated surge voltage	6 kV (1.2/50 µs)

#### Air and creepage distances, output/output

Rated insulation voltage	260 V
Rated surge voltage	2.2 kV (1.2/50 µs)

### Input data

#### Coil side

Nominal input voltage $U_N$	24 V DC
Input voltage range	19.2 V DC ... 26.4 V DC (20 °C)
Typical input current at $U_N$	17 mA
Typical response time	12 ms
Typical release time	7 ms
Protective circuit	Reverse polarity protection; Polarity protection diode Freewheeling diode; Freewheeling diode
Operating voltage display	Yellow LED

### Output data

# EMG 22-REL/KSR-G 24/TRN24/SO62 - Relay module



2944407

<https://www.phoenixcontact.com/us/products/2944407>

## Switching

Contact switching type	Single contact, 2 N/O contact
Type of switch contact	Single contact
Contact material	AgNi
Maximum switching voltage	250 V AC
Limiting continuous current	4 A
Interrupting rating (ohmic load) max.	96 W (at 24 V DC)
	85 W (at 48 V DC)
	60 W (at 60 V DC)
	44 W (at 110 V DC)
	57 W (at 220 V DC)
	1000 VA (for 250 V AC)

## Connection data

### Coil side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

### Contact side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

## Dimensions

### Item dimensions

Width	22.5 mm
Height	75 mm
Depth	100 mm

## Material specifications

Color	green (RAL 6021)
-------	------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Degree of protection (Installation location)	≥ IP54 (Installation location)

# EMG 22-REL/KSR-G 24/TRN24/SO62 - Relay module



2944407

<https://www.phoenixcontact.com/us/products/2944407>

Ambient temperature (operation)	-20 °C ... 50 °C
Altitude	≤ 2000 m

## Standards and regulations

Air clearances and creepage distances, input/output

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

Air and creepage distances, output/output

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

# EMG 22-REL/KSR-G 24/TRN24/SO62 - Relay module



2944407

<https://www.phoenixcontact.com/us/products/2944407>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2944407>



**EAC**

Approval ID: RU\*C-DE.\*08.B.00010

# EMG 22-REL/KSR-G 24/TRN24/SO62 - Relay module



2944407

<https://www.phoenixcontact.com/us/products/2944407>

## Classifications

### ECLASS

ECLASS-13.0	27371601
ECLASS-15.0	27371601

### ETIM

ETIM 10.0	EC001437
-----------	----------

### UNSPSC

UNSPSC 21.0	39122300
-------------	----------

2944407

<https://www.phoenixcontact.com/us/products/2944407>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	bfef9e03-15f1-4977-a0ce-57602de6366b

### EF3.1 Climate Change

CO2e kg	2.801 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
 586 Fulling Mill Road  
 Middletown, PA 17057, United States  
 (+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)