

EMG 22-REL/KSR- 24/21AU/SO12 - Relay module



2944821

<https://www.phoenixcontact.com/us/products/2944821>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay module, with soldered-in miniature switching relay, contact (AgNi+Au): small to large loads, 1 changeover contact, input voltage 24 V AC/DC

Commercial data

Item number	2944821
Packing unit	10 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	DK614Y
GTIN	4017918279035
Weight per piece (including packing)	68.2 g
Weight per piece (excluding packing)	63.67 g
Country of origin	DE

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Relay Module
Mechanical service life	> 10 ⁷ cycles

Insulation characteristics

Overvoltage category	III
Pollution degree	2

Data management status

Date of last data management	12.09.2025
------------------------------	------------

Electrical properties

Maximum power dissipation for nominal condition	0.46 W
Test voltage (Winding/contact)	4 kV AC (50 Hz, 1 min., winding/contact)

Input data

Coil side

Nominal input voltage U_N	24 V AC/DC
Input voltage range	19.2 V AC/DC ... 26.4 V AC/DC
Input voltage range in reference to U_N	0.8 ... 1.1
Typical input current at U_N	19 mA
Typical response time	9 ms
Typical release time	12 ms
Coil voltage	24 V DC
Operating voltage display	Yellow LED
Coil resistance	1440 Ω \pm 15 %

Output data

Switching

Contact switching type	Single contact, 1 changeover contact
Type of switch contact	Single contact
Contact material	AgNi, hard gold-plated
Maximum switching voltage	30 V AC 36 V DC
Minimum switching voltage	100 mV
Maximum inrush current	50 mA

EMG 22-REL/KSR- 24/21AU/SO12 - Relay module



2944821

<https://www.phoenixcontact.com/us/products/2944821>

Min. switching current	1 mA (At 5 V)
Interrupting rating (ohmic load) max.	1.2 W (at 24 V DC)

Switching: when the gold layer is destroyed

Note	the following values are applicable if a gold layer is destroyed
Maximum switching voltage	250 V AC
	300 V DC
Limiting continuous current	5 A
Maximum inrush current	6 A
Interrupting rating (ohmic load) max.	1100 VA (for 250 V AC)

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

Standards and regulations

Standards/regulations	VDE 0110
-----------------------	----------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

EMG 22-REL/KSR- 24/21AU/SO12 - Relay module



2944821

<https://www.phoenixcontact.com/us/products/2944821>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com