

EMG 17-RC/0,47MYF/220R/S - RC module



2948254

<https://www.phoenixcontact.com/us/products/2948254>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Motor attenuation module, for star-connected three-phase motors. Power range: 7.5 kW



Commercial data

Item number	2948254
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	C440
Product key	DK66M3
GTIN	4017918083205
Weight per piece (including packing)	68.97 g
Weight per piece (excluding packing)	58.8 g
Customs tariff number	85363010
Country of origin	DE

Technical data

Product properties

Product type	Diode module
--------------	--------------

Insulation characteristics

Pollution degree	2
------------------	---

Electrical properties

Capacitor in RC combination	0.47 μ F
Nominal motor power	7.5 kW
Nominal frequency f_N	50 Hz (60 Hz)
Nominal voltage U_N	500 V AC (phase conductor/phase conductor)
Mains type	3-phase
Type of circuit	Star circuit
Power dissipation	0.5 W
Resistor in RC combination	220 Ω
Rated insulation voltage	300 V

Connection data

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 2.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Dimensions

Width	17.5 mm
Height	75 mm
Depth	100 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Approvals

CE

Certificate	CE-compliant
-------------	--------------

EMC data

Low Voltage Directive	Conformance with Low Voltage Directive
-----------------------	--

EMG 17-RC/0,47MYF/220R/S - RC module



2948254

<https://www.phoenixcontact.com/us/products/2948254>

Standards and regulations

Standards/regulations	DIN EN 50178
-----------------------	--------------

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

EMG 17-RC/0,47MYF/220R/S - RC module


2948254

<https://www.phoenixcontact.com/us/products/2948254>



Drawings

Circuit diagram



EMG 17-RC/0,47MYF/220R/S - RC module



2948254

<https://www.phoenixcontact.com/us/products/2948254>

Classifications

UNSPSC

UNSPSC 21.0	32151504
-------------	----------

EMG 17-RC/0,47MYF/220R/S - RC module



2948254

<https://www.phoenixcontact.com/us/products/2948254>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com