

UM-BEFE 35 BK (VPE 500) - Base element



2957355

<https://www.phoenixcontact.com/us/products/2957355>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Press-drawn section housings, DIN rail mounting, Plug-in module base element, with ribs, with snap-on foot, width: 35 mm, height: 111 mm, depth: 27.7 mm



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2957355 |
| Packing unit | 500 pc |
| Minimum order quantity | 500 pc |
| Note | Made to order (non-returnable) |
| Sales key | AC13 |
| Product key | ACHDDA |
| GTIN | 4017918279677 |
| Weight per piece (including packing) | 25.93 g |
| Weight per piece (excluding packing) | 25.3 g |
| Customs tariff number | 85369010 |
| Country of origin | PL |

UM-BEFE 35 BK (VPE 500) - Base element



2957355

<https://www.phoenixcontact.com/us/products/2957355>

Technical data

Product properties

| | |
|------------------------------|------------------------------------|
| Product type | Component housing lower part |
| Housing type | Press-drawn section housings |
| Housing type | Plug-in module DIN rail-mount base |
| Housing series | UM |
| Product family | UM BE |
| Ventilation openings present | no |

Dimensions

| | |
|--------|---------|
| Width | 35 mm |
| Height | 111 mm |
| Depth | 27.7 mm |

Material specifications

| | |
|-----------------|------------------|
| Color (Housing) | black (RAL 9005) |
| Material | PA |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

PCB data

| | |
|-----------------------|---|
| Number of PCB holders | 1 |
|-----------------------|---|

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

UM-BEFE 35 BK (VPE 500) - Base element



2957355

<https://www.phoenixcontact.com/us/products/2957355>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2957355>



UL Recognized

Approval ID: E240868

UM-BEFE 35 BK (VPE 500) - Base element



2957355

<https://www.phoenixcontact.com/us/products/2957355>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190601 |
| ECLASS-15.0 | 27190601 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

UM-BEFE 35 BK (VPE 500) - Base element



2957355

<https://www.phoenixcontact.com/us/products/2957355>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.144 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com