

UM 25-D15SUB/S/FRONT/Q - Termination board



2959599

<https://www.phoenixcontact.com/us/products/2959599>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

VARIOFACE SLIM LINE, with screw connection and D-subminiature pin strip, for assembly at a right angle on NS 35/7.5, 15 positions



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2959599 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C422 |
| Product key | DK21A2 |
| GTIN | 4017918086244 |
| Weight per piece (including packing) | 137.8 g |
| Weight per piece (excluding packing) | 109.07 g |
| Customs tariff number | 85369010 |
| Country of origin | DE |

UM 25-D15SUB/S/FRONT/Q - Termination board



2959599

<https://www.phoenixcontact.com/us/products/2959599>

Technical data

Product properties

| | |
|---------------------|------------------|
| Product type | Interface module |
| Number of positions | 15 |

Insulation characteristics: Air clearances and creepage distances

| | |
|----------------------|-----------------------|
| Insulation | Functional insulation |
| Overvoltage category | II |
| Pollution degree | 2 |

Electrical properties

| | |
|-------------------------|-----------|
| Operating voltage (AC) | ≤ 30 V AC |
| Operating voltage (DC) | ≤ 60 V DC |
| Current (per branch) | ≤ 2.5 A |
| Current (Total current) | ≤ 37.5 A |

Air clearances and creepage distances

| | |
|--------------------------|--------------------|
| Rated insulation voltage | 125 V |
| Rated surge voltage | 1.2 kV (1.2/50 μs) |

Connection data

Connection 1 (control level)

| | |
|----------------------------------|-----------------|
| Connection in acc. with standard | IEC 60807-2 |
| Connection method | D-SUB pin strip |
| Screw thread | UNC 4-40 |
| Number of connections | 1 |
| Number of positions | 15 |
| Insertion/withdrawal cycles | > 500 |
| Pitch | 2.74 mm |

Connection 2 (field level)

| | |
|---|--|
| Connection method | Screw connection |
| Stripping length | 9 mm |
| Screw thread | M3 |
| Number of positions | 16 |
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section rigid (2 conductors with same cross section) | 0.2 mm ² ... 0.75 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| | 0.25 mm ² ... 1.5 mm ² (Ferrule without plastic sleeve) |
| | 0.25 mm ² ... 1.5 mm ² (Ferrule with plastic sleeve) |
| Conductor cross-section flexible (2 conductors with same cross section) | 0.2 mm ² ... 0.75 mm ² |
| | 0.25 mm ² ... 0.34 mm ² (Ferrule without plastic sleeve) |
| Conductor cross-section AWG | 24 ... 14 |

UM 25-D15SUB/S/FRONT/Q - Termination board



2959599

<https://www.phoenixcontact.com/us/products/2959599>

| | |
|-------------------|-------------------|
| Tightening torque | 0.4 Nm ... 0.5 Nm |
| Pitch | 5 mm |

Signaling

| | |
|------------------------|----|
| Status display present | no |
|------------------------|----|

Dimensions

Item dimensions

| | |
|--------|----------|
| Width | 25 mm |
| Height | 147 mm |
| Depth | 46.49 mm |

Material specifications

| | |
|-----------------------------|------------------|
| Color | green (RAL 6021) |
| Housing insulation material | PVC |

Environmental and real-life conditions

Ambient conditions

| | |
|--|------------------|
| Degree of protection (Module) | IP20 |
| Degree of protection (Installation location) | ≥ IP54 |
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |
| Altitude | ≤ 2000 m |

Approvals

UKCA

| | |
|-------------|----------------|
| Certificate | UKCA-compliant |
|-------------|----------------|

Standards and regulations

Air clearances and creepage distances

| | |
|-----------------------|----------------|
| Standards/regulations | EN IEC 60664-1 |
|-----------------------|----------------|

Mounting

| | |
|-------------------|-------------------|
| Mounting type | DIN rail mounting |
| Mounting position | any |

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

UM 25-D15SUB/S/FRONT/Q - Termination board

2959599

<https://www.phoenixcontact.com/us/products/2959599>



Drawings

Circuit diagram



UM 25-D15SUB/S/FRONT/Q - Termination board



2959599

<https://www.phoenixcontact.com/us/products/2959599>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27141152 |
| ECLASS-15.0 | 27141152 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002780 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

UM 25-D15SUB/S/FRONT/Q - Termination board



2959599

<https://www.phoenixcontact.com/us/products/2959599>

Environmental product compliance

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com