

QUINT-UPS/24DC/24DC/40/C1 - Power supply



2909892

<https://www.phoenixcontact.com/us/products/2909892>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Customer-specific uninterruptible power supply with IQ technology for DIN rail mounting; version with customer-specific parameters, input: 24 V DC, output: 24 V DC/40 A, including mounted UTA 107/30 universal DIN rail adapter

Commercial data

Item number	2909892
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	CMUQ4Y
GTIN	4055626437781
Weight per piece (including packing)	877.7 g
Weight per piece (excluding packing)	600 g
Country of origin	CN

Technical data

Input data

DC operation

Input voltage	24 V DC
Nominal input voltage range	24 V DC
Input voltage range	18 V DC ... 30 V DC
Input voltage range DC	18 V DC ... 30 V DC
Voltage type of supply voltage	DC

Output data

Nominal output voltage	24 V DC
Nominal output current (I_N)	40 A
Bridging time	3600 s
Power dissipation	2.8 W (Mains operation)
	13 W (Mains operation)
	3.51 W (Battery operation)
	16.4 W (Battery operation)

Mains operation

Nominal output voltage	24 V DC
Output voltage range	18 V DC ... 30 V DC

Battery operation

Nominal output voltage	24 V DC
Output voltage range	19.2 V DC ... 27.6 V DC ($U_{OUT} = U_{BAT} - 0,5 \text{ V DC}$)

Energy storage

Nominal capacity range	7 Ah ... 200 Ah
------------------------	-----------------

Connection data

Output

Connection method	Pluggable screw connection
-------------------	----------------------------

Product properties

Product type	DC UPS
--------------	--------

Dimensions

Width	47 mm
Height	130 mm
Depth	125 mm

Alternative assembly

Width	123 mm
-------	--------

QUINT-UPS/24DC/24DC/40/C1 - Power supply



2909892

<https://www.phoenixcontact.com/us/products/2909892>

Height	130 mm
Depth	51 mm

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Material specifications

Housing material	Metal
------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
----------------------	------

QUINT-UPS/24DC/24DC/40/C1 - Power supply



2909892

<https://www.phoenixcontact.com/us/products/2909892>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2909892>



EAC

Approval ID: RU S-DE.BL08.W.00764



EAC

Approval ID: RU S-DE.BL08.W.00764



LR

Approval ID: LR22136091TA

QUINT-UPS/24DC/24DC/40/C1 - Power supply



2909892

<https://www.phoenixcontact.com/us/products/2909892>

Classifications

ECLASS

ECLASS-13.0	27040705
ECLASS-15.0	27040705

ETIM

ETIM 10.0	EC000382
-----------	----------

UNSPSC

UNSPSC 21.0	39121000
-------------	----------

2909892

<https://www.phoenixcontact.com/us/products/2909892>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

EF3.1 Climate Change

CO2e kg	24.836 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com