

ME DH36 NS 35 - Spacer



2909895

<https://www.phoenixcontact.com/us/products/2909895>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Spacers, for protection of the input or output contacts for DIN rail NS 35, width [B] 36 mm



Your advantages

- Easy installation

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2909895 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Note | Made to order (non-returnable) |
| Sales key | AC08 |
| Product key | ACHACZ |
| GTIN | 4017918166885 |
| Weight per piece (including packing) | 13.146 g |
| Weight per piece (excluding packing) | 13.146 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

ME DH36 NS 35 - Spacer

2909895

<https://www.phoenixcontact.com/us/products/2909895>



Technical data

Notes

| | |
|---------------|---|
| Assembly note | Please observe the application note in the download area. |
|---------------|---|

Product properties

| | |
|------------------------------|-------------------|
| Product type | Mounting material |
| Housing type | DIN rail housing |
| Housing series | ME |
| Ventilation openings present | no |

Material specifications

| | |
|--|------------------|
| Color (Housing) | green (RAL 6021) |
| Material Housing | PA |
| Flammability rating according to UL 94 | V0 |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Max. IP code to attain | IP20 |
| Ambient temperature (operation) | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C |
| Ambient temperature (assembly) | -5 °C ... 100 °C |
| Relative humidity (storage/transport) | 80 % |

ME DH36 NS 35 - Spacer

2909895

<https://www.phoenixcontact.com/us/products/2909895>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002779 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

ME DH36 NS 35 - Spacer



2909895

<https://www.phoenixcontact.com/us/products/2909895>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com