

# IOA REL 120V DI/1.0A/EX - Relay module



2910157

<https://www.phoenixcontact.com/us/products/2910157>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay module for VIP I/O-Marshalling base elements. For the electrically isolated coupling of 120 V AC field devices to digital inputs. Integrated fuse and fuse failure indication.

## Product description

Relay module for digital input signals for the electrically isolated coupling of 120 V AC field devices. The control path is protected by an integrated replaceable 1 A fuse. If the fuse fails, this is indicated by an LED. The module is installed on a corresponding VIP I/O-Marshalling base element by means of plug-in contact. Installation in zone 2, "ec" type of protection is permitted.

## Your advantages

- Active relay coil indication
- Two-stage progressive release allowing for voltage checks with field-powered devices
- Channel for marking accessories
- Replaceable TE5-style fusing
- 120 V internal marshalling option for connected field device
- Integrated keying reduces possible user error during replacement

## Commercial data

Item number	2910157
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C480
Product key	DK1153
GTIN	4055626447704
Weight per piece (including packing)	68.2 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85364900
Country of origin	US

# IOA REL 120V DI/1.0A/EX - Relay module



2910157

<https://www.phoenixcontact.com/us/products/2910157>

## Technical data

### Product properties

Product type	Relay Module
Product family	VIP I/O-Marshalling
Application	Input function
Operating mode	100% operating factor
Mechanical service life	2x 10 <sup>7</sup> cycles

### Insulation characteristics

Overvoltage category	II
Pollution degree	2

### Data management status

Date of last data management	27.05.2026
------------------------------	------------

### Input data

#### Coil side

Nominal input voltage $U_N$	120 V AC
Input voltage range in reference to $U_N$	0.9 ... 1.1
Typical input current at $U_N$	3 mA
Typical response time	5 ms
Typical release time	4 ms
Protective circuit	Bridge rectifier
Operating voltage display	Yellow LED

### Output data

#### Switching

Contact switching type	1 N/O contact
Type of switch contact	Single contact
Contact material	AgSnO, hard gold-plated
Maximum switching voltage	24 V DC
Limiting continuous current	50 mA
Maximum inrush current	50 mA
Min. switching current	1 mA (at 24 V)
Interrupting rating (ohmic load) max.	1.2 W (at 24 V DC)

### Connection data

#### Control circuits

Connection method	Plug-in connection
-------------------	--------------------

### Ex data

#### Safety data

# IOA REL 120V DI/1.0A/EX - Relay module



2910157

<https://www.phoenixcontact.com/us/products/2910157>

Input voltage $U_i$	120 V AC
Input current $I_i$	3 mA

## Dimensions

### Item dimensions

Width	10.3 mm
Height	64.2 mm
Depth	72.9 mm

## Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Altitude	≤ 2000 m
Permissible humidity (operation)	0 % ... 95 % (non-condensing)

## Approvals

### ATEX

Identification	Ⓜ II 3G Ex ec nC IIC T4 Gc
Certificate	Sira 17ATEX4293X

### IECEX

Identification	Ex ec nC IIC T4 Gc
Certificate	IECEX SIR 17.0078X

### UKEX

Identification	Ⓜ II 3G Ex ec nC IIC T4 Gc
Certificate	PxCIF23UKEX2910153X

### UL, USA/Canada

Identification	Class I, Div. 2, Groups A, B, C, D T4
	Class I, Zone 2, Group IIC T4

### CSA, USA/Canada

Identification	Class I, Div. 2, Groups A, B, C, D T4
	Class I, Zone 2, AEx ec nC IIC T4 Gc
	Ex ec nC IIC T4 Gc

## Standards and regulations

Standards/regulations	IEC 60664
-----------------------	-----------

# IOA REL 120V DI/1.0A/EX - Relay module



2910157

<https://www.phoenixcontact.com/us/products/2910157>

	DIN EN 50178
--	--------------

## Mounting

Mounting type	Plug-in mounting
Assembly note	Plugs into VIP/...BASE...
Mounting position	any

# IOA REL 120V DI/1.0A/EX - Relay module

2910157


<https://www.phoenixcontact.com/us/products/2910157>

## Drawings

Dimensional drawing



Circuit diagram



# IOA REL 120V DI/1.0A/EX - Relay module



2910157

<https://www.phoenixcontact.com/us/products/2910157>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2910157>



**IECEx**

Approval ID: IECEx SIR 17.0078X



**ATEX**

Approval ID: SIRA 17ATEX4293X



**CSA**

Approval ID: 70134758



**CSAus**

Approval ID: 70134758



**cUL Listed**

Approval ID: FILE E 196811



**UL Listed**

Approval ID: FILE E 196811

# IOA REL 120V DI/1.0A/EX - Relay module



2910157

<https://www.phoenixcontact.com/us/products/2910157>

## Classifications

### ECLASS

ECLASS-13.0	27371601
ECLASS-15.0	27371601

### ETIM

ETIM 10.0	EC001437
-----------	----------

### UNSPSC

UNSPSC 21.0	39122300
-------------	----------

# IOA REL 120V DI/1.0A/EX - Relay module



2910157

<https://www.phoenixcontact.com/us/products/2910157>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	5040228c-7d17-4db3-8ddd-b0709142f05c

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)