

PSR-SPP-24UC/ESAM4/8X1/1X2 - Safety relays



2963996

<https://www.phoenixcontact.com/us/products/2963996>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a version with a screw connection

Safety relay for emergency stop and safety door monitoring up to SIL 3 or Cat. 4, PL e in accordance with EN ISO 13849, single- or two-channel operation, 8 enabling current paths, $U_S = 24 \text{ V DC}$, pluggable Push-in terminal block

Your advantages

- Up to Cat. 4/PL e in accordance with EN ISO 13849-1, SIL 3 in accordance with EN IEC 62061, SIL 3 in accordance with IEC 61508
- Manually monitored and automatic activation in a single device
- 1- and 2-channel control
- 8 enabling current paths, 1 signaling current path

Commercial data

Item number	2963996
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN01
Product key	DNA114
GTIN	4017918904814
Weight per piece (including packing)	366 g
Weight per piece (excluding packing)	335.56 g
Customs tariff number	85371098
Country of origin	DE

Technical data

Product properties

Product type	Safety relays
Product family	PSRclassic
Application	Emergency stop Safety door
Control	1 and 2 channel
Mechanical service life	approx. 10^7 cycles
Relay type	Electromechanical relay with force-guided contacts in accordance with IEC/EN 61810-3

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Times

Typical response time	< 140 ms (For U_S manual, monitored start)
	< 120 ms (For U_S autostart)
Typ. starting time with U_S	< 200 ms (with U_S / when controlled via A1)
Typical release time	< 20 ms (At U_S on demand via sensor circuit)
	< 50 ms (At U_S /on demand via A1)
Restart time	< 1 s (Boot time)
Recovery time	500 ms (following demand of the safety function)
	250 ms (Availability time after activating the sensor circuit during manual start)
Start pulse length	min. 500 ms (manual start)

Electrical properties

Maximum power dissipation for nominal condition	31.7 W ($U_S = 26.4$ V, $I_L^2 = 144$ A ² , $P_{Total\ max} = 2.9$ W + 28.8 W)
Nominal operating mode	100% operating factor
Rated insulation voltage	250 V
Rated surge voltage/insulation	See data sheet, section "Insulation coordination".

Supply

Designation	A1/A2
Rated control circuit supply voltage U_S	24 V DC -15 % / +10 %
Rated control supply current I_S	typ. 100 mA (at U_S)
Power consumption at U_S	typ. 2.4 W
Inrush current	typ. 3.5 A (with U_S , $\Delta t = 2$ ms)
Filter time	2 ms (in the event of voltage dips at U_S)
Protective circuit	Serial protection against polarity reversal; Suppressor diode

Input data

Digital: Sensor circuit (S10, S12, S22)

PSR-SPP-24UC/ESAM4/8X1/1X2 - Safety relays



2963996

<https://www.phoenixcontact.com/us/products/2963996>

Description of the input	safety-related
Number of inputs	3
Input voltage range "0" signal	0 V DC ... 5 V DC (S10, S12) S22 open
Input voltage range "1" signal	20.4 V ... 26.4 V (S10, S12) 0 V ... 0 V (S22)
Input current range "0" signal	0 mA ... 2 mA (S10, S12)
Inrush current	max. 150 mA ($\Delta t = 1$ ms, with U_g/I_x at S10) max. 200 mA ($\Delta t = 1$ ms, with U_g/I_x at S12) max. -180 mA ($\Delta t = 1$ ms, with U_g/I_x at S22)
Filter time	No brightness test pulses / high test pulses permitted. max. 1.5 ms (Test pulse width, low test pulses (S10, S12)) Test pulse rate = 5 x test pulse width, low test pulses (S10, S12)
Concurrence	∞
Max. permissible overall conductor resistance	11 Ω
Protective circuit	Suppressor diode
Current consumption	50 mA (S10, S12) -50 mA (S22)

Digital: Start circuit (S34, S35)

Description of the input	non-safety-related
Number of inputs	2
Input voltage range "1" signal	20.4 V ... 26.4 V
Inrush current	< 10 mA
Filter time	No test pulses permitted
Max. permissible overall conductor resistance	50 Ω
Protective circuit	Suppressor diode
Current consumption	0 mA (S34) 1 mA (S35)

Output data

Relay: Enabling current paths (13/14, 23/24, 33/34, 43/44, 53/54, 63/64, 73/74, 83/84)

Output description	2 N/O contacts each in series, safety-related, floating
Number of outputs	8
Contact switching type	8 enabling current paths
Contact material	AgSnO ₂
Switching voltage	min. 5 V AC/DC max. 250 V AC/DC
Switching power	min. 50 mW
Inrush current	min. 10 mA AC/DC max. 6 A
Switching capacity	3 A (AC15) 5 A (DC13)
Limiting continuous current	6 A (observe derating)

PSR-SPP-24UC/ESAM4/8X1/1X2 - Safety relays



2963996

<https://www.phoenixcontact.com/us/products/2963996>

Sq. Total current	144 A ² (observe derating)
Switching frequency	max. 0.5 Hz
Mechanical service life	10x 10 ⁶ cycles
Output fuse	10 A gL/gG
	6 A gL/gG (Low demand)

Relay: Signaling current path (91/92)

Output description	2 N/C contacts parallel, non-safety-related, floating
Number of outputs	1
Contact switching type	1 signaling current path
Contact material	AgSnO ₂
Switching voltage	min. 5 V AC/DC
	max. 250 V AC/DC
Switching power	min. 50 mW
Inrush current	min. 10 mA
	max. 6 A
Switching capacity	1.5 A (AC15)
	5 A (DC13)
Limiting continuous current	6 A
Sq. Total current	36 A ²
Switching frequency	max. 0.5 Hz
Mechanical service life	10x 10 ⁶ cycles
Output fuse	6 A gL/gG
	4 A gL/gG (Low demand)

Connection data

Connection technology

pluggable	yes
-----------	-----

Conductor connection

Connection method	Push-in connection
Conductor cross-section rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm ² ... 1.5 mm ² (only together with CRIMPFOX 6)
Conductor cross-section, flexible, with ferrule, without plastic sleeve	0.25 mm ² ... 1.5 mm ² (only together with CRIMPFOX 6)
Conductor cross-section AWG	24 ... 16
Stripping length	8 mm

Signaling

Status display	2 x LED (green)
Operating voltage display	1 x LED (green)

Dimensions

Width	45 mm
-------	-------

PSR-SPP-24UC/ESAM4/8X1/1X2 - Safety relays



2963996

<https://www.phoenixcontact.com/us/products/2963996>

Height	112 mm
Depth	114.5 mm

Material specifications

Color (Housing)	yellow (RAL 1018)
Housing material	PA

Characteristics

Safety data

Stop category (EN 60204-1)	0
----------------------------	---

Safety data: EN ISO 13849

Performance level (PL)	e (3 A DC13; 3 A AC15; 8760 switching cycles/year)
------------------------	--

Safety data: IEC 61508 - High demand

Safety Integrity Level (SIL)	3
------------------------------	---

Safety data: IEC 61508 - Low demand

Safety Integrity Level (SIL)	3
------------------------------	---

Safety data: EN IEC 62061

Safety Integrity Level (SIL)	3
------------------------------	---

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Min. degree of protection of inst. location	IP54
Ambient temperature (operation)	-20 °C ... 55 °C (observe derating)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Maximum altitude	≤ 2000 m (Above sea level)
Max. permissible humidity (storage/transport)	75 % (on average, 85% infrequently, non-condensing)
Max. permissible relative humidity (operation)	75 % (on average, 85% infrequently, non-condensing)
Shock	15g (contact interruptions < 100 µs possible)
Vibration (operation)	10 Hz ... 150 Hz, 2g

Approvals

CE

Identification	CE-compliant
----------------	--------------

Mounting

Mounting type	DIN rail mounting
Assembly note	See derating curve
Mounting position	vertical or horizontal

PSR-SPP-24UC/ESAM4/8X1/1X2 - Safety relays




2963996

<https://www.phoenixcontact.com/us/products/2963996>

Drawings

Circuit diagram



Block diagram

PSR-SPP-24UC/ESAM4/8X1/1X2 - Safety relays



2963996

<https://www.phoenixcontact.com/us/products/2963996>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2963996>



cULus Listed

Approval ID: E140324



Functional Safety

Approval ID: 01/205/5363.04/24

PSR-SPP-24UC/ESAM4/8X1/1X2 - Safety relays



2963996

<https://www.phoenixcontact.com/us/products/2963996>

Classifications

ECLASS

ECLASS-13.0	27371819
ECLASS-15.0	27371819
ECLASS-15.0 ASSET	27250101

ETIM

ETIM 10.0	EC001449
-----------	----------

UNSPSC

UNSPSC 21.0	39122200
-------------	----------

PSR-SPP-24UC/ESAM4/8X1/1X2 - Safety relays



2963996

<https://www.phoenixcontact.com/us/products/2963996>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	01173c64-6e5f-4621-878f-998922d82156

EF3.1 Climate Change

CO2e kg	7.82 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com