

# LCD TOUCH 5015 D IP VESA - Monitor



2913302

<https://www.phoenixcontact.com/us/products/2913302>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

LCD monitor with touch screen, 15" display, with digital image transmission, IP65 housing



## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 2913302                        |
| Packing unit                         | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | DR12                           |
| Product key                          | DRBBAD                         |
| GTIN                                 | 4046356324632                  |
| Weight per piece (including packing) | 4.44 kg                        |
| Weight per piece (excluding packing) | 4.44 kg                        |
| Customs tariff number                | 85299020                       |
| Country of origin                    | DE                             |

# LCD TOUCH 5015 D IP VESA - Monitor



2913302

<https://www.phoenixcontact.com/us/products/2913302>

## Technical data

### Product properties

|              |         |
|--------------|---------|
| Product type | Monitor |
|--------------|---------|

### Computer data

|                     |                          |
|---------------------|--------------------------|
| Processor           | without processor        |
| Operating system    | without operating system |
| RAM                 | without RAM              |
| Data storage system | without data storage     |
| Cooling             | passive                  |
| Slots               | without slots            |
| Optical drive       | without drive            |

### Display

|                       |  |
|-----------------------|--|
| Display type          | 38.1 cm / 15"-TFT                          |
| Screen resolution     | 1024 x 768 Pixel(s) (XGA)                  |
| Touch technology      | Resistive industrial touch screen          |
| Display lighting type | CCFL                                       |
| Brightness            | 330 cd/m <sup>2</sup> typical (adjustable) |

### System properties

|               |                       |
|---------------|-----------------------|
| User software | without user software |
|---------------|-----------------------|

### Electrical properties

#### Supply

|                   |          |
|-------------------|----------|
| Power supply unit | 230 V AC |
|-------------------|----------|

### Interfaces

|            |                 |
|------------|-----------------|
| Interfaces | 1x DVI-D        |
| Network    | without network |

### Dimensions

|        |        |
|--------|--------|
| Width  | 395 mm |
| Height | 292 mm |
| Depth  | 65 mm  |

#### External dimensions

|                        |                         |
|------------------------|-------------------------|
| Width / Height / Depth | 395 mm / 292 mm / 65 mm |
|------------------------|-------------------------|

### Environmental and real-life conditions

#### Ambient conditions

|                                 |                |
|---------------------------------|----------------|
| Degree of protection            | IP65           |
| Ambient temperature (operation) | 5 °C ... 45 °C |

# LCD TOUCH 5015 D IP VESA - Monitor



2913302

<https://www.phoenixcontact.com/us/products/2913302>

|  |                  |
|--|------------------|
| Ambient temperature (storage/transport)  | -20 °C ... 60 °C |
| Permissible humidity (operation)         | 10 % ... 85 %    |
| Permissible humidity (storage/transport) | 10 % ... 85 %    |

## Mounting

|               |   |
|---------------|---|
| Mounting type | LCD monitor for mounting in the front panel |
|---------------|---|

# LCD TOUCH 5015 D IP VESA - Monitor



2913302

<https://www.phoenixcontact.com/us/products/2913302>

## Environmental product compliance

### EU REACH SVHC

| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)