

EMG 25-LG/G - Electronics housing

2914343

<https://www.phoenixcontact.com/us/products/2914343>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a version of the product

Electronics housing ,Component housing, without vents, Lower and upper part, closed, cross connection: without bus connector, color: green, width: 25 mm, height: 47.5 mm, number of positions cross connector: not relevant

Commercial data

Item number	2914343
Packing unit	10 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	ACHCBA
GTIN	4017918954369
Weight per piece (including packing)	29.07 g
Weight per piece (excluding packing)	29.07 g
Country of origin	DE

EMG 25-LG/G - Electronics housing



2914343

<https://www.phoenixcontact.com/us/products/2914343>

Technical data

Product properties

Product type	Complete housing
Housing type	Component housing
Housing series	EMG
Product family	EMG

Dimensions

Width	25 mm
Installed height	47.5 mm
Depth	75 mm

Material specifications

Color	green
Flammability rating according to UL 94	V0
Housing material	Polycarbonate, glass-fiber-reinforced

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 125 °C

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

EMG 25-LG/G - Electronics housing

2914343

<https://www.phoenixcontact.com/us/products/2914343>



Classifications

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

EMG 25-LG/G - Electronics housing



2914343

<https://www.phoenixcontact.com/us/products/2914343>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com