

# IEG-PS-230AC/S0 - Solid-state relay module



2964665

<https://www.phoenixcontact.com/us/products/2964665>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power supply unit, for passive S0 meter interfaces, input: 230 V AC, output: S0

The figure shows the version ST-PS 4-100AC/S0

## Commercial data

Item number	2964665
Packing unit	10 pc
Minimum order quantity	1 pc
Product key	DK66M3
GTIN	4017918139193
Weight per piece (including packing)	101.18 g
Weight per piece (excluding packing)	101.18 g
Country of origin	DE

# IEG-PS-230AC/S0 - Solid-state relay module



2964665

<https://www.phoenixcontact.com/us/products/2964665>

## Technical data

### Input data

Input voltage	230 V AC $\pm$ 10 %
---------------	---------------------

### Output data

Nominal output voltage	max. 27 V DC (in acc. with DIN 43864)
Output current $I_{\max}$	27 mA (in acc. with DIN 43864)

### Connection data

#### Input

Connection method	Screw connection
Conductor cross-section, rigid min.	0.2 mm <sup>2</sup>
Conductor cross-section, rigid max.	4 mm <sup>2</sup>
Conductor cross-section flexible min.	0.2 mm <sup>2</sup>
Conductor cross-section flexible max.	4 mm <sup>2</sup>
Conductor cross-section AWG min.	24
Conductor cross-section AWG max.	12
Stripping length	8 mm
Screw thread	M3

#### Output

Connection method	Screw connection
Conductor cross-section, rigid min.	0.2 mm <sup>2</sup>
Conductor cross-section, rigid max.	4 mm <sup>2</sup>
Conductor cross-section flexible min.	0.2 mm <sup>2</sup>
Conductor cross-section flexible max.	4 mm <sup>2</sup>
Conductor cross-section AWG min.	24
Conductor cross-section AWG max.	12
Stripping length	8 mm

### Electrical properties

Rated insulation voltage	300 V (acc. to EN 50178)
--------------------------	--------------------------

### Product properties

Product type	Power supply
--------------	--------------

#### Insulation characteristics

Overvoltage category	III, basic insulation (as per EN 50178)
Pollution degree	2 (in accordance with EN 50178)

### Dimensions

Width	27 mm
Height	74 mm

# IEG-PS-230AC/S0 - Solid-state relay module



2964665

<https://www.phoenixcontact.com/us/products/2964665>

Depth	79 mm
Horizontal pitch	1.5 Div.

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 55 °C
Ambient temperature (storage/transport)	-20 °C ... 60 °C

## Approvals

### Conformity/Approvals

Conformance	CE-compliant
-------------	--------------

## EMC data

Electromagnetic compatibility	Conformance with EMC directive
Low Voltage Directive	Conformance with Low Voltage Directive
Noise immunity	EN 61000-6-2

### Noise emission

Standards/regulations	EN 61000-6-4
-----------------------	--------------

# IEG-PS-230AC/S0 - Solid-state relay module




2964665

<https://www.phoenixcontact.com/us/products/2964665>

## Drawings

### Circuit diagram



# IEG-PS-230AC/S0 - Solid-state relay module



2964665

<https://www.phoenixcontact.com/us/products/2964665>

## Environmental product compliance

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)