

CT 10-2/2-GS/3E-110AC - Magazine



2920829

<https://www.phoenixcontact.com/us/products/2920829>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



LSA-PLUS coarse protection magazine for 10 double conductors, equipped with 10 three-electrode gas-filled surge arresters.

Your advantages

- Space-saving due to compact design
- Flexible fields of application with modular protective plug
- Can be used in LSA-PLUS disconnect and control strips or CT-TERMIBLOCK via adapted connection technology

Commercial data

Item number	2920829
Packing unit	10 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	CL3212
GTIN	4046356181822
Weight per piece (including packing)	81.51 g
Weight per piece (excluding packing)	73 g
Country of origin	DE

Technical data

Product properties

Product type	Surge protection for information technology
Product family	COMTRAB
IEC test classification	C2
	C3
	D1
Type	LSA-PLUS module
Number of positions	20
Surge protection fault message	none
Wire pairs per module	10

Insulation characteristics

Overvoltage category	III
Pollution degree	2


Electrical properties

Nominal voltage U_N	110 V AC
-----------------------	----------

Connection data

Connection method	can be plugged into COMTRAB-TERMIBLOCK and LSA-PLUS disconnect and switching strips
-------------------	---

Dimensions

Dimensional drawing	
Width	113.3 mm
Height	22.5 mm
Depth	41.35 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V-0
Housing material	PBT

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Protective circuit

Direction of action	Line-Line & Line-Earth Ground
Nominal voltage U_N	110 V AC
Maximum continuous operating voltage U_C	60 V DC
	130 V AC
Rated current	1.5 A AC (per path)
	150 mA DC (per path)
Operating effective current I_C at U_C	$\leq 1 \mu\text{A}$ (per path)
Protective conductor current I_{PE}	$\leq 20 \mu\text{A}$
Nominal discharge current I_n (8/20) μs (line-ground)	5 kA
Pulse discharge current I_{imp} (10/350) μs (line-earth)	2.5 kA
Nominal pulse current I_{an} (10/1000) μs (line-earth)	100 A
Output voltage limitation at 1 kV/ μs (line-earth) spike	$\leq 500 \text{ V}$
Response time t_A (line-earth)	$\leq 100 \text{ ns}$
Capacity (Core-Earth)	typ. 5 pF
Resistance per path	$\leq 10 \text{ m}\Omega$
Surge protection fault message	none
Impulse durability (line-earth)	C2 - 10 kV / 5 kA
	C3 - 100 A
	D1 - 2.5 kA
Alternating current carrying capacity (line-earth)	10 A - 1 s

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 75 °C
Altitude	$\leq 2000 \text{ mm}$ (amsl)

Standards and regulations

Air clearances and creepage distances


Standards/regulations	VDE 0110-1 / IEC 60664-1
Standards/specifications	IEC 61643-21
Note	2000 + corrigendum 2001 + A1:2008, modified + A2:2012
Standards/specifications	EN 61643-21
Note	2001 + A1:2009 + A2:2013

Mounting


Mounting type	On CT-TERMIBLOCK and LSA-PLUS disconnect strip
---------------	--

Drawings

Dimensional drawing



Circuit diagram



2920829

<https://www.phoenixcontact.com/us/products/2920829>

Classifications

ECLASS

ECLASS-13.0	27171503
ECLASS-15.0	27171503

ETIM

ETIM 10.0	EC001466
-----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

2920829

<https://www.phoenixcontact.com/us/products/2920829>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com