

MACX MCR-EX-SL-SD-21-60-LP-SP - Solenoid driver



2924100

<https://www.phoenixcontact.com/us/products/2924100>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ex i solenoid driver. For the intrinsically safe control of Ex i solenoid valves, alarm modules or LEDs installed in the Ex area. Current limitation at 58 mA. For gases up to Group IIB, loop-powered, electrical isolation, SIL 3. Push-in connection.

Your advantages

- Mechanically compatible with the DIN rail connector
- Various output characteristic curves compatible with standard solenoid valves
- Loop-powered: the required power is supplied via the control signal on the input side.
- Installation in zone 2, protection type "n" (EN 60079-15) permitted
- Up to SIL 3 in accordance with IEC 61508
- 2-way electrical isolation
- Input: 19.2 V DC ... 30 V DC
- Output [Ex ia] IIB

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2924100 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C430 |
| Product key | DK1214 |
| GTIN | 4046356338523 |
| Weight per piece (including packing) | 160.433 g |
| Weight per piece (excluding packing) | 155 g |
| Customs tariff number | 85437090 |
| Country of origin | DE |

2924100

<https://www.phoenixcontact.com/us/products/2924100>

Technical data

Product properties

| | |
|------------------|---|
| Product type | Solenoid driver |
| Product family | MACX Analog |
| No. of channels | 1 |
| Compatible valve | ASCO Coil 302 (12 V) ASCO Coil 302 (24 V) Bürkert Coil AC 10 standard Bürkert Coil AC 10 high resistance FESTO Coil MFH-...IA-SA-EX GBXE022AIAD03 FESTO Coil (J)MFH-...BIA-SA-EX GBXE022AIAD03 Norgren Herion Coil 2050 Norgren Herion Coil 2051 Norgren Herion Coil 2052 Norgren Herion Coil 2053 Parker Coil VZ95 482160.01 EEx ia IIB T6 |
| Note | This is an extract of possible combinations of valves and solenoid drivers. |

Electrical properties

| | |
|---|-----------------|
| Electrical isolation | 2-way isolation |
| Electrical isolation between input and output | yes |
| Maximum temperature coefficient | 0.01 %/K |

Electrical isolation

| | |
|----------------------|-------------------------|
| Test voltage | 2.5 kV AC (50 Hz, 60 s) |
| Overvoltage category | II |
| Pollution degree | 2 |

Electrical isolation Output/input IEC/EN 60079-11

| | |
|--------------------------|---------------------|
| Standards/regulations | IEC/EN 60079-11 |
| Rated insulation voltage | 375 V _{PP} |

Electrical isolation Output/input IEC/EN 61010-1

| | |
|--------------------------|----------------------|
| Standards/regulations | IEC/EN 61010-1 |
| Rated insulation voltage | 300 V _{rms} |
| Insulation | Safe isolation |

Supply

| | |
|----------------------|--|
| Supply voltage range | loop-powered, no external supply necessary |
| Power dissipation | < 1.325 W |

Input data

Signal: Voltage

2924100

<https://www.phoenixcontact.com/us/products/2924100>

| | |
|---------------------------|--|
| Number of inputs | 1 |
| Voltage input signal | 19.2 V DC ... 30 V DC (24 V DC, -20 % ... +25 %) |
| Max. current input signal | 95 mA ($U_e = 24$ V DC) |

Output data

Signal: Voltage

| | |
|----------------------|--------------------------|
| Output description | intrinsically safe |
| Number of outputs | 1 |
| Output voltage | ≥ 12.9 V DC (58 mA) |
| Current limitation | > 58 mA |
| Response time | < 20 ms |
| Open-circuit voltage | > 21.9 V DC |
| Short-circuit-proof | yes |

Connection data

| | |
|---|---|
| Connection method | Push-in connection |
| Stripping length | 10 mm |
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible (2 conductors with same cross section) | 0.25 mm ² ... 0.34 mm ² (TWIN ferrule without plastic sleeve) |
| | 0.5 mm ² ... 1.5 mm ² (TWIN ferrule with plastic sleeve) |
| Conductor cross-section AWG | 24 ... 14 |
| | 24 ... 22 (TWIN ferrule without plastic sleeve) |
| | 20 ... 16 (TWIN ferrule with plastic sleeve) |

Ex data

| | |
|-----------------------|----------|
| Ex installation (EPL) | Gc |
| | Div. 2 |
| Ex i circuits (EPL) | [Ga] |
| | [Da] |
| | [Ma] |
| | [Div. 1] |

Safety data

| | |
|--------------------------------------|----------------|
| Input power P_i | negligible |
| Max. internal inductance L_i | negligible |
| Max. internal capacitance C_i | negligible |
| Max. output voltage U_o | 25.1 V |
| Max. output current I_o | 188 mA |
| Max. output power P_o | 1.18 W |
| Maximum internal resistance R_i | 133.4 Ω |
| Safety-related maximum voltage U_m | 253 V AC |
| | 125 V DC |

MACX MCR-EX-SL-SD-21-60-LP-SP - Solenoid driver



2924100


<https://www.phoenixcontact.com/us/products/2924100>

| | |
|--|---|
| I/A/I (simple circuit): Max. external inductivity L_o / Max. external capacitance C_o | 8 mH / 2.93 μ F |
| IIB/IIIC (simple circuit): Max. external inductivity L_o / Max. external capacitance C_o | 4 mH / 0.83 μ F |
| I/A/I (mixed circuit): Max. external inductivity L_o / Max. external capacitance C_o | 5 mH / 510 nF, 1 mH / 560 nF, 0.5 mH / 660 nF, 0.1 mH / 1000 nF |
| IIB/IIIC (mixed circuit): Max. external inductivity L_o / Max. external capacitance C_o | 2 mH / 300 nF, 0.15 mH / 500 nF |

Signaling

| | |
|----------------|--|
| Status display | Yellow LED (switching state / status, lights up when output circuit is active) |
|----------------|--|

Dimensions

| | |
|---------------------|---|
| Dimensional drawing |  |
| Width | 12.5 mm |
| Height | 107.9 mm |
| Depth | 113.7 mm |
| Depth NS 35/7,5 | 114.5 mm (Snapped onto DIN rail NS 35/7,5 in accordance with EN 60715) |

Material specifications

| | |
|--|-----------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 (Housing) | V0 (Housing) |
| Housing material | PA 6.6-FR |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Degree of protection | IP20 (not assessed by UL) |
| Ambient temperature (operation) | -40 °C ... 60 °C (Any mounting position) -40 °C ... 70 °C (Derating) |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Permissible humidity (operation) | 10 % ... 95 % (non-condensing) |

Altitude range (≤ 2000 m)

| | |
|--------------------------------------|---|
| Altitude | ≤ 2000 m (The technical data refers to altitudes ≤ 2000 m above mean sea level. For altitudes >2000 m above mean sea level, refer to the data sheet.) |
| Ambient temperature (operation) | -40 °C ... 70 °C |
| Safety-related maximum voltage U_m | 253 V AC 125 V DC |

MACX MCR-EX-SL-SD-21-60-LP-SP - Solenoid driver



2924100

<https://www.phoenixcontact.com/us/products/2924100>

| | |
|--------------------------|--|
| Rated insulation voltage | 375 V _{PP} (IEC/EN 60079-11) |
| | 265 V (U _{Isolation rated "ec"}) |

Altitude range (≤ 3000 m)

| | |
|---|--|
| Height range | > 2000 m ... 3000 m |
| Ambient temperature (operation) | -40 °C ... 63 °C |
| Safety-related maximum voltage U _m | 190 V AC |
| | 110 V DC |
| Rated insulation voltage | 190 V (IEC/EN 60079-11) |
| | 190 V (U _{Isolation rated "ec"}) |

Altitude range (≤ 4000 m)

| | |
|---|---|
| Height range | > 3000 m ... 4000 m |
| Ambient temperature (operation) | -40 °C ... 56 °C |
| Safety-related maximum voltage U _m | 60 V |
| Rated insulation voltage | 60 V (IEC/EN 60079-11) |
| | 60 V (U _{Isolation rated "ec"}) |

Altitude range (≤ 5000 m)

| | |
|---|---|
| Height range | > 4000 m ... 5000 m |
| Ambient temperature (operation) | -40 °C ... 49 °C |
| Safety-related maximum voltage U _m | 60 V |
| Rated insulation voltage | 60 V (IEC/EN 60079-11) |
| | 60 V (U _{Isolation rated "ec"}) |

Approvals

CE

| | |
|-------------|--------------|
| Certificate | CE-compliant |
| Note | and EN 61326 |

ATEX

| | |
|----------------|--|
| Identification | ⊕ I (M1) [Ex ia Ma] I |
| | ⊕ II (1) G [Ex ia Ga] IIB |
| | ⊕ II (1) D [Ex ia Da] IIIC |
| | ⊕ II 3 (1) G Ex ec [ia IIB Ga] IIC T4 Gc |
| Certificate | IBExU 07 ATEX 1133X |

IECEX

| | |
|----------------|-----------------------------|
| Identification | [Ex ia Ma] I |
| | [Ex ia Ga] IIB |
| | [Ex ia Da] IIIC |
| | Ex ec [ia IIB Ga] IIC T4 Gc |
| Certificate | IECEX IBE 08.0002X |

CCC / China-Ex

| | |
|--|----------------|
| | [Ex ia Ga] IIB |
|--|----------------|

MACX MCR-EX-SL-SD-21-60-LP-SP - Solenoid driver



2924100

<https://www.phoenixcontact.com/us/products/2924100>

| | |
|----------------|-----------------------------|
| Identification | [Ex ia Da] IIC |
| | Ex ec [ia IIB Ga] IIC T4 Gc |
| Certificate | 2022122316115980 |

UL, USA/Canada

| | |
|----------------|--|
| Identification | UL 61010 Listed |
| | Class I, Div. 2, Groups A, B, C, D T4 |
| | Class I, Div. 2, Groups IIC, IIB, IIA T4 |
| | Associated apparatus for use in Class I, Division 1, Groups C,D |
| | Associated apparatus for use in Class II, Div.1 Groups E,F,G |
| | Associated apparatus for use in Class III, Division 1 |
| Certificate | Associated apparatus for use in Class I, Zone 0,1,2, Groups IIB, IIA |
| | Ⓢ.Ⓢ. C.D.-No 83104549 |

Shipbuilding approval

| | |
|-------------|-------------------|
| Certificate | DNV GL TAA000020C |
|-------------|-------------------|

Safety Integrity Level (SIL, IEC 61508)

| | |
|----------------|---|
| Identification | 3 |
|----------------|---|

INMETRO

| | |
|----------------|-----------------------------|
| Identification | [Ex ia Ma] I |
| | [Ex ia Ga] IIB |
| | [Ex ia Da] IIC |
| | Ex ec [ia IIB Ga] IIC T4 Gc |
| Certificate | DNV 18.0115 X |

Shipbuilding data

| | |
|-------------|---|
| Temperature | B |
| Humidity | B |
| Vibration | A |
| EMC | A |
| Enclosure | Required protection according to the Rules shall be provided upon installation on board |

EMC data

| | |
|-------------------------------|--------------------------------|
| Electromagnetic compatibility | Conformance with EMC directive |
| Noise immunity | EN 61000-6-2 |

Noise emission

| | |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

Standards and regulations

| | |
|----------------------|-----------------|
| Electrical isolation | 2-way isolation |
|----------------------|-----------------|

GB Standard

| | |
|--|-------------|
| | GB/T 3836.1 |
|--|-------------|

MACX MCR-EX-SL-SD-21-60-LP-SP - Solenoid driver



2924100

<https://www.phoenixcontact.com/us/products/2924100>

| | |
|-----------------------|-------------|
| Standards/regulations | GB/T 3836.3 |
| | GB/T 3836.4 |

Mounting


| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

Drawings

Dimensional drawing



Diagram



Block diagram



2924100

<https://www.phoenixcontact.com/us/products/2924100>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2924100>

DNV

Approval ID: TAA000020C



UL Listed

Approval ID: E330267



cUL Listed

Approval ID: E330267

Functional Safety

Approval ID: 16/04-017 R025 V1R1



IECEx

Approval ID: IECEx IBE 08.0002X



CCC

Approval ID: 2022122316115980



cUL Listed

Approval ID: E199827



UL Listed

Approval ID: E199827



ATEX

Approval ID: IBExU 07 ATEX 1133 X

INMETRO

Approval ID: DNV 18.0115 X

INMETRO

Approval ID: DNV 18.0115 X

MACX MCR-EX-SL-SD-21-60-LP-SP - Solenoid driver



2924100

<https://www.phoenixcontact.com/us/products/2924100>



IECEx

Approval ID: IECEx IBE 08.0002X



ATEX

Approval ID: IBExU 07 ATEX 1133 X

2924100

<https://www.phoenixcontact.com/us/products/2924100>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27210120 |
| ECLASS-15.0 | 27210120 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002653 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121000 |
|-------------|----------|

2924100

<https://www.phoenixcontact.com/us/products/2924100>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| | 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7) |
| SCIP | dcdae1ed-7b65-4b50-a476-f39582934baa |

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com