

PLC-ESK GY - Power terminal block



2966508

<https://www.phoenixcontact.com/us/products/2966508>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Power terminal block, for the input of up to four potentials, for mounting on NS 35/7.5



Commercial data

Item number	2966508
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	C461
Product key	DK62Z3
GTIN	4017918147600
Weight per piece (including packing)	37.97 g
Weight per piece (excluding packing)	34.506 g
Customs tariff number	85369010
Country of origin	DE

PLC-ESK GY - Power terminal block



2966508

<https://www.phoenixcontact.com/us/products/2966508>

Technical data

Product properties

Product type	Feed-in module
Product family	PLC-INTERFACE

Electrical properties

Operating voltage (AC/DC)	250 V AC/DC (The separating plate PLC-ATP should be installed for voltages larger than 250 V (L1, L2, L3) between identical terminal blocks in adjacent modules. Potential bridging is then carried out with FBST 8-PLC... or ...FBST 500...)
Current (Total current)	32 A

Connection data

Connection method	Screw connection
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 4 mm ²
Conductor cross-section AWG	24 ... 10

Dimensions

Item dimensions

Width	9 mm
Height	80 mm
Depth	85.7 mm

Material specifications

Color	gray (RAL 7042)
-------	-----------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C

Approvals

CE

Certificate	CE-compliant
-------------	--------------

UKCA

Certificate	UKCA-compliant
-------------	----------------

Shipbuilding approval

Certificate	TAE0000196
-------------	------------

Corrosive gas test

Identification	ISA-S71.04. G3 Harsh Group
----------------	----------------------------

PLC-ESK GY - Power terminal block



2966508

<https://www.phoenixcontact.com/us/products/2966508>

	EN 60068-2-60
--	---------------

Shipbuilding data

Temperature	D
Humidity	A
Vibration	B/C
EMC	B
Enclosure	Required protection according to the Rules shall be provided upon installation on board

EMC data

Electromagnetic compatibility	Conformance with EMC directive
Low Voltage Directive	Conformance with Low Voltage Directive

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

PLC-ESK GY - Power terminal block



2966508

<https://www.phoenixcontact.com/us/products/2966508>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2966508>



cUL Recognized
Approval ID: E238705



UL Recognized
Approval ID: E238705



EAC
Approval ID: RU C-DE.A*30.B.01742



cULus Listed
Approval ID: E140324



cULus Listed
Approval ID: E140324



cULus Listed
Approval ID: E140324

DNV

Approval ID: TAE0000196

PLC-ESK GY - Power terminal block



2966508

<https://www.phoenixcontact.com/us/products/2966508>

Classifications

ECLASS

ECLASS-13.0	27371692
ECLASS-15.0	27371692

ETIM

ETIM 10.0	EC002586
-----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

PLC-ESK GY - Power terminal block



2966508

<https://www.phoenixcontact.com/us/products/2966508>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.288 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com