

# MACX MCR-SL-RPSSI-2I-SP - Repeater power supply



2924838

<https://www.phoenixcontact.com/us/products/2924838>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Measuring transducer repeater power supply and input signal conditioner transmits supplied or active 0 mA/4 mA ... 20 mA electrically isolated signals from the field to two loads. number of channels: 1, HART transparency, Standard configuration, 3-way isolation, Safety Integrity Level (SIL, IEC 61508): 2, Performance Level (ISO 13849): d / KAT 2, Systematic Capability: 3, Push-in connection

## Your advantages

- Power supply possible via DIN rail connector
- Up to SIL 2 in accordance with EN 61508
- Installation in zone 2, protection type "n" (EN 60079-15) permitted
- Two electrically isolated 0/4 mA ... 20 mA (active) outputs
- Bidirectional transmission of digital HART communication signals (both outputs)
- Plug-in screw or spring-cage connection technology (Push-in technology), with integrated sockets for HART communicators
- Input: 0/4 mA ... 20 mA (powered or not powered)
- 4-way electrical isolation

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2924838       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | C402          |
| Product key                          | DK1111        |
| GTIN                                 | 4046356572057 |
| Weight per piece (including packing) | 230.7 g       |
| Weight per piece (excluding packing) | 153 g         |
| Customs tariff number                | 85437090      |
| Country of origin                    | DE            |

## Technical data

### Product properties

|                 |                       |
|-----------------|-----------------------|
| Product type    | Repeater power supply |
| Product family  | MACX Analog           |
| No. of channels | 1                     |

### Electrical properties

|   |   |
|---|---|
| Electrical isolation                            | 3-way isolation                           |
| Electrical isolation between input and output   | yes                                       |
| Maximum power dissipation for nominal condition | 1.45 W (24 V DC / 20 mA)                  |
| Signal transmission behavior                    | In = Out                                  |
| Step response (10-90%)                          | 1.3 ms (for jump 4 mA ... 20 mA, typical) |
| Maximum temperature coefficient                 | < 0.01 %/K                                |
| Maximum transmission error                      | < 0.1 % (of final value 20 mA)            |
| Transmission error, typical                     | < 0.05 % (of final value 20 mA)           |

#### Electrical isolation

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Pollution degree     | 2  |

#### Electrical isolation Input/output/power supply IEC/EN 61010-1

|                          |                         |
|--------------------------|-------------------------|
| Standards/regulations    | IEC/EN 61010-1          |
| Rated insulation voltage | 300 V <sub>rms</sub>    |
| Test voltage             | 2.5 kV AC (50 Hz, 60 s) |
| Insulation               | Safe isolation          |

#### Electrical isolation Output 1/output 2

|              |                         |
|--------------|-------------------------|
| Test voltage | 1.5 kV AC (50 Hz, 60 s) |
|--------------|-------------------------|

#### Supply

|                          |                                 |
|--------------------------|---------------------------------|
| Designation              | Repeater power supply operation |
| Nominal supply voltage   | 24 V DC -20 % ... +25 %         |
| Supply voltage range     | 19.2 V DC ... 30 V DC           |
| Max. current consumption | < 75 mA (24 V DC / 20 mA)       |
| Power dissipation        | < 1.45 W (24 V DC / 20 mA)      |
| Power consumption        | ≤ 1.8 W                         |

#### Supply

|                          |                              |
|--------------------------|------------------------------|
| Designation              | Signal conditioner operation |
| Nominal supply voltage   | 24 V DC -20 % ... +25 %      |
| Supply voltage range     | 19.2 V DC ... 30 V DC        |
| Max. current consumption | < 46 mA (24 V DC / 20 mA)    |
| Power dissipation        | < 1.2 W (24 V DC / 20 mA)    |

## Input data

# MACX MCR-SL-RPSSI-2I-SP - Repeater power supply



2924838

<https://www.phoenixcontact.com/us/products/2924838>

Signal: Repeater power supply operation

|                                 |  |
|---------------------------------|--|
| Description of the input        | Repeater power supply operation                              |
| Number of inputs                | 1  |
| Current input signal            | 4 mA ... 20 mA   |
| Transmitter supply voltage      | > 21.5 V (20 mA)<br>> 21 V (23 mA)                           |
| Underload/overload signal range | 0 mA ... 24 mA (Extended transmission range for diagnostics) |

Signal: Signal conditioner operation

|                                 |  |
|---------------------------------|--|
| Description of the input        | Signal conditioner operation                                 |
| Current input signal            | 0 mA ... 20 mA<br>4 mA ... 20 mA                             |
| Voltage drop                    | < 3.9 V (in input isolating amplifier operation)             |
| Underload/overload signal range | 0 mA ... 24 mA (Extended transmission range for diagnostics) |

## Output data

Signal: Repeater power supply operation

|  |   |
|--|---|
| Output description                       | Repeater power supply operation   |
| Number of outputs                        | 2   |
| Current output signal                    | 4 mA ... 20 mA (active)<br>0 mA ... 20 mA                                     |
| Load/output load current output          | < 450 Ω (20 mA)<br>< 380 Ω (23 mA)  |
| Output ripple                            | < 20 mV <sub>rms</sub>  |
| Output behavior in the event of an error | 0 mA (Cable break in the input)<br>≥ 23 mA (Cable short-circuit in the input) |
| Underload/overload signal range          | 0 mA ... 24 mA (Extended transmission range for diagnostics)                  |

Signal: Signal conditioner operation

|  |  |
|--|--|
| Output description                       | Signal conditioner operation   |
| Current output signal                    | 0 mA ... 20 mA (active)<br>4 mA ... 20 mA (active)                         |
| Load/output load current output          | < 450 Ω (20 mA)<br>< 380 Ω (23 mA)   |
| Output ripple                            | < 20 mV <sub>rms</sub>   |
| Output behavior in the event of an error | 0 mA (Cable break in the input)<br>0 mA (Cable short-circuit in the input) |
| Underload/overload signal range          | 0 mA ... 24 mA (Extended transmission range for diagnostics)               |

## Connection data

|                                  |   |
|----------------------------------|---|
| Connection method                | Push-in connection                          |
| Stripping length                 | 10 mm                                       |
| Conductor cross-section rigid    | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |

# MACX MCR-SL-RPSSI-2I-SP - Repeater power supply



2924838

<https://www.phoenixcontact.com/us/products/2924838>

|   |   |
|---|---|
| Conductor cross-section flexible (2 conductors with same cross section) | 0.25 mm <sup>2</sup> ... 0.34 mm <sup>2</sup> (TWIN ferrule without plastic sleeve) |
|   | 0.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (TWIN ferrule with plastic sleeve)      |
| Conductor cross-section AWG   | 24 ... 14   |
|   | 24 ... 22 (TWIN ferrule without plastic sleeve)                                     |
|   | 20 ... 16 (TWIN ferrule with plastic sleeve)  |

## Ex data

|                       |        |
|-----------------------|--------|
| Ex installation (EPL) | Gc     |
|                       | Div. 2 |

## Interfaces


### Data communication (bypass)

|                     |                   |
|---------------------|-------------------|
| HART function       | HART transparency |
| Protocols supported | HART              |

## Signaling

|                |                            |
|----------------|----------------------------|
| Status display | Green LED (supply voltage) |
|----------------|----------------------------|

## Dimensions

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
| Width               | 12.5 mm  |
| Height              | 107.9 mm   |
| Depth               | 113.7 mm   |
| Depth NS 35/7,5     | 114.5 mm (Snapped onto DIN rail NS 35/7,5 in accordance with EN 60715)               |

## Material specifications

|  |                 |
|--|-----------------|
| Color  | gray (RAL 7042) |
| Flammability rating according to UL 94 (Housing) | V0 (Housing)    |
| Housing material                                 | PA 6.6-FR       |

## Environmental and real-life conditions

### Ambient conditions

|   |  |
|---|--|
| Degree of protection                    | IP20 (not assessed by UL)                |
| Ambient temperature (operation)         | -40 °C ... 60 °C (Any mounting position) |
|   | -40 °C ... 70 °C (Derating)              |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C                         |
| Permissible humidity (operation)        | 10 % ... 95 % (non-condensing)           |

# MACX MCR-SL-RPSSI-2I-SP - Repeater power supply



2924838

<https://www.phoenixcontact.com/us/products/2924838>

## Altitude range (≤ 2000 m)

|                                 |  |
|---------------------------------|--|
| Altitude                        | ≤ 2000 m (The technical data refers to altitudes ≤2000 m above mean sea level. For altitudes >2000 m above mean sea level, refer to the data sheet.) |
| Ambient temperature (operation) | -40 °C ... 60 °C<br>-40 °C ... 70 °C (Derating)  |
| Rated insulation voltage        | 375 V <sub>PP</sub> (Power supply, input / output)   |

## Altitude range (≤ 3000 m)

|                                 |  |
|---------------------------------|--|
| Height range                    | > 2000 m ... 3000 m  |
| Ambient temperature (operation) | -40 °C ... 54 °C<br>-40 °C ... 63 °C (Derating)                                    |
| Rated insulation voltage        | 190 V AC (Power supply, input / output)<br>110 V DC (Power supply, input / output) |

## Altitude range (≤ 4000 m)

|                                 |   |
|---------------------------------|---|
| Height range                    | > 3000 m ... 4000 m                             |
| Ambient temperature (operation) | -40 °C ... 48 °C<br>-40 °C ... 56 °C (Derating) |
| Rated insulation voltage        | 60 V AC/DC (Power supply, input / output)       |

## Altitude range (≤ 5000 m)

|                                 |   |
|---------------------------------|---|
| Height range                    | > 4000 m ... 5000 m                             |
| Ambient temperature (operation) | -40 °C ... 42 °C<br>-40 °C ... 49 °C (Derating) |
| Rated insulation voltage        | 60 V AC/DC (Power supply, input / output)       |

## Approvals

### CE

|             |                |
|-------------|----------------|
| Certificate | CE-compliant   |
| Note        | and EN 61326-1 |

### ATEX

|                |                            |
|----------------|----------------------------|
| Identification | ⊕ II 3 G Ex ec IIC T4 Gc X |
| Certificate    | PxCCIF11ATEX2924825        |

### IECEX

|                |                    |
|----------------|--------------------|
| Identification | Ex ec IIC T4 Gc    |
| Certificate    | IECEX BVS 10.0097X |

### CCC / China-Ex

|                |                  |
|----------------|------------------|
| Identification | Ex ec IIC T4 Gc  |
| Certificate    | 2022122316115971 |

### UL, USA/Canada

|                |                                  |
|----------------|----------------------------------|
| Identification | UL 508 Listed<br>UL 61010 Listed |
|----------------|----------------------------------|

# MACX MCR-SL-RPSSI-2I-SP - Repeater power supply



2924838

<https://www.phoenixcontact.com/us/products/2924838>

|  |  |
|--|--|
|  | Class I, Div. 2, Groups A, B, C, D T4    |
|  | Class I, Zone 2, Groups IIC, IIB, IIA T4 |

## Shipbuilding approval

|             |                   |
|-------------|-------------------|
| Certificate | DNV GL TAA000020C |
|-------------|-------------------|

## Safety Integrity Level (SIL, IEC 61508)

|                |                        |
|----------------|------------------------|
| Identification | 2                      |
| Certificate    | IN-AT-AS-MRL-23-00432A |

## Systematic Capability

|                |   |
|----------------|---|
| Identification | 3 |
|----------------|---|

## Performance Level (ISO 13849)

|                |           |
|----------------|-----------|
| Identification | d / KAT 2 |
|----------------|-----------|

## INMETRO

|                |                 |
|----------------|-----------------|
| Identification | Ex ec IIC T4 Gc |
| Certificate    | DNV 18.0139 X   |

## Shipbuilding data

|             |   |
|-------------|---|
| Temperature | B   |
| Humidity    | B   |
| Vibration   | A   |
| EMC         | A   |
| Enclosure   | Required protection according to the Rules shall be provided upon installation on board |

## EMC data

|                               |  |
|-------------------------------|--|
| Electromagnetic compatibility | Conformance with EMC directive                                       |
| Noise immunity                | EN 61000-6-2   |
| Note                          | When being exposed to interference, there may be minimal deviations. |

## Noise emission

|                       |              |
|-----------------------|--------------|
| Standards/regulations | EN 61000-6-4 |
|-----------------------|--------------|

## Electromagnetic HF field

|  |                          |
|--|--------------------------|
| Designation  | Electromagnetic RF field |
| Standards/regulations                                  | EN 61000-4-3             |
| Typical deviation from the measuring range final value | 3 %                      |

## Fast transients (burst)

|  |                         |
|--|-------------------------|
| Designation  | Fast transients (burst) |
| Standards/regulations                                  | EN 61000-4-4            |
| Typical deviation from the measuring range final value | 3 %                     |

## Conducted interference

|             |                         |
|-------------|-------------------------|
| Designation | Conducted interferences |
|-------------|-------------------------|

# MACX MCR-SL-RPSSI-2I-SP - Repeater power supply



2924838

<https://www.phoenixcontact.com/us/products/2924838>

|  |              |
|--|--------------|
| Standards/regulations                                  | EN 61000-4-6 |
| Typical deviation from the measuring range final value | 3 %          |

## Standards and regulations

|                      |                 |
|----------------------|-----------------|
| Electrical isolation | 3-way isolation |
|----------------------|-----------------|

## Mounting

|               |                   |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

## Drawings

Dimensional drawing



Diagram



Signal transmission analog and digital at the same time


# MACX MCR-SL-RPSSI-2I-SP - Repeater power supply



2924838

<https://www.phoenixcontact.com/us/products/2924838>

Block diagram



2924838

<https://www.phoenixcontact.com/us/products/2924838>

## Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2924838>


 **UL Listed**  
Approval ID: E330267


 **cUL Listed**  
Approval ID: E330267


**Functional Safety**  
Approval ID: BVS PB 13-10-04


**DNV**  
Approval ID: TAA000020C

 **EAC Ex**  
Approval ID: BY/112 02.01 TP012xx

 **cUL Listed**  
Approval ID: FILE E 199827

 **UL Listed**  
Approval ID: FILE E 199827

 **IECEX**  
Approval ID: IECEX BVS 10.0097X

 **CCC**  
Approval ID: 2022122316115971

2924838

<https://www.phoenixcontact.com/us/products/2924838>

## Classifications

### ECLASS

|                   |          |
|-------------------|----------|
| ECLASS-13.0       | 27210120 |
| ECLASS-15.0       | 27210120 |
| ECLASS-15.0 ASSET | 27250101 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002653 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121000 |
|-------------|----------|

2924838

<https://www.phoenixcontact.com/us/products/2924838>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes                |
| Exemption                               | 6(c), 7(a), 7(c)-I |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |  |
|-------------------------------------|--|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)   |
|                                     | 2,2',6,6'-tetrabromo-4,4'-isopropylidenediphenol(CAS: 79-94-7) |
| SCIP                                | f14a7259-76c2-44b8-b736-209837a72a63                           |

### EF3.1 Climate Change

|         |              |
|---------|--------------|
| CO2e kg | 6.77 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
 586 Fulling Mill Road  
 Middletown, PA 17057, United States  
 (+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)