

# UMKS- E48M-VS - Termination board



2970154

<https://www.phoenixcontact.com/us/products/2970154>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, for IEC 603/DIN 41612 connector, type E, 48-pos., a, c, e components mounted, with male connector, cable housing with screw interlock

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 2970154                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | C422                           |
| Product key                          | DK2187                         |
| GTIN                                 | 4017918087661                  |
| Weight per piece (including packing) | 297.8 g                        |
| Weight per piece (excluding packing) | 285.2 g                        |
| Customs tariff number                | 85369010                       |
| Country of origin                    | DE                             |

# UMKS- E48M-VS - Termination board



2970154

<https://www.phoenixcontact.com/us/products/2970154>

## Technical data

### Product properties

|                     |                  |
|---------------------|------------------|
| Product type        | Interface module |
| Product family      | VARIOFACE        |
| Number of positions | 48               |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Pollution degree     | 2  |

### Electrical properties

|   |                                |
|---|--------------------------------|
| Nominal voltage $U_N$                     | 125 V AC/DC                    |
| Max. current carrying capacity per branch | 4 A                            |
| Rated insulation voltage                  | 125 V                          |
| Rated surge voltage                       | 1.2 kV (Functional insulation) |

### Connection data

#### Field level

|                                  |   |
|----------------------------------|---|
| Connection in acc. with standard | IEC / EN                                    |
| Connection method                | Screw connection                            |
| Stripping length                 | 8 mm  |
| Screw thread                     | M3  |
| Conductor cross-section rigid    | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross-section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section AWG      | 24 ... 12                                   |

#### Controller level

|                       |                              |
|-----------------------|------------------------------|
| Connection method     | IEC 603/DIN 41612 connection |
| Number of connections | 1                            |
| Number of positions   | 48                           |

### Signaling

|                        |    |
|------------------------|----|
| Status display present | no |
|------------------------|----|

### Dimensions

#### Item dimensions

|        |          |
|--------|----------|
| Width  | 123.6 mm |
| Height | 77 mm    |
| Depth  | 70.87 mm |

### Material specifications

|                             |                             |
|-----------------------------|-----------------------------|
| Color                       | green (RAL 6021)            |
| Housing insulation material | Polyamide PA non-reinforced |

# UMKS- E48M-VS - Termination board



2970154

<https://www.phoenixcontact.com/us/products/2970154>

## Environmental and real-life conditions

### Ambient conditions

|   |                  |
|---|------------------|
| Degree of protection                    | IP20             |
| Ambient temperature (operation)         | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

## Standards and regulations

|                       |              |
|-----------------------|--------------|
| Standards/regulations | DIN EN 50178 |
|                       | IEC 60664    |

## Mounting

|                   |                   |
|-------------------|-------------------|
| Mounting type     | DIN rail mounting |
| Mounting position | any               |

## Notes

|                    |  |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

# UMKS- E48M-VS - Termination board



2970154

<https://www.phoenixcontact.com/us/products/2970154>

## Classifications

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121432 |
|-------------|----------|

# UMKS- E48M-VS - Termination board



2970154

<https://www.phoenixcontact.com/us/products/2970154>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)