

UMK- 4 RM 24 - Multiple relay module

2971344

<https://www.phoenixcontact.com/us/products/2971344>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, for 4 plug-in miniature relays or miniature optocouplers, with LED, 24 V AC/DC input voltage

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2971344 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C460 |
| Product key | DK6164 |
| GTIN | 4017918088330 |
| Weight per piece (including packing) | 152.6 g |
| Weight per piece (excluding packing) | 111.76 g |
| Customs tariff number | 85364190 |
| Country of origin | DE |

UMK- 4 RM 24 - Multiple relay module



2971344

<https://www.phoenixcontact.com/us/products/2971344>

Technical data

Notes

Utilization restriction

| | |
|----------|---|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---|

Product properties

| | |
|-----------------------|--|
| Product type | Multi-channel relay module |
| No. of channels | 4 |
| Compatible components | Miniature relays or miniature optocouplers |
| With components | no |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree | 2 |

Electrical properties

| | |
|--------------------------|--|
| Rated insulation voltage | 260 V AC |
| Rated surge voltage | 4 kV (Basic insulation between output contact current paths) 6 kV (Safe isolation and reinforced insulation between input circuit and output contact paths) |

Input data

| | |
|---|------------------------------------|
| Nominal input voltage U_N | 24 V AC/DC $\pm 10\%$ |
| Input voltage range in reference to U_N | 0.8 ... 1.1 |
| Typical input current at U_N | 2 mA |
| Protective circuit | Bridge rectifier; Bridge rectifier |
| Status display/channel | Yellow LED |

Output data

| | |
|-----------------------|--|
| Compatible components | Miniature relays or miniature optocouplers |
|-----------------------|--|

Switching

| | |
|--|----------------------|
| Contact switching type | 1 changeover contact |
| Maximum switching voltage | 250 V AC/DC |
| Limiting continuous current | 6 A |
| Maximum inrush current | 8 A |
| Error detection (line break / short-circuit) | no |

Connection data

| | |
|-----------------------|------------------|
| Connection method | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M3 |
| Number of connections | 1 |

UMK- 4 RM 24 - Multiple relay module



2971344

<https://www.phoenixcontact.com/us/products/2971344>

| | |
|----------------------------------|---|
| Number of positions | 6 |
| Conductor cross-section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |
| Connection method | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M3 |
| Number of connections | 12 |
| Number of positions | 3 |
| Conductor cross-section rigid | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |

Dimensions

| | |
|--------|---------|
| Width | 67.5 mm |
| Height | 77 mm |
| Depth | 59 mm |

Material specifications

| | |
|-------|------------------|
| Color | green (RAL 6021) |
|-------|------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---|------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -20 °C ... 70 °C |

Standards and regulations

| | |
|-----------------------|--------------|
| Standards/regulations | DIN EN 50178 |
| | IEC 60664 |

Mounting

| | |
|-------------------|---------------------------|
| Mounting type | DIN rail mounting |
| Assembly note | in rows with zero spacing |
| Mounting position | any |


UMK- 4 RM 24 - Multiple relay module

2971344

<https://www.phoenixcontact.com/us/products/2971344>

Drawings

Circuit diagram



UMK- 4 RM 24 - Multiple relay module

2971344

<https://www.phoenixcontact.com/us/products/2971344>



Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39122335 |
|-------------|----------|

UMK- 4 RM 24 - Multiple relay module



2971344

<https://www.phoenixcontact.com/us/products/2971344>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
|-------------------------------------|----------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com