

QUINT-PS-120AC/24DC/10 - Power supply



2939072

<https://www.phoenixcontact.com/us/products/2939072>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power supply unit, primary switched-mode, input 120 V AC, output 24 V DC/10 A

Commercial data

Item number	2939072
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	CM11
Product key	CMPP13
GTIN	4017918155285
Weight per piece (including packing)	1,751.3 g
Weight per piece (excluding packing)	1,751.3 g
Customs tariff number	85044094
Country of origin	00

Technical data

Input data

AC operation

Input voltage	120 V AC
Input voltage range	90 V AC ... 132 V AC
Input voltage range AC	90 V AC ... 132 V AC
Inrush current	< 24 A (at 25 °C)
AC frequency range	47 Hz ... 63 Hz
Mains buffering time	> 20 ms
Current consumption	approx. 3 A
Input fuse	6.3 A (slow-blow, soldered internally)

Output data

Efficiency	> 84 %
Nominal output voltage	24 V DC \pm 1 % (typical)
Setting range of the output voltage (U_{Set})	11.5 V DC ... 18 V DC (constant)
Nominal output current (I_N)	10 A
Residual ripple	150 mV _{PP}
Peak switching voltages idling	100 mV _{PP} (1.2 MHz bandwidth)
Maximum no-load power dissipation	< 5 W
Power loss nominal load max.	< 53 W
Connection in parallel	yes, for assembling redundant systems and increasing efficiency

Connection data

Input

Connection method	Pluggable screw connection
Conductor cross-section, rigid min.	0.2 mm ²
Conductor cross-section, rigid max.	2.5 mm ²
Conductor cross-section flexible min.	0.2 mm ²
Conductor cross-section flexible max.	2.5 mm ²
Conductor cross-section AWG min.	24
Conductor cross-section AWG max.	14
Stripping length	8 mm
Screw thread	M2,5

Output

Connection method	Pluggable screw connection
Conductor cross-section, rigid min.	0.2 mm ²
Conductor cross-section, rigid max.	4 mm ²
Conductor cross-section flexible min.	0.2 mm ²
Conductor cross-section flexible max.	4 mm ²
Conductor cross-section AWG min.	24

QUINT-PS-120AC/24DC/10 - Power supply



2939072

<https://www.phoenixcontact.com/us/products/2939072>

Conductor cross-section AWG max.	10
Stripping length	8 mm
Screw thread	M2,5

Signaling

Operating voltage display	LED
---------------------------	-----

Electrical properties

Insulation voltage input/output	1.8 kV (routine test)
	3 kV (type test)

Product properties

Product type	Power supply
MTBF (IEC 61709, SN 29500)	> 500000 h

Dimensions

Width	180 mm
Height	115 mm
Depth	125 mm

Mounting

Assembly note	alignable: vertical with spacing = 10 cm, horizontal with zero spacing
Mounting position	on horizontal DIN rail NS 35 in acc. with EN 60715

Material specifications

Housing material	Metal
Type of housing	High-grade steel plate, enclosed
Side element version	ABS V0, color: green

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 70 °C (UL up to 50°C)
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	up to 95 % (at 25 °C, non-condensing)

Standards and regulations

Standard - Electrical safety	EN 60950/VDE 0805-1
	DIN EN 50178/VDE 0160
	UL 508C
	CSA C22.2-14
	UL 1950
	CSA C22.2-950
	DIN VDE 0100-410

QUINT-PS-120AC/24DC/10 - Power supply




2939072

<https://www.phoenixcontact.com/us/products/2939072>


	DIN VDE 0106-101
Standard - Safe isolation	DIN VDE 0100-410
	DIN VDE 0106-101

Drawings

Diagram



Circuit diagram



QUINT-PS-120AC/24DC/10 - Power supply



2939072

<https://www.phoenixcontact.com/us/products/2939072>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com