

CM 50-PS-120-230AC/24DC/2,5/F - Power supply



2939425

<https://www.phoenixcontact.com/us/products/2939425>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power supply unit, primary switched-mode, input 100 V-240 V AC/ 100 V-370 V DC, output 24 V DC/2.5 A, with filter

Commercial data

Item number	2939425
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	CM11
Product key	CMPL13
GTIN	4017918163198
Weight per piece (including packing)	575.7 g
Weight per piece (excluding packing)	500 g
Customs tariff number	85044094
Country of origin	DE

Technical data

Input data

Nominal input voltage range	110 V AC ... 240 V AC
Input voltage range	90 V AC ... 264 V AC
	100 V DC ... 350 V DC
Input voltage range AC	90 V AC ... 264 V AC
Input voltage range DC	100 V DC ... 350 V DC
Inrush current	< 15 A (at 25 °C)
AC frequency range	47 Hz ... 63 Hz
Mains buffering time	20 ms (at 120 V AC)
	80 ms (at 230 V AC)
Current consumption	0.9 A (at 120 V)
	0.5 A (at 230 V)
Input fuse	4 A (slow-blow)

Output data

Efficiency	> 85 %
Number of outputs	1
Nominal output voltage	24 V DC \pm 1 %
Setting range of the output voltage (U_{Set})	22.5 V DC ... 28.5 V DC
Nominal output current (I_N)	2.5 A
Residual ripple	< 200 mV _{pp} (at no-load, typ. 20 mV _{pp})
	< 200 mV _{pp} (at nominal load, typ. 20 mV _{pp})
Peak switching voltages idling	< 200 mV _{pp} (at nominal load, typ. 20 mV _{pp})
Peak switching voltages nominal load	< 200 mV _{pp} (at nominal load, typ. 20 mV _{pp})
Maximum no-load power dissipation	< 4 W
Power loss nominal load max.	< 10 W
Connection in parallel	yes, for assembling redundant systems and increasing efficiency

Connection data

Input

Connection method	Screw connection
Conductor cross-section, rigid min.	0.2 mm ²
Conductor cross-section, rigid max.	2.5 mm ²
Conductor cross-section flexible min.	0.2 mm ²
Conductor cross-section flexible max.	2.5 mm ²
Conductor cross-section AWG min.	24
Conductor cross-section AWG max.	14
Stripping length	8 mm
Screw thread	M2,5

Output

CM 50-PS-120-230AC/24DC/2,5/F - Power supply



2939425

<https://www.phoenixcontact.com/us/products/2939425>

Connection method	Screw connection
Conductor cross-section, rigid min.	0.2 mm ²
Conductor cross-section, rigid max.	4 mm ²
Conductor cross-section flexible min.	0.2 mm ²
Conductor cross-section flexible max.	4 mm ²
Conductor cross-section AWG min.	24
Conductor cross-section AWG max.	10
Stripping length	8 mm
Screw thread	M2,5

Signaling

Operating voltage display	LED
---------------------------	-----

Electrical properties

Insulation voltage input/output	3 kV (routine test)
	5 kV (type test)

Product properties

Product type	Power supply
MTBF (IEC 61709, SN 29500)	> 500000 h

Dimensions

Width	50 mm
Height	130 mm
Depth	102 mm

Mounting

Assembly note	alignable: vertical with spacing = 10 cm, horizontal with zero spacing
Mounting position	on horizontal DIN rail NS 35 in acc. with EN 60715

Material specifications

Type of housing	Polycarbonate PC, color: green
-----------------	--------------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	up to 100 % (at 25°C, device will still start up with condensation)

Standards and regulations

Standard - Electrical safety	EN 60950/VDE 0805-1
	DIN EN 50178/VDE 0160
	UL 508C

CM 50-PS-120-230AC/24DC/2,5/F - Power supply




2939425

<https://www.phoenixcontact.com/us/products/2939425>

	CSA C22.2-14
	UL 1950
	CSA C22.2-950
	DIN VDE 0100-410
	DIN VDE 0106-101

Drawings

Diagram




CM 50-PS-120-230AC/24DC/2,5/F - Power supply



2939425

<https://www.phoenixcontact.com/us/products/2939425>

Circuit diagram



CM 50-PS-120-230AC/24DC/2,5/F - Power supply



2939425

<https://www.phoenixcontact.com/us/products/2939425>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com