

PSR-SCP- 24DC/SDC4/2X1/B - Safety relays



2981486

<https://www.phoenixcontact.com/us/products/2981486>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safety relay for emergency stop, safety door, and magnetic switches and for light grids, up to SIL 3 or Cat. 4, PL e in accordance with EN ISO 13849, 2 N/O contacts, TBUS interface, automatic or manual activation, plug-in screw connection terminal blocks

Your advantages

- Up to Cat. 4/PL e in accordance with ISO 13849-1, SIL 3 in accordance with EN IEC 62061, SIL 3 in accordance with IEC 61508
- Modular system with TBUS extension
- For emergency stop and safety door monitoring, plus evaluation of light grids
- 2 enabling current paths, 1 signaling current path
- 1- and 2-channel control

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2981486 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN01 |
| Product key | DNA211 |
| GTIN | 4046356051682 |
| Weight per piece (including packing) | 185.8 g |
| Weight per piece (excluding packing) | 224.8 g |
| Customs tariff number | 85371098 |
| Country of origin | DE |

PSR-SCP- 24DC/SDC4/2X1/B - Safety relays



2981486

<https://www.phoenixcontact.com/us/products/2981486>

Technical data

Product properties

| | |
|-------------------------|--|
| Product type | Safety relays |
| Product family | PSRclassic |
| Application | Emergency stop |
| | Safety door |
| | Light grid |
| | Magnetic switch |
| Control | 1 and 2 channel |
| Mechanical service life | approx. 10^7 cycles |
| Relay type | Electromechanical relay with force-guided contacts in accordance with IEC/EN 61810-3 |

Insulation characteristics

| | |
|----------------------|---|
| Overvoltage category | II, III (See the section "Insulation coordination") |
| Degree of pollution | 2 |

Times

| | |
|-----------------------|--------------------------|
| Typical response time | 20 ms (manual start) |
| | 150 ms (automatic start) |
| Typical release time | 10 ms |
| Recovery time | 1 s |

Electrical properties

| | |
|---|--|
| Maximum power dissipation for nominal condition | 5.6 W |
| Nominal operating mode | 100% operating factor |
| Rated insulation voltage | 250 V |
| Rated surge voltage/insulation | See data sheet, section "Insulation coordination". |

Supply

| | |
|--|---|
| Designation | A1/A2, PSR-TBUS |
| Rated control circuit supply voltage U_S | 24 V DC -15 % / +10 % |
| Rated control supply current I_S | typ. 70 mA |
| Power consumption at U_S | typ. 1.7 W |
| Protective circuit | Serial protection against polarity reversal |
| | Suppressor diode |

Input data

Digital: Sensor circuit (S10, S12, S13, S22)

| | |
|---|------------------|
| Description of the input | safety-related |
| Number of inputs | 4 |
| Concurrence | ∞ |
| Max. permissible overall conductor resistance | 50 Ω |
| Protective circuit | Suppressor diode |

PSR-SCP- 24DC/SDC4/2X1/B - Safety relays



2981486

<https://www.phoenixcontact.com/us/products/2981486>

Digital: Start circuit ()

| | |
|--------------------------|--------------------|
| Description of the input | non-safety-related |
|--------------------------|--------------------|

Output data

Relay: Enabling current paths (13/14, 23/24)

| | |
|-----------------------------|--|
| Output description | 2 N/O contacts in series, safety-related, floating |
| Number of outputs | 2 |
| Contact switching type | 2 enabling current paths |
| Contact material | AgSnO ₂ |
| Switching voltage | max. 250 V AC/DC min. 15 V AC/DC |
| Switching power | min. 0.4 W |
| Inrush current | min. 25 mA max. 6 A |
| Switching capacity | 5 A (AC15) 5 A (DC13) |
| Limiting continuous current | 6 A |
| Sq. Total current | 72 A ² (observe derating) |
| Mechanical service life | 10x 10 ⁶ cycles |
| Output fuse | 10 A gL/gG NEOZED |

Signal: Y30

| | |
|---------------------------------|-------------------------------------|
| Output description | PNP non-safety-related |
| Number of outputs | 1 |
| Load/output load voltage output | min. 240 Ω |
| Voltage | typ. 23 V DC (U _S - 1 V) |
| Current | max. 100 mA |
| Switching frequency | 1 Hz |

Connection data

Connection technology

| | |
|-----------|-----|
| pluggable | yes |
|-----------|-----|

Conductor connection

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |
| Stripping length | 7 mm |
| Screw thread | M3 |
| Tightening torque | 0.5 Nm ... 0.6 Nm |

Dimensions

PSR-SCP- 24DC/SDC4/2X1/B - Safety relays



2981486

<https://www.phoenixcontact.com/us/products/2981486>

| | |
|--------|----------|
| Width | 22.5 mm |
| Height | 99 mm |
| Depth | 114.5 mm |

Material specifications

| | |
|------------------|-------------------|
| Color (Housing) | yellow (RAL 1018) |
| Housing material | PA |

Characteristics

Safety data

| | |
|----------------------------|---|
| Stop category (EN 60204-1) | 0 |
|----------------------------|---|

Safety data: EN ISO 13849

| | |
|------------------------|--|
| Performance level (PL) | e (5 A DC13; 5 A AC15; 8760 switching cycles/year) |
|------------------------|--|

Safety data: IEC 61508 - High demand

| | |
|------------------------------|---|
| Safety Integrity Level (SIL) | 3 |
|------------------------------|---|

Safety data: IEC 61508 - Low demand

| | |
|------------------------------|---|
| Safety Integrity Level (SIL) | 3 |
|------------------------------|---|

Safety data: EN IEC 62061

| | |
|------------------------------|---|
| Safety Integrity Level (SIL) | 3 |
|------------------------------|---|

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Degree of protection | IP20 |
| Min. degree of protection of inst. location | IP54 |
| Ambient temperature (operation) | -20 °C ... 55 °C |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |
| Maximum altitude | ≤ 2000 m (Above sea level) |
| Max. permissible humidity (storage/transport) | 75 % (on average, 85% infrequently, non-condensing) |
| Max. permissible relative humidity (operation) | 75 % (on average, 85% infrequently, non-condensing) |
| Shock (operation) | 15g |
| Vibration (operation) | 10 Hz ... 150 Hz, 2g |

Approvals

CE

| | |
|----------------|--------------|
| Identification | CE-compliant |
|----------------|--------------|

Mounting

| | |
|-------------------|-------------------|
| Mounting type | DIN rail mounting |
| Mounting position | any |

PSR-SCP- 24DC/SDC4/2X1/B - Safety relays




2981486

<https://www.phoenixcontact.com/us/products/2981486>


Drawings

Connection diagram



PSR-TBUS DIN rail connectors are used for cross-wiring between the modules.

Circuit diagram



Block diagram


PSR-SCP- 24DC/SDC4/2X1/B - Safety relays



2981486

<https://www.phoenixcontact.com/us/products/2981486>

Circuit diagram




2-channel emergency stop monitoring

PSR-SCP- 24DC/SDC4/2X1/B - Safety relays

2981486

<https://www.phoenixcontact.com/us/products/2981486>

Circuit diagram



Light grid monitoring


PSR-SCP- 24DC/SDC4/2X1/B - Safety relays



2981486

<https://www.phoenixcontact.com/us/products/2981486>

Circuit diagram



Two-channel magnetic switch monitoring

PSR-SCP- 24DC/SDC4/2X1/B - Safety relays



2981486

<https://www.phoenixcontact.com/us/products/2981486>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2981486>



cULus Listed

Approval ID: E140324



Functional Safety

Approval ID: 01/205/0660.04/24

PSR-SCP- 24DC/SDC4/2X1/B - Safety relays



2981486

<https://www.phoenixcontact.com/us/products/2981486>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27371819 |
| ECLASS-15.0 | 27371819 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001449 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39122200 |
|-------------|----------|

PSR-SCP- 24DC/SDC4/2X1/B - Safety relays



2981486

<https://www.phoenixcontact.com/us/products/2981486>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | d72e7db1-94f1-4bbe-b1b1-ea81c50ae8cb |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 5.859 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com