

EMG 17-REL/KSR-120/21-21-LC AU - Relay module



2941455

<https://www.phoenixcontact.com/us/products/2941455>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay module, with soldered-in miniature switching relay, contact (AgNi+Au): small to large loads, 2 changeover contacts, input voltage 120 V AC/DC

The figure shows version EMG 17-REL/KSR- 24/21-21-LC AU, with soldered-in miniature switching relay

Your advantages

- Safe isolation between coil and contact side
- Integrated input circuit and interference suppression circuit

Commercial data

Item number	2941455
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	C460
Product key	DK61C2
GTIN	4017918080457
Weight per piece (including packing)	57.41 g
Weight per piece (excluding packing)	57.41 g
Customs tariff number	85364190
Country of origin	DE

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Relay Module
Product family	EMG
Application	Universal
Operating mode	100% operating factor
Mechanical service life	approx. 2×10^7 cycles

Insulation characteristics: Air clearances and creepage distances between the power circuits

Insulation	Basic insulation Safe isolation, reinforced insulation, and 6 kV between input circuit and output contact current paths
Overvoltage category	II
Pollution degree	2

Insulation characteristics: Air clearances and creepage distances between input and contact circuit (or output contact current path)

Insulation	Safe isolation, reinforced insulation
Overvoltage category	III
Pollution degree	2

Data management status

Date of last data management	01.04.2026
------------------------------	------------

Electrical properties

Maximum power dissipation for nominal condition	0.72 W
Test voltage (Winding/contact)	4 kV AC (50 Hz, 1 min., winding/contact)
Test voltage (Contact/contact)	1 kV AC (50 Hz, 1 min., changeover contact/changeover contact)

Air clearances and creepage distances between the power circuits

Rated insulation voltage	260 V AC
Rated surge voltage	2.3 kV

Air clearances and creepage distances between input and contact circuit (or output contact current path)

Rated insulation voltage	260 V AC
Rated surge voltage	6 kV

Input data

Coil side

Nominal input voltage U_N	120 V AC/DC
-----------------------------	-------------

EMG 17-REL/KSR-120/21-21-LC AU - Relay module



2941455

<https://www.phoenixcontact.com/us/products/2941455>

Input voltage range	96 V AC/DC ... 132 V AC/DC (20 °C)
Drive and function	monostable
Drive (polarity)	polarized
Typical input current at U_N	6 mA
Typical response time	8 ms
Typical release time	10 ms
Protective circuit	Bridge rectifier; Bridge rectifier
Operating voltage display	Yellow LED

Output data

Switching

Contact switching type	2 changeover contacts
Type of switch contact	Single contact
Contact material	AgNi, hard gold-plated
Maximum switching voltage	30 V AC 36 V DC
Limiting continuous current	50 mA
Maximum inrush current	0.2 A
Interrupting rating (ohmic load) max.	1.2 W (at 24 V DC)

Switching: when the gold layer is destroyed

Note	the following values are applicable if a gold layer is destroyed
Maximum switching voltage	250 V AC/DC
Limiting continuous current	5 A
Maximum inrush current	6 A
Interrupting rating (ohmic load) max.	120 W (at 24 V DC) 95 W (at 48 V DC) 60 W (at 60 V DC) 40 W (at 110 V DC) 55 W (at 220 V DC) 1250 VA (for 250 V AC)

Connection data

Coil side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm

Contact side

EMG 17-REL/KSR-120/21-21-LC AU - Relay module



2941455

<https://www.phoenixcontact.com/us/products/2941455>

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Dimensions

Item dimensions

Width	17.5 mm
Height	75 mm
Depth	62.5 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 40 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Air clearances and creepage distances between the power circuits

Standards/regulations	IEC 60664-1
-----------------------	-------------

Air clearances and creepage distances between input and contact circuit (or output contact current path)

Standards/regulations	IEC 60664-1
-----------------------	-------------

Standards/regulations

Standards/regulations	EN 61810-1
-----------------------	------------

Mounting


Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

2941455

<https://www.phoenixcontact.com/us/products/2941455>

Drawings

Circuit diagram



EMG 17-REL/KSR-120/21-21-LC AU - Relay module



2941455

<https://www.phoenixcontact.com/us/products/2941455>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2941455>



cUL Recognized

Approval ID: E238705



UL Recognized

Approval ID: E238705

2941455

<https://www.phoenixcontact.com/us/products/2941455>

Classifications

ECLASS

ECLASS-13.0	27371601
ECLASS-15.0	27371601

ETIM

ETIM 10.0	EC001437
-----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

2941455

<https://www.phoenixcontact.com/us/products/2941455>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c8b403ce-6c6a-442a-a774-3d161101e06a

EF3.1 Climate Change

CO2e kg	0.982 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com