

EMG 17-REL/KSR-G 24/2E/SO38 - Relay



2941646

<https://www.phoenixcontact.com/us/products/2941646>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay module for high continuous currents, with soldered-in relay, contacts (AgSnO): medium to large loads, 1 N/O contact, input voltage 24 V DC, limiting continuous current 10 A, with 2 inputs for manual/automatic

Your advantages

- Can be snapped onto standard EN DIN rails
- Clear terminal marking using Phoenix Contact labeling material
- Modular DIN-rail mountable EMG housing with 17.5 mm design width
- User-friendly plug-in housing
- Easy maintenance

Commercial data

Item number	2941646
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	C460
Product key	DK61CY
GTIN	4017918080556
Weight per piece (including packing)	58.06 g
Weight per piece (excluding packing)	58.06 g
Customs tariff number	85364190
Country of origin	DE

Technical data

Notes

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

Product properties

Product type	Relay Module
Product family	EMG
Application	high inrush currents
Operating mode	100% operating factor
Mechanical service life	3x 10 ⁷ cycles

Insulation characteristics

Insulation	safe isolation
Overvoltage category	III
Pollution degree	2

Data management status

Date of last data management	01.04.2026
------------------------------	------------

Electrical properties

Maximum power dissipation for nominal condition	0.55 W
Test voltage (Winding/contact)	4 kV AC (50 Hz, 1 min., winding/contact)

Input data

Coil side

Nominal input voltage U_N	24 V DC
Input voltage range	21.6 V DC ... 26.4 V DC (20 °C)
Drive and function	monostable
Drive (polarity)	polarized
Typical input current at U_N	23 mA
Typical response time	9 ms
Typical release time	10 ms
Protective circuit	Freewheeling diode; Freewheeling diode Reverse polarity protection; Polarity protection diode
Operating voltage display	Automatic: Yellow LED, Manual: Red LED

Output data

Switching

Contact switching type	1 N/O contact
Type of switch contact	Single contact

EMG 17-REL/KSR-G 24/2E/SO38 - Relay



2941646

<https://www.phoenixcontact.com/us/products/2941646>

Contact material	AgSnO
Maximum switching voltage	250 V AC/DC
Limiting continuous current	10 A
Maximum inrush current	120 A (20 ms)
Interrupting rating (ohmic load) max.	240 W (at 24 V DC)
	120 W (at 48 V DC)
	85 W (at 60 V DC)
	70 W (at 110 V DC)
	90 W (at 220 V DC)
	100 W (for 250 V DC)
Interrupting rating (lamp load) max.	2500 VA (for 250 V AC)
Interrupting rating (lamp load) max.	on request

Connection data

Coil side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12
Tightening torque	0.5 Nm ... 0.6 Nm

Contact side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Dimensions

Item dimensions

Width	17.5 mm
Height	75 mm
Depth	62.5 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
---------------------------------	------------------

EMG 17-REL/KSR-G 24/2E/SO38 - Relay



2941646

<https://www.phoenixcontact.com/us/products/2941646>

Ambient temperature (storage/transport)	-20 °C ... 70 °C
---	------------------

Standards and regulations

Standards/regulations	IEC 60664
	EN 50178

Mounting

Mounting type	DIN rail mounting
Mounting position	any

EMG 17-REL/KSR-G 24/2E/SO38 - Relay




2941646

<https://www.phoenixcontact.com/us/products/2941646>

Drawings

Circuit diagram



EMG 17-REL/KSR-G 24/2E/SO38 - Relay



2941646

<https://www.phoenixcontact.com/us/products/2941646>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2941646>



EAC

Approval ID: RU*DE*08.B.01841/19

EMG 17-REL/KSR-G 24/2E/SO38 - Relay



2941646

<https://www.phoenixcontact.com/us/products/2941646>

Classifications

ECLASS

ECLASS-13.0	27371601
ECLASS-15.0	27371601

ETIM

ETIM 10.0	EC001437
-----------	----------

UNSPSC

UNSPSC 21.0	39122300
-------------	----------

2941646

<https://www.phoenixcontact.com/us/products/2941646>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f5e99c25-03b1-4069-bba7-3ed2d025fbd6

EF3.1 Climate Change

CO2e kg	1.386 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com