

IB IL 24 PSDO 8-PAC - Safety module



2985631

<https://www.phoenixcontact.com/us/products/2985631>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safety-related digital output module, IP20 degree of protection, for SafetyBridge, INTERBUS-Safety, and PROFIsafe systems. The module has four safe digital outputs for two-channel assignment or eight safe digital outputs for single-channel assignment

Product description

The safety module is an output module from the Inline product range designed for use at any point within a SafetyBridge, INTERBUS-Safety or PROFIsafe system. The transmission speed of the safety module can be set to 500 kBaud or 2 Mbaud using a switch. One transmission speed must be used consistently within a station. The module has four safe digital outputs for two-channel assignment or eight digital outputs for single-channel assignment.

Your advantages


- SIL 3 according to IEC/EN 61508
- SIL 3 in accordance with EN IEC 62061
- PL e in accordance with EN ISO 13849-1

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2985631 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN03 |
| Product key | DNA431 |
| GTIN | 4046356131605 |
| Weight per piece (including packing) | 350.8 g |
| Weight per piece (excluding packing) | 245.6 g |
| Customs tariff number | 85389091 |
| Country of origin | DE |

Technical data

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 48.8 mm |
| Height | 119.8 mm |
| Depth | 71.5 mm |
| Note on dimensions | Housing dimensions |

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Material specifications

| | |
|-----------------|-------------------|
| Color (Housing) | yellow (RAL 1018) |
|-----------------|-------------------|

Interfaces

Inline local bus

| | |
|--------------------|-------------------------------------|
| No. of channels | 2 |
| Connection method | Inline data jumper |
| Transmission speed | 500 kbps / 2 Mbps (can be switched) |

System properties

Programming data (LocalbusSlave)

| | |
|-------------------------|---|
| Length code (hex) | 04 |
| ID code (dec.) | 167 |
| Length code (dec) | 04 |
| Process data channel | 8 Byte ((Operating mode: SafetyBridge)) |
| Input address area | 8 Byte ((Operating mode: SafetyBridge)) |
| Output address area | 8 Byte ((Operating mode: SafetyBridge)) |
| Parameter channel (PCP) | 0 Byte ((Operating mode: SafetyBridge)) |
| Register length (bus) | 8 Byte ((Operating mode: SafetyBridge)) |

Fieldbus data telegram

| | |
|-----------------------------|---|
| Required parameter data | 1 Byte ((Operating mode: SafetyBridge)) |
| Required configuration data | 5 Byte ((Operating mode: SafetyBridge)) |

Output data

Digital:

| | |
|---|---|
| Output name | Digital outputs |
| Connection method | Spring-cage connection |
| Connection technology | 2-, 3-conductor |
| Number of outputs | 4 (for 2-channel assignment) |
| | 8 (for 1-channel assignment) |
| | 8 |
| Protective circuit | Overload protection, short-circuit protection of outputs |
| Output voltage | 24 V DC ($U_S - 1 V$) |
| Output current | max. 6 A (Total current of all outputs, -25 °C ... 50 °C) |
| | max. 4 A (Total current of all outputs, >50 °C ... 55 °C) |
| Maximum output current per group | 3 A |
| Maximum output current per channel | 2 A |
| Max. current carrying capacity per output | See technical data |
| Maximum output current per module | 3 A (See technical data) |
| Nominal output voltage | 24 V DC |
| Nominal load, inductive | see safety data |
| Nominal load, lamp | see safety data |
| Nominal load, ohmic | see safety data |
| Behavior with inductive overload | Output can be destroyed |

Product properties

| | |
|----------------------|---|
| Product type | I/O component |
| Product family | Inline |
| Application | Functional safety |
| Type | modular |
| Diagnostics messages | Short-circuit or overload of the digital outputs Error message in diagnostics code (bus) and display by means of the LED on the motor |

Electrical properties

| | |
|---------------------|--------|
| Transmission medium | Copper |
|---------------------|--------|

Potentials: Communications power (U_L)

| | |
|----------------|-------------------------------|
| Supply voltage | 7.5 V DC (see safety data) |
| Current draw | max. 230 mA (see safety data) |

Potentials: Main circuit supply (U_M)

| | |
|----------------------|--|
| Supply voltage | 24 V DC |
| Supply voltage range | 19.2 V DC ... 30 V DC (including all tolerances, including ripple) |
| Current draw | max. 6.03 A |
| | typ. 30 mA (all outputs set including actuator current) |

Supply: Module electronics

IB IL 24 PSDO 8-PAC - Safety module



2985631

<https://www.phoenixcontact.com/us/products/2985631>

| | |
|----------------------|------------------------------|
| Supply voltage | 24 V DC (via voltage jumper) |
| Supply voltage range | 19.2 V DC ... 30 V DC |

Electrical isolation/isolation of the voltage ranges

| | |
|---|------------------------|
| Test voltage: 5 V supply, incoming remote bus/7.5 V supply (bus logics) | 500 V AC, 50 Hz, 1 min |
| Test voltage: 5 V supply, outgoing remote bus/7.5 V supply (bus logics) | 500 V AC, 50 Hz, 1 min |
| Test voltage: 7.5 V supply (bus logics)/24 V supply (I/O) | 500 V AC, 50 Hz, 1 min |
| Test voltage: 24 V supply (I/O) / functional ground | 500 V AC, 50 Hz, 1 min |

Connection data

Connection technology

| | |
|-----------------|------------------|
| Connection name | Inline connector |
| pluggable | yes |

Inline connector

| | |
|-----------------------------------|---|
| Connection method | Spring-cage connection |
| pluggable | yes |
| Conductor cross-section, rigid | 0.2 mm ² ... 1.5 mm ² |
| Conductor cross-section, flexible | 0.2 mm ² ... 1.5 mm ² |
| Conductor cross-section AWG | 24 ... 16 |

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Ambient temperature (operation) | -25 °C ... 55 °C |
| Degree of protection | IP20 |
| Air pressure (operation) | 80 kPa ... 108 kPa (up to 2000 m above sea level) |
| Air pressure (storage/transport) | 66 kPa ... 108 kPa (up to 3500 m above sea level) |
| Ambient temperature (storage/transport) | -25 °C ... 70 °C |
| Permissible humidity (operation) | 10 % ... 85 % (Take suitable measures against increased air humidity within the permitted temperature range.) |
| Permissible humidity (storage/transport) | 10 % ... 85 % (Take suitable measures against increased air humidity within the permitted temperature range.) |

Standards and regulations

| | |
|------------------|---------------------------------------|
| Protection class | III (IEC 61140, EN 61140, VDE 0140-1) |
|------------------|---------------------------------------|

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

IB IL 24 PSDO 8-PAC - Safety module



2985631

<https://www.phoenixcontact.com/us/products/2985631>


Drawings

Dimensional drawing



Dimensions (in mm)

Connection diagram



Example connection of a contactor

IB IL 24 PSDO 8-PAC - Safety module



2985631

<https://www.phoenixcontact.com/us/products/2985631>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2985631>

PROFIsafe

Approval ID: Z20081



cULus Listed

Approval ID: E140324



Functional Safety

Approval ID: 968/FSP 2449.00/22

2985631

<https://www.phoenixcontact.com/us/products/2985631>

Classifications

ECLASS

| | |
|-------------------|----------|
| ECLASS-13.0 | 27242604 |
| ECLASS-15.0 | 27242604 |
| ECLASS-15.0 ASSET | 27250101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001599 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 32151600 |
|-------------|----------|

2985631

<https://www.phoenixcontact.com/us/products/2985631>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 90c06790-7b35-4495-a1c9-40ab602f2746 |

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 16.5 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com