

EMG 30-S2/16A - Switching module



2944533

<https://www.phoenixcontact.com/us/products/2944533>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE switch module, with screw connection, for mounting on NS 32 or NS 35/7.5

Commercial data

Item number	2944533
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	C440
Product key	DK66MY
GTIN	4017918278939
Weight per piece (including packing)	75.51 g
Weight per piece (excluding packing)	74.94 g
Customs tariff number	85365080
Country of origin	DE

EMG 30-S2/16A - Switching module



2944533

<https://www.phoenixcontact.com/us/products/2944533>

Technical data

Product properties

Product type	Interface module
--------------	------------------

Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

Electrical properties

Nominal voltage U_N	250 V AC
Max. total current of all branches	16 A

Air clearances and creepage distances

Rated insulation voltage	250 V
Rated surge voltage	2.2 kV (1.2/50 μ s)

Connection data

COMBICON connection

Connection method	Screw connection
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Dimensions

Item dimensions

Width	30 mm
Height	77.5 mm
Depth	60 mm

Material specifications

Color	green (RAL 6021)
-------	------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Degree of protection (Installation location)	\geq IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 45 °C
Altitude	max. 2000 m

Standards and regulations

Air clearances and creepage distances

EMG 30-S2/16A - Switching module



2944533

<https://www.phoenixcontact.com/us/products/2944533>

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

EMG 30-S2/16A - Switching module



2944533

<https://www.phoenixcontact.com/us/products/2944533>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2944533>



EAC

Approval ID: RU*DE*08.B.01841/19

EMG 30-S2/16A - Switching module



2944533

<https://www.phoenixcontact.com/us/products/2944533>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 10.0	EC002780
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

EMG 30-S2/16A - Switching module



2944533

<https://www.phoenixcontact.com/us/products/2944533>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	4be0dd03-ea9d-4a9e-b95d-11b14fd956ee

EF3.1 Climate Change

CO2e kg	0.384 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com