

# IB IL 24 PSDOR 4-PAC - Safety module



2985864

<https://www.phoenixcontact.com/us/products/2985864>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safety-related decentralized relay output module, IP20 degree of protection, for SafetyBridge, INTERBUS-Safety, and PROFIsafe systems. The module has four safe relay outputs, each with two contacts.

## Product description

The safety module is an output module from the Inline product range designed for use at any point within a SafetyBridge, INTERBUS-Safety or PROFIsafe system. The transmission speed can be set to 500 kBaud or 2 Mbaud on the safety module using a switch. One transmission speed must be used consistently within a station. The module has four safe relay outputs, each with two relay contacts.

## Your advantages

- SIL 3 according to IEC/EN 61508
- SIL 3 in accordance with EN IEC 62061
- PL e in accordance with EN ISO 13849-1

## Commercial data

Item number	2985864
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN03
Product key	DNA432
GTIN	4046356131599
Weight per piece (including packing)	461.5 g
Weight per piece (excluding packing)	386 g
Customs tariff number	85389091
Country of origin	DE

## Technical data

### Dimensions

Width	73.2 mm
Height	119.8 mm
Depth	71.5 mm
Note on dimensions	Housing dimensions

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Material specifications

Color (Housing)	yellow (RAL 1018)
-----------------	-------------------

### Interfaces

#### Inline local bus

No. of channels	2
Connection method	Inline data jumper
Transmission speed	500 kbps / 2 Mbps (can be switched)

### System properties

#### Programming data (LocalbusSlave)

Length code (hex)	04
ID code (dec.)	167
Length code (dec)	04
Process data channel	8 Byte ((Operating mode: SafetyBridge))
Input address area	8 Byte ((Operating mode: SafetyBridge))
Output address area	8 Byte ((Operating mode: SafetyBridge))
Parameter channel (PCP)	0 Byte ((Operating mode: SafetyBridge))
Register length (bus)	8 Byte ((Operating mode: SafetyBridge))

#### Fieldbus data telegram

Required parameter data	1 Byte ((Operating mode: SafetyBridge))
Required configuration data	5 Byte ((Operating mode: SafetyBridge))

### Output data

#### Relay

Number of outputs	4 (Safety relays with 2 floating contacts each)
Connection method	Spring-cage connection
Contact switching type	N/O contact

# IB IL 24 PSDOR 4-PAC - Safety module



2985864

<https://www.phoenixcontact.com/us/products/2985864>

## Product properties

Product type	I/O component
Product family	Inline
Application	Functional safety PROFIsafe
Type	modular

## Electrical properties

Transmission medium	Copper
---------------------	--------

### Potentials: Communications power ( $U_L$ )

Supply voltage	7.5 V DC (see safety data)
Current draw	max. 360 mA

### Potentials: Main circuit supply ( $U_M$ )

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 0.03 A typ. 30 mA (all outputs set including actuator current)

### Potentials: Segment circuit supply ( $U_S$ )

Supply voltage	24 V
----------------	------

### Supply: Module electronics

Supply voltage	24 V DC (via voltage jumper)
Supply voltage range	19.2 V DC ... 30 V DC

### Electrical isolation/isolation of the voltage ranges

Test voltage: 5 V supply, incoming remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 5 V supply, outgoing remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 7.5 V supply (bus logics)/24 V supply (I/O)	500 V AC, 50 Hz, 1 min
Test voltage: 24 V supply ( $U_M$ , $U_S$ ), GND, clock outputs/7.5 V supply (bus logic), relay outputs	500 V AC, 50 Hz, 1 min
Test voltage: COMBICON X3 relay outputs/COMBICON X4 relay outputs, Inline connector relay outputs, 7.5 V supply (bus logic), 24 V supply ( $U_M$ , $U_S$ ), GND, clock outputs, FE	2500 V AC, 50 Hz, 1 min
Test voltage: COMBICON X4 relay outputs/COMBICON X3 relay outputs, Inline connector relay outputs, 7.5 V supply (bus logic), 24 V supply ( $U_M$ , $U_S$ ), GND, clock outputs,	2500 V AC, 50 Hz, 1 min

## Connection data

### Connection technology

Connection name	Inline connector
pluggable	yes

### Inline connector

2985864

<https://www.phoenixcontact.com/us/products/2985864>

Connection method	Spring-cage connection
pluggable	yes
Conductor cross-section, rigid	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 16

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	80 kPa ... 108 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (up to 3500 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	10 % ... 85 % (Take suitable measures against increased air humidity within the permitted temperature range.)
Permissible humidity (storage/transport)	10 % ... 85 % (Take suitable measures against increased air humidity within the permitted temperature range.)

## Standards and regulations


Protection class	I (IEC 61140, EN 61140, VDE 0140-1)
------------------	-------------------------------------

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

Drawings

Connection diagram



Example connection of a contactor

2985864

<https://www.phoenixcontact.com/us/products/2985864>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2985864>



**cULus Listed**

Approval ID: E140324

**PROFIsafe**

Approval ID: Z20211



**Functional Safety**

Approval ID: 968/FSP 2449.00/22

2985864

<https://www.phoenixcontact.com/us/products/2985864>

## Classifications

### ECLASS

ECLASS-13.0	27242604
ECLASS-15.0 ASSET	27250101
ECLASS-15.0	27242604

### ETIM

ETIM 10.0	EC001599
-----------	----------

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

2985864

<https://www.phoenixcontact.com/us/products/2985864>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	5baf3f4-7fc1-4e11-acb1-6ed436545098

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)