

FL SWITCH SMCS 8TX-PN - Industrial Ethernet Switch



2989103

<https://www.phoenixcontact.com/us/products/2989103>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ethernet Smart Managed Compact Switch with eight 10/100 Mbps RJ45 ports, PROFINET mode (default)

Product description

The Smart Managed Compact Switch (SMCS) is an Ethernet switch suitable for industrial applications with eight Fast Ethernet ports in RJ45 format. The switch has "PROFINET" mode activated by default.

Your advantages

- VLANs
- SNMP
- MRP (client and manager)
- RSTP
- Web-based management, SNMP

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2989103 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | DN17 |
| Product key | DNN122 |
| GTIN | 4046356320757 |
| Weight per piece (including packing) | 730 g |
| Weight per piece (excluding packing) | 650 g |
| Customs tariff number | 85176200 |
| Country of origin | DE |

FL SWITCH SMCS 8TX-PN - Industrial Ethernet Switch



2989103

<https://www.phoenixcontact.com/us/products/2989103>

Technical data

Dimensions

| | |
|--------|--------|
| Width | 128 mm |
| Height | 110 mm |
| Depth | 69 mm |

Material specifications

| | |
|-------|---------------|
| Color | gray aluminum |
|-------|---------------|

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

Interfaces

Ethernet (RJ45)

| | |
|-------------------------------|--|
| Connection method | RJ45 |
| Note on the connection method | Auto negotiation and autocrossing |
| Transmission speed | 10/100 Mbps |
| Transmission physics | Copper |
| Transmission length | 100 m (per segment) |
| Signal LEDs | Supply voltage, data transmission, error, link, activity |
| No. of channels | 8 (RJ45 ports) |

Serial (RS-232)

| | |
|-------------------|---|
| Connection method | RS-232-C, 6-pos. MINI-DIN socket (PS/2) |
|-------------------|---|

Product properties

| | |
|----------------|---------------------|
| Product type | Switch |
| Product family | Managed Switch SMCS |
| Type | Block design |

Insulation characteristics

| | |
|------------------|----------------|
| Protection class | III (VDE 0106) |
|------------------|----------------|

Switch functions

| | |
|--------------------------------|--|
| Diagnostic functions | RMON History |
| | N:1-Portmirroring |
| | LLDP (Link Layer Discovery Protocol) |
| | SNMP-Traps |
| Basic functions | ACD (Address Conflict Detection) |
| | Store-and-forward switch complies with IEEE 802.3 4 priority classes in acc. with IEEE 802.1 P TCP/IP protocol, BootP-capable, port-mirroring, integrated web server function, multicast filtering, IGMP snooping, VLAN, Rapid Spanning Tree (RSTP), PROFINET Device, Media Redundancy Protocol (MRP). |
| Signal contact control voltage | 24 V (typical) |

FL SWITCH SMCS 8TX-PN - Industrial Ethernet Switch



2989103

<https://www.phoenixcontact.com/us/products/2989103>

| | |
|----------------------------------|--|
| Signal contact control current | 600 mA |
| PROFINET conformance class | Conformance Class B |
| PROFINET device function | PROFINET device Fast Startup |
| Filter functions | Quality of Service (4 priority classes) Port-Priorisierung VLAN IGMP Snooping (128 groups) IGMP Query Auto-Query-Port Extended Multicast Filtering Static Multicast Filtering |
| MAC address table | 4000 |
| Management | Web-based management (HTTP) SNMP v1/v2 Serial interface (V.24) |
| Redundancy | MRP (Media Redundancy Protocol) RSTP (Rapid Spanning Tree Protocol) FRD (Fast Ring Detection) Large Tree Support |
| Status and diagnostic indicators | LEDs: US1, US2 (power supply), Fail (alarm contact), 2 LEDs per Ethernet port (Link and switchable Activity/Speed/Duplex) |
| Supported browsers | Internet Explorer 5.5 or higher |
| Additional functions | BootP DHCP-Client |
| Time synchronization | SNTP |

Security functions

| | |
|--------------------------------------|--|
| Basic functions | Store-and-forward switch complies with IEEE 802.3 4 priority classes in acc. with IEEE 802.1 P TCP/IP protocol, BootP-capable, port-mirroring, integrated web server function, multicast filtering, IGMP snooping, VLAN, Rapid Spanning Tree (RSTP), PROFINET Device, Media Redundancy Protocol (MRP). |
| Link Layer Discovery Protocol (LLDP) | As per protocol 802.2 |

Electrical properties

| | |
|---|--|
| Current consumption | 600 mA |
| Local diagnostics | US1/2 Supply voltage US1, US2 Green LED FAIL Div. LED red LINK Link status Green LED ACT/MODE Receiving/sending telegrams Green LED SPD/MODE Data transmission speed Green/orange LED FD/MODE Duplex mode Green LED |
| Maximum power dissipation for nominal condition | 14.4 W |
| Test section | 500 V DC 1 min |
| Transmission medium | Copper |

FL SWITCH SMCS 8TX-PN - Industrial Ethernet Switch



2989103

<https://www.phoenixcontact.com/us/products/2989103>

Supply

| | |
|-----------------------------|--|
| Supply voltage (DC) | 24 V DC (redundant) |
| Supply voltage range | 18 V DC ... 32 V DC |
| Power supply connection | Via COMBICON, max. conductor cross-section 2.5 mm ² |
| Residual ripple | 3.6 V _{PP} (within the permitted voltage range) |
| Typical current consumption | 240 mA (at U _S = 24 V DC) |
| Current consumption | 600 mA |

Function

| | |
|--------------------------------|----------------|
| Signal contact control voltage | 24 V (typical) |
| Signal contact control current | 600 mA |

Connection data

| | |
|-----------------------------------|---|
| Connection method | Screw connection |
| Conductor cross-section, rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |
| Stripping length | 7 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|--|--|
| Degree of protection | IP20 |
| Ambient temperature (operation) | 0 °C ... 60 °C (non-condensing) |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Permissible humidity (operation) | 5 % ... 95 % (non-condensing) |
| Permissible humidity (storage/transport) | 5 % ... 95 % (non-condensing) |
| Vibration (operation) | in accordance with IEC 60068-2-6: 5g, 10 Hz ... 150 Hz |
| Air pressure (operation) | 86 kPa ... 108 kPa (2000 m above mean sea level) |
| Air pressure (storage/transport) | 66 kPa ... 108 kPa (3500 m above sea level) |

Standards and regulations

| | |
|---|-----|
| Free from substances that could impair the application of coating | Yes |
|---|-----|

EMC data

| | |
|---------------------------------|--|
| Electromagnetic compatibility | Conformance with EMC Directive 2014/30/EU |
| Conformance with EMC directives | IEC 61000-6-2 IEC 61000-4-2 (ESD) Criterion A |
| | IEC 61000-4-3 (electromagnetic fields) Criterion A |
| | IEC 61000-4-4 (burst) Criterion A |
| | IEC 61000-4-5 (surge) Criterion A |
| | IEC 61000-4-6 (immunity to conducted interference) Criterion A |
| Noise immunity | EN 61000-6-2:2005 |

Noise emission

| | |
|-----------------------|-------------------|
| Standards/regulations | EN 61000-6-3 +A11 |
|-----------------------|-------------------|

FL SWITCH SMCS 8TX-PN - Industrial Ethernet Switch



2989103

<https://www.phoenixcontact.com/us/products/2989103>

System properties

Functionality

| | |
|-----------------|--|
| Basic functions | Store-and-forward switch complies with IEEE 802.3 4 priority classes in acc. with IEEE 802.1 P TCP/IP protocol, BootP-capable, port-mirroring, integrated web server function, multicast filtering, IGMP snooping, VLAN, Rapid Spanning Tree (RSTP), PROFINET Device, Media Redundancy Protocol (MRP). |
|-----------------|--|

System requirements

| | |
|--------------------|---------------------------------|
| Supported browsers | Internet Explorer 5.5 or higher |
|--------------------|---------------------------------|

Signaling

| | |
|----------------|---|
| Status display | LEDs: US1, US2 (power supply), Fail (alarm contact), 2 LEDs per Ethernet port (Link and switchable Activity/Speed/Duplex) |
|----------------|---|

FL SWITCH SMCS 8TX-PN - Industrial Ethernet Switch



2989103

<https://www.phoenixcontact.com/us/products/2989103>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43222612 |
|-------------|----------|

FL SWITCH SMCS 8TX-PN - Industrial Ethernet Switch



2989103

<https://www.phoenixcontact.com/us/products/2989103>

Environmental product compliance

EU RoHS

| | |
|---|----------------------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(a)-I, 6(c), 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
|-------------------------------------|----------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com