

# EMG 45-DIO 8M-1N5408 - Diode block

2954882

<https://www.phoenixcontact.com/us/products/2954882>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Diode module, with eight diodes, common anode, diode type 1N 5408

## Your advantages

- Electrical decoupling of messages in fault reporting systems
- Spark-suppression diodes for limiting surge voltages of inductive loads

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2954882       |
| Packing unit                         | 5 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | C440          |
| Product key                          | DK66M1        |
| GTIN                                 | 4017918085162 |
| Weight per piece (including packing) | 91.09 g       |
| Weight per piece (excluding packing) | 91.09 g       |
| Customs tariff number                | 85411000      |
| Country of origin                    | DE            |

# EMG 45-DIO 8M-1N5408 - Diode block



2954882

<https://www.phoenixcontact.com/us/products/2954882>

## Technical data

### Product properties

|              |              |
|--------------|--------------|
| Product type | Diode module |
|--------------|--------------|

### Insulation characteristics

|                  |   |
|------------------|---|
| Pollution degree | 2 |
|------------------|---|

### Input data

#### Diode

|                                    |   |
|------------------------------------|---|
| Description of the input           | 8 diodes, common anode                                      |
| Diode type                         | 1 N 5408  |
| Max. operating voltage $U_{max}$   | 250 V AC  |
| Peak reverse voltage per diode     | 1000 V  |
| Reverse current per diode          | 10 $\mu$ A  |
| Conducting state voltage per diode | approx. 0.8 V   |
| Conducting state current per diode | 1.5 A (with single load)<br>0.3 A (with simultaneous loads) |

### Connection data

|                                  |   |
|----------------------------------|---|
| Connection method                | Screw connection                            |
| Stripping length                 | 8 mm  |
| Screw thread                     | M3  |
| Conductor cross-section rigid    | 0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross-section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section AWG      | 24 ... 12                                   |

### Dimensions

|        |       |
|--------|-------|
| Width  | 45 mm |
| Height | 75 mm |
| Depth  | 55 mm |

### Material specifications

|       |                  |
|-------|------------------|
| Color | green (RAL 6021) |
|-------|------------------|

### Environmental and real-life conditions

#### Ambient conditions

|   |                  |
|---|------------------|
| Ambient temperature (operation)         | -20 °C ... 50 °C |
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |

### Approvals

#### CE

|             |              |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

# EMG 45-DIO 8M-1N5408 - Diode block



2954882

<https://www.phoenixcontact.com/us/products/2954882>

|      |              |
|------|--------------|
| Note | and EN 61326 |
|------|--------------|

## Standards and regulations

|                       |              |
|-----------------------|--------------|
| Standards/regulations | DIN EN 50178 |
|-----------------------|--------------|

## Mounting

|                   |                           |
|-------------------|---------------------------|
| Mounting type     | DIN rail mounting         |
| Assembly note     | in rows with zero spacing |
| Mounting position | any                       |

# EMG 45-DIO 8M-1N5408 - Diode block



2954882

<https://www.phoenixcontact.com/us/products/2954882>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2954882>



**EAC**

Approval ID: RU\*DE\*08.B.01841/19

# EMG 45-DIO 8M-1N5408 - Diode block



2954882

<https://www.phoenixcontact.com/us/products/2954882>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27371010 |
| ECLASS-15.0 | 27371010 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000683 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 32151500 |
|-------------|----------|

# EMG 45-DIO 8M-1N5408 - Diode block



2954882

<https://www.phoenixcontact.com/us/products/2954882>

## Environmental product compliance

### EU RoHS

|   |      |
|---|------|
| Fulfills EU RoHS substance requirements | Yes  |
| Exemption                               | 7(a) |

### China RoHS

|  |   |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50   |
|  | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

### EU REACH SVHC

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1)                 |
| SCIP                                | 137e52a0-09f7-44ec-832a-552e9c24f986 |

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 1.332 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)