

# UM108-SEFE/R - Lateral element



2959683

<https://www.phoenixcontact.com/us/products/2959683>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Side element with foot, 5 mm wide (right), for mounting on NS 32 or NS 35/7.5. PCB width: 107.5 mm



## Your advantages

- Easy installation
- Flexible size and shape
- Inexpensive as a result of reducing the number of separate housing parts

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2959683       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | AC13          |
| Product key                          | ACHDBA        |
| GTIN                                 | 4017918086336 |
| Weight per piece (including packing) | 9.15 g        |
| Weight per piece (excluding packing) | 8.98 g        |
| Customs tariff number                | 39269097      |
| Country of origin                    | PL            |

# UM108-SEFE/R - Lateral element



2959683

<https://www.phoenixcontact.com/us/products/2959683>

## Technical data

### Product properties

|                              |                               |
|------------------------------|-------------------------------|
| Product type                 | Panel mounting base side part |
| Housing type                 | Press-drawn section housings  |
| Housing series               | UM                            |
| Product family               | UM108                         |
| Ventilation openings present | no                            |

### Dimensions

|        |          |
|--------|----------|
| Width  | 5 mm     |
| Height | 125.4 mm |
| Depth  | 37.6 mm  |

### Material specifications

|  |                  |
|--|------------------|
| Color (Side element)                   | green (RAL 6021) |
| Material Lateral element               | PA               |
| Flammability rating according to UL 94 | V0               |

### Environmental and real-life conditions

#### Ambient conditions

|   |  |
|---|--|
| Ambient temperature (operation)         | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C                                   |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                   |
| Relative humidity (storage/transport)   | 80 %   |

### Mounting

|               |   |
|---------------|---|
| Mounting type | DIN rail mounting, screw connection with extruded profile |
|---------------|---|

### Packaging specifications

|                      |                     |
|----------------------|---------------------|
| Type of packaging    | packed in cardboard |
| Outer packaging type | Carton              |

# UM108-SEFE/R - Lateral element



2959683

<https://www.phoenixcontact.com/us/products/2959683>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2959683>



**UL Recognized**

Approval ID: E240868

# UM108-SEFE/R - Lateral element



2959683

<https://www.phoenixcontact.com/us/products/2959683>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27190602 |
| ECLASS-15.0 | 27190602 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# UM108-SEFE/R - Lateral element



2959683

<https://www.phoenixcontact.com/us/products/2959683>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.258 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)