

# EMG 10-REL/KSR-230/21-LC AU - Relay module



2964393

<https://www.phoenixcontact.com/us/products/2964393>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Relay module, with soldered-in miniature switching relay, gold contact for small loads, 1 changeover contact, input voltage 230 V AC/DC

## Your advantages

- Integrated input circuit and interference suppression circuit

## Commercial data

Item number	2964393
Packing unit	10 pc
Minimum order quantity	1 pc
Product key	DK61C2
GTIN	4017918107451
Weight per piece (including packing)	41.62 g
Weight per piece (excluding packing)	41.62 g
Country of origin	DE

# EMG 10-REL/KSR-230/21-LC AU - Relay module



2964393

<https://www.phoenixcontact.com/us/products/2964393>

## Technical data

### Notes

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

### Product properties

Product type	Relay Module
Product family	EMG
Application	Universal
Operating mode	100% operating factor
Mechanical service life	approx. $2 \times 10^7$ cycles

#### Insulation characteristics

Insulation	Basic insulation
Overvoltage category	III
Pollution degree	2

#### Data management status

Date of last data management	01.04.2026
------------------------------	------------

### Electrical properties

Maximum power dissipation for nominal condition	1.15 W
Test voltage (Winding/contact)	4 kV AC (50 Hz, 1 min., winding/contact)

### Input data

#### Coil side

Nominal input voltage $U_N$	230 V AC/DC
Input voltage range	184 V AC/DC ... 253 V AC/DC (20 °C)
Drive and function	monostable
Drive (polarity)	polarized
Typical input current at $U_N$	5 mA
Typical response time	7 ms
Typical release time	11 ms
Protective circuit	Bridge rectifier; Bridge rectifier Surge protection; Varistor
Operating voltage display	Yellow LED

### Output data

#### Switching

Contact switching type	1 changeover contact
Type of switch contact	Double contact

# EMG 10-REL/KSR-230/21-LC AU - Relay module



2964393

<https://www.phoenixcontact.com/us/products/2964393>

Contact material	AgPd60, hard gold-plated
Maximum switching voltage	30 V AC
	36 V DC
Limiting continuous current	0.5 A
Maximum inrush current	0.2 A
Interrupting rating (ohmic load) max.	5 W (at 24 V DC)

Switching: when the gold layer is destroyed

Note	the following values are applicable if a gold layer is destroyed
Maximum switching voltage	125 V AC
	150 V DC
Limiting continuous current	2 A
Maximum inrush current	2 A
Interrupting rating (ohmic load) max.	29 W (at 24 V DC)
	29 W (at 48 V DC)
	29 W (at 60 V DC)
	60 VA (for 250 V AC)

## Connection data

Coil side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

Contact side

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross-section rigid	0.2 mm <sup>2</sup> ... 4 mm <sup>2</sup>
Conductor cross-section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

## Dimensions

Item dimensions

Width	10.6 mm
Height	75 mm
Depth	62.5 mm

## Material specifications

Color	green (RAL 6021)
-------	------------------

# EMG 10-REL/KSR-230/21-LC AU - Relay module



2964393

<https://www.phoenixcontact.com/us/products/2964393>

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 40 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

## Standards and regulations

Standards/regulations	IEC 60664
	EN 50178

## Mounting

Mounting type	DIN rail mounting
Assembly note	in rows with zero spacing
Mounting position	any

# EMG 10-REL/KSR-230/21-LC AU - Relay module

2964393

<https://www.phoenixcontact.com/us/products/2964393>



## Drawings

Connection diagram



# EMG 10-REL/KSR-230/21-LC AU - Relay module



2964393

<https://www.phoenixcontact.com/us/products/2964393>

Circuit diagram



# EMG 10-REL/KSR-230/21-LC AU - Relay module



2964393

<https://www.phoenixcontact.com/us/products/2964393>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2964393>



**cUL Recognized**

Approval ID: E238705



**UL Recognized**

Approval ID: E238705



**EAC**

Approval ID: RU\*C-DE.\*08.B.00010

# EMG 10-REL/KSR-230/21-LC AU - Relay module



2964393

<https://www.phoenixcontact.com/us/products/2964393>

## Classifications

### ECLASS

ECLASS-13.0	27371601
ECLASS-15.0	27371601

### ETIM

ETIM 10.0	EC001437
-----------	----------

### UNSPSC

UNSPSC 21.0	39122300
-------------	----------

2964393

<https://www.phoenixcontact.com/us/products/2964393>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Hexahydromethylphthalic anhydride(CAS: n/a)
	Lead(CAS: 7439-92-1)
SCIP	1a7d53af-3283-4108-a601-c2a31d57f48d

### EF3.1 Climate Change

CO2e kg	0.356 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)