

PT 2X10/9X4 BU - Potential collective terminal



3002368

<https://www.phoenixcontact.com/us/products/3002368>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Potential collective terminal, nom. voltage: 1000 V, nominal current: 57 A, Line contact, connection method: Push-in connection, Rated cross section: 10 mm², cross section: 0.5 mm² - 16 mm², Load contact, connection method: Push-in connection, Rated cross section: 4 mm², cross section: 0.5 mm² - 6 mm², mounting: NS 35/7,5, color: blue

Commercial data

Item number	3002368
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BE22
Product key	BE2219
GTIN	4055626431079
Weight per piece (including packing)	49.98 g
Weight per piece (excluding packing)	46.1 g
Customs tariff number	85369010
Country of origin	IN

PT 2X10/9X4 BU - Potential collective terminal



3002368

<https://www.phoenixcontact.com/us/products/3002368>

Technical data

Product properties

Product type	Potential distributor
Product family	PT
Number of connections	11
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	1.02 W

Connection data

Number of connections per level	11
Nominal cross section	4 mm ²

Line contact

Connection method	Push-in connection
Stripping length	20 mm
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	0.5 mm ² ... 16 mm ²
Cross section AWG	20 ... 6 (converted acc. to IEC)
Conductor cross-section flexible	0.5 mm ² ... 10 mm ²
Conductor cross-section, flexible [AWG]	20 ... 8 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.5 mm ² ... 10 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.5 mm ² ... 10 mm ²
Nominal cross section	10 mm ²
Nominal current	57 A
Maximum load current	101 A (with 2x10 mm ² conductor cross-section)
Nominal voltage	1000 V

Load contact

Connection method	Push-in connection
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	0.5 mm ² ... 6 mm ²
Cross section AWG	20 ... 10 (converted acc. to IEC)
Conductor cross-section flexible	0.5 mm ² ... 4 mm ²
Conductor cross-section, flexible [AWG]	20 ... 12 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.5 mm ² ... 4 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.5 mm ² ... 4 mm ²

PT 2X10/9X4 BU - Potential collective terminal



3002368

<https://www.phoenixcontact.com/us/products/3002368>

2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ² ... 1 mm ²
Nominal cross section	4 mm ²
Nominal current	32 A
Maximum load current	36 A (with 6 mm ² conductor cross-section)
Nominal voltage	1000 V

Line contact Connection cross sections directly pluggable

Conductor cross-section rigid	1 mm ² ... 16 mm ²
Conductor cross-section flexible (ferrule without plastic sleeve)	0.5 mm ² ... 10 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.5 mm ² ... 10 mm ²

Load contact Connection cross sections directly pluggable

Conductor cross-section rigid	0.5 mm ² ... 6 mm ²
Conductor cross-section flexible (ferrule without plastic sleeve)	0.5 mm ² ... 4 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.5 mm ² ... 4 mm ²

Dimensions

Width	18.5 mm
Height	83.2 mm
Depth	42.4 mm
Depth on NS 35/7,5	47.9 mm

Material specifications

Color	blue (RAL 5015)
Flammability rating according to UL 94	PA 6.6
Insulating material group	I
Insulating material	PA

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

PT 2X10/9X4 BU - Potential collective terminal



3002368

<https://www.phoenixcontact.com/us/products/3002368>

Connection in acc. with standard	IEC 60947-7-1
	IEC 60947-7-1

Mounting

Mounting type	NS 35/7,5
---------------	-----------

PT 2X10/9X4 BU - Potential collective terminal




3002368

<https://www.phoenixcontact.com/us/products/3002368>

Drawings

Circuit diagram



PT 2X10/9X4 BU - Potential collective terminal




3002368

<https://www.phoenixcontact.com/us/products/3002368>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3002368>

 cULus Recognized Approval ID: E60425		Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B					
Output		600 V	25 A	20 - 10	-
Input		600 V	50 A	20 - 8	-
C					
Output		600 V	25 A	20 - 10	-
Input		600 V	50 A	20 - 8	-
F					
Output		1000 V	25 A	20 - 10	-
Input		1000 V	50 A	20 - 8	-

 EAC Approval ID: KZ7500651131219505	
---	--

PT 2X10/9X4 BU - Potential collective terminal



3002368

<https://www.phoenixcontact.com/us/products/3002368>

Classifications

ECLASS

ECLASS-13.0	27250119
ECLASS-15.0	27250119

ETIM

ETIM 10.0	EC000897
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PT 2X10/9X4 BU - Potential collective terminal



3002368

<https://www.phoenixcontact.com/us/products/3002368>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com