


PT 4-PE/L/N - Multi-level terminal block



3002614

<https://www.phoenixcontact.com/us/products/3002614>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Multi-level terminal block, nom. voltage: 500 V, nominal current: 30 A, number of connections: 5, connection method: Push-in connection, Rated cross section: 4 mm², cross section: 0.2 mm² - 6 mm², connection method: Push-in connection, Rated cross section: 4 mm², cross section: 0.2 mm² - 6 mm², mounting type: NS 35/7,5, NS 35/15, color: gray

Your advantages

- Time-saving conductor connection thanks to tool-free direct-connection technology
- Vibration-resistant and maintenance-free conductor connection
- Full flexibility thanks to the standardized CLIPLINE complete bridging, marking, and testing accessories
- Meet the requirements of DIN EN 60947-7-2 or IEC 60947-7-2 for protective conductor connections
- High level of safety thanks to the low-resistance connection to the ground potential via the top-hat rail
- Direct contacting with the DIN rail enables fast, error-free grounding without additional wiring effort.

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3002614 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BE22 |
| Product key | BE2225 |
| GTIN | 4055626370279 |
| Weight per piece (including packing) | 30.128 g |
| Weight per piece (excluding packing) | 28 g |
| Customs tariff number | 85369010 |
| Country of origin | IN |

PT 4-PE/L/N - Multi-level terminal block



3002614

<https://www.phoenixcontact.com/us/products/3002614>

Technical data

Product properties

| | |
|-----------------------|-----------------------|
| Product type | Ground terminal block |
| Product family | PT |
| Number of connections | 5 |
| Number of rows | 3 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---|--------|
| Rated surge voltage | 6 kV |
| Maximum power dissipation for nominal condition | 1.02 W |

Connection data

| | |
|---------------------------------|-------------------|
| Grounding foot | Yes |
| Number of connections per level | 2 |
| Nominal cross section | 4 mm ² |

Level 1

| | |
|---|--|
| Connection method | Push-in connection |
| Stripping length | 10 mm ... 12 mm |
| Internal cylindrical gage | A4 |
| Connection in acc. with standard | IEC 60947-7-3 |
| Conductor cross-section rigid | 0.2 mm ² ... 6 mm ² |
| Cross section AWG | 24 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.2 mm ² ... 6 mm ² |
| Conductor cross-section, flexible [AWG] | 24 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible ultrasound-compressed | 0.34 mm ² ... 6 mm ² |
| Conductor cross-section, flexible [AWG] ultrasound-compressed | 22 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.25 mm ² ... 4 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.25 mm ² ... 4 mm ² |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm ² ... 1 mm ² |
| Nominal cross section | 4 mm ² |
| Nominal current | 30 A |
| Maximum load current | 32 A (with 6 mm ² conductor cross-section, rigid) |
| Nominal voltage | 500 V |

Level 2

| | |
|----------------------------------|--------------------|
| Connection method | Push-in connection |
| Stripping length | 10 mm ... 12 mm |
| Connection in acc. with standard | IEC 60947-7-3 |

PT 4-PE/L/N - Multi-level terminal block



3002614

<https://www.phoenixcontact.com/us/products/3002614>

| | |
|---|--|
| Conductor cross-section rigid | 0.2 mm ² ... 6 mm ² |
| Cross section AWG | 24 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section, flexible [AWG] | 24 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.25 mm ² ... 4 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.25 mm ² ... 4 mm ² |
| Conductor cross-section flexible (2 conductors with the same cross-section, with TWIN ferrule and plastic sleeve) | 0.5 mm ² ... 1 mm ² |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm ² ... 1 mm ² |
| Nominal cross section | 4 mm ² |
| Nominal current | 20 A |
| Maximum load current | 20 A |
| Nominal voltage | 500 V |

Level 1 Connection cross sections directly pluggable

| | |
|---|---|
| Conductor cross-section rigid | 0.5 mm ² ... 6 mm ² |
| Conductor cross-section, rigid [AWG] | 20 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.5 mm ² ... 4 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.5 mm ² ... 4 mm ² |

Level 2 Connection cross sections directly pluggable

| | |
|---|---|
| Conductor cross-section rigid | 0.5 mm ² ... 6 mm ² |
| Conductor cross-section, rigid [AWG] | 20 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.5 mm ² ... 4 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.5 mm ² ... 4 mm ² |

Ex data

Rated data (ATEX/IECEx)

| | |
|--|--|
| Identification | Ⓔ II 3 G Ex ec IIC Gc |
| Operating temperature range | -60 °C ... 125 °C |
| Ex-certified accessories | 3002619 D-PT 4-PE/L/HESI 1205066 SZS 1,0X4,0 VDE 3022276 CLIPFIX 35-5 3022218 CLIPFIX 35 |
| List of bridges | Plug-in bridge / FBS 2-6 / 3030336 Plug-in bridge / FBS 3-6 / 3030242 Plug-in bridge / FBS 4-6 / 3030255 Plug-in bridge / FBS 5-6 / 3030349 Plug-in bridge / FBS 10-6 / 3030271 Plug-in bridge / FBS 20-6 / 3030365 |
| Bridge data | 28 A / 4 mm ² 19 A / 4 mm ² |
| for bridging with bridge | 275 V |
| - At bridging between non-adjacent terminal blocks | 275 V |

PT 4-PE/L/N - Multi-level terminal block



3002614

<https://www.phoenixcontact.com/us/products/3002614>

| | |
|--|-------------|
| - At cut-to-length bridging with cover | 275 V |
| Rated insulation voltage | 250 V |
| output | (Permanent) |

Ex level General

| | |
|---------------|-------|
| Rated voltage | 275 V |
|---------------|-------|

Ex connection data General

| | |
|------------------------------|---|
| Nominal cross section | 4 mm ² |
| Rated cross section AWG | 12 |
| Connection capacity rigid | 0.2 mm ² ... 6 mm ² |
| Connection capacity AWG | 24 ... 10 |
| Connection capacity flexible | 0.2 mm ² ... 4 mm ² |
| Connection capacity AWG | 24 ... 12 |
| output | (Permanent) |

Ex level Level 2

| | |
|----------------------|--------------------------------|
| Rated current | 29 A (4 mm ²) |
| Maximum load current | 32 A (6 mm ²) |
| Contact resistance | 0.9 mΩ |
| Temperature increase | 40 K (29 A/4 mm ²) |
| output | (Permanent) |

Ex level Level 3

| | |
|----------------------|--------------------------------|
| Rated current | 20 A (4 mm ²) |
| Maximum load current | 20 A (6 mm ²) |
| Contact resistance | 1.7 mΩ |
| Temperature increase | 35 K (20 A/4 mm ²) |

Dimensions

| | |
|--------------------|----------|
| Width | 6.2 mm |
| Height | 119.5 mm |
| Depth | 54.5 mm |
| Depth on NS 35/7,5 | 56 mm |
| Depth on NS 35/15 | 63.5 mm |

Material specifications

| | |
|---|-----------------|
| Color | gray (RAL 7042) |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |

PT 4-PE/L/N - Multi-level terminal block



3002614

<https://www.phoenixcontact.com/us/products/3002614>

| | |
|---|-------------|
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Calorimetric heat release NFPA 130 (ASTM E 1354) | 28 MJ/kg |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Mechanical properties

Mechanical data

| | |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

Environmental and real-life conditions

Oscillation/broadband noise

| | |
|------------------------|--|
| Specification | DIN EN 50155 (VDE 0115-200):2008-03 |
| Spectrum | Long life test category 1, class B, body mounted |
| Frequency | $f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$ |
| ASD level | $0.964 \text{ (m/s}^2\text{)}^2\text{/Hz}$ |
| Acceleration | 0.58g |
| Test duration per axis | 5 h |
| Test directions | X-, Y- and Z-axis |
| Result | Test passed |

Shocks

| | |
|--------------------------------|-------------------------------------|
| Specification | DIN EN 50155 (VDE 0115-200):2008-03 |
| Pulse shape | Half-sine |
| Acceleration | 5g |
| Shock duration | 30 ms |
| Number of shocks per direction | 3 |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |
| Result | Test passed |

Ambient conditions

| | |
|--|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Standards and regulations

| | |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-3 |
| | IEC 60947-7-3 |

PT 4-PE/L/N - Multi-level terminal block



3002614

<https://www.phoenixcontact.com/us/products/3002614>

Mounting

| | |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
| | NS 35/15 |

PT 4-PE/L/N - Multi-level terminal block




3002614

<https://www.phoenixcontact.com/us/products/3002614>

Drawings

Circuit diagram



PT 4-PE/L/N - Multi-level terminal block




3002614

<https://www.phoenixcontact.com/us/products/3002614>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3002614>

 **CSA**
Approval ID: 158887

 **EAC**
Approval ID: RU C-DE.BL08.B.00644


 **cULus Recognized**
Approval ID: E60425


| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|--------------|-----------------------|-----------------------|-------------------|-----------------------------|
| B | | | | |
| upper level | 300 V | 16 A | 24 - 10 | - |
| lower level | 300 V | - | 24 - 10 | - |
| middle level | 300 V | 20 A | 24 - 10 | - |
| C | | | | |
| upper level | 300 V | 16 A | 24 - 10 | - |
| lower level | 300 V | - | 24 - 10 | - |
| middle level | 300 V | 20 A | 24 - 10 | - |
| D | | | | |
| | 600 V | 5 A | 24 - 10 | - |

 **CSA**
Approval ID: 13631

 **cUL Recognized**
Approval ID: E192998

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|--------------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine | | | | |
| upper level | 275 V | 16 A | 24 - 10 | 24 - 10 |
| lower level | 275 V | 20 A | 24 - 10 | 24 - 10 |

 **IECEx**
Approval ID: IECExKIWA17.0025U

 **CCC**
Approval ID: 2020322313000626

PT 4-PE/L/N - Multi-level terminal block



3002614

<https://www.phoenixcontact.com/us/products/3002614>



ATEX

Approval ID: KIWA17ATEX0045U



UKCA-EX

Approval ID: CSAE 21UKEX3605U



EAC Ex

Approval ID: KZ 7500525010101950

PT 4-PE/L/N - Multi-level terminal block



3002614

<https://www.phoenixcontact.com/us/products/3002614>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250104 |
| ECLASS-15.0 | 27250104 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000901 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

PT 4-PE/L/N - Multi-level terminal block



3002614

<https://www.phoenixcontact.com/us/products/3002614>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|-------------|
| CO2e kg | 0.4 kg CO2e |
|---------|-------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com