


# PTFIX 6X1,5-NS15A VT - Distribution block



3002973

<https://www.phoenixcontact.com/us/products/3002973>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Distribution block, bridged internally, nom. voltage: 500 V, nominal current: 17.5 A, number of connections: 6, connection method: Push-in connection, cross section: 0.14 mm<sup>2</sup> - 2.5 mm<sup>2</sup>, mounting type: NS 15, color: violet

## Your advantages

- Space-saving, thanks to the compact design
- Flexible use, thanks to DIN rail and direct mounting
- Space-saving potential distribution, thanks to compact micro potential distributors
- Convenient test options, thanks to test openings at every terminal point
- Clear arrangement thanks to marking of all terminal points

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3002973       |
| Packing unit                         | 20 pc         |
| Minimum order quantity               | 20 pc         |
| Sales key                            | BE09          |
| Product key                          | BEA113        |
| GTIN                                 | 4055626433813 |
| Weight per piece (including packing) | 6.401 g       |
| Weight per piece (excluding packing) | 6.3 g         |
| Customs tariff number                | 85369010      |
| Country of origin                    | PL            |

# PTFIX 6X1,5-NS15A VT - Distribution block



3002973

<https://www.phoenixcontact.com/us/products/3002973>

## Technical data

### Notes

|                    |  |
|--------------------|--|
| Notes on operation | the blocks can be bridged with one another via the conductor shaft, for corresponding plug-in bridges, see accessories |
|--------------------|--|

### General

|      |  |
|------|--|
| Note | The maximum load current of a single clamping unit must not be exceeded. |
|------|--|

### Product properties

|                       |                            |
|-----------------------|----------------------------|
| Product type          | Distributor terminal block |
| Number of connections | 6                          |
| Number of rows        | 1                          |
| Potentials            | 1                          |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|   |        |
|---|--------|
| Rated surge voltage                             | 6 kV   |
| Maximum power dissipation for nominal condition | 0.56 W |

### Connection data

|   |  |
|---|--|
| Number of connections per level                                   | 6  |
| Nominal cross section   | 1.5 mm <sup>2</sup>                          |
| Rated cross section AWG   | 14   |
| Connection method   | Push-in connection                           |
| Stripping length  | 8 mm ... 10 mm                               |
| Internal cylindrical gage   | A1 / B1                                      |
| Connection in acc. with standard                                  | IEC 60947-7-1                                |
| Conductor cross-section rigid                                     | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Cross section AWG   | 26 ... 14 (converted acc. to IEC)            |
| Conductor cross-section flexible                                  | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section, flexible [AWG]                           | 26 ... 14 (converted acc. to IEC)            |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Nominal current   | 17.5 A                                       |
| Maximum load current  | 22 A   |
| Maximum total current   | 26 A   |
| Nominal voltage   | 500 V  |

### Connection cross sections directly pluggable

|                               |  |
|-------------------------------|--|
| Conductor cross-section rigid | 0.34 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
|-------------------------------|--|

# PTFIX 6X1,5-NS15A VT - Distribution block



3002973

<https://www.phoenixcontact.com/us/products/3002973>

|   |  |
|---|--|
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.34 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 0.34 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |

## Dimensions

|                |         |
|----------------|---------|
| Width          | 12.5 mm |
| Height         | 21.6 mm |
| Depth on NS 15 | 27.4 mm |

## Material specifications

|   |                   |
|---|-------------------|
| Color   | violet (RAL 4005) |
| Flammability rating according to UL 94                                  | V0                |
| Insulating material group   | I                 |
| Insulating material   | PA                |
| Static insulating material application in cold                          | -60 °C            |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 125 °C            |
| Relative insulation material temperature index (Elec., UL 746 B)        | 130 °C            |
| Fire protection for rail vehicles (DIN EN 45545-2) R22                  | HL 1 - HL 3       |
| Fire protection for rail vehicles (DIN EN 45545-2) R23                  | HL 1 - HL 3       |
| Fire protection for rail vehicles (DIN EN 45545-2) R24                  | HL 1 - HL 3       |
| Fire protection for rail vehicles (DIN EN 45545-2) R26                  | HL 1 - HL 3       |
| Calorimetric heat release NFPA 130 (ASTM E 1354)                        | 27,5 MJ/kg        |
| Surface flammability NFPA 130 (ASTM E 162)                              | passed            |
| Specific optical density of smoke NFPA 130 (ASTM E 662)                 | passed            |
| Smoke gas toxicity NFPA 130 (SMP 800C)                                  | passed            |

## Electrical tests

### Surge voltage test

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 7.3 kV      |
| Result                | Test passed |

### Temperature-rise test

|  |                                |
|--|--------------------------------|
| Requirement temperature-rise test                | Increase in temperature ≤ 45 K |
| Result   | Test passed                    |
| Short-time withstand current 1.5 mm <sup>2</sup> | 0.18 kA                        |
| Short-time withstand current 2.5 mm <sup>2</sup> | 0.3 kA                         |
| Result   | Test passed                    |

### Power-frequency withstand voltage

|                       |             |
|-----------------------|-------------|
| Test voltage setpoint | 1.89 kV     |
| Result                | Test passed |

## Mechanical properties

### Mechanical data

|                 |    |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

## Mechanical tests

### Mechanical strength

|        |             |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

### Attachment on the carrier

|                         |   |
|-------------------------|---|
| DIN rail/fixing support | NS 35/NS 15   |
| Test force setpoint     | 1 N   |
| Result                  | Test passed   |
| Note                    | <p>When aligning several blocks, it is recommended to either place a DIN rail adapter underneath the connection point or a flange element between the blocks.</p> <p>For versions with 6 or 7 connections, it is enough to place one DIN rail adapter centrally per block and place flange elements after every other block.</p> <p>When using the DIN rail adapter PTFIX-NS35, an aligned block must not protrude by more than a half.</p> |

### Test for conductor damage and slackening

|                                |                               |
|--------------------------------|-------------------------------|
| Rotation speed                 | 10 rpm                        |
| Revolutions                    | 135                           |
| Conductor cross-section/weight | 0.14 mm <sup>2</sup> / 0.2 kg |
|                                | 1.5 mm <sup>2</sup> / 0.4 kg  |
|                                | 2.5 mm <sup>2</sup> / 0.7 kg  |
| Result                         | Test passed                   |

## Environmental and real-life conditions

### Aging

|                    |             |
|--------------------|-------------|
| Temperature cycles | 192         |
| Result             | Test passed |

### Needle-flame test

|                  |             |
|------------------|-------------|
| Time of exposure | 30 s        |
| Result           | Test passed |

### Oscillation/broadband noise

|                        |  |
|------------------------|--|
| Specification          | DIN EN 50155 (VDE 0115-200):2018-05            |
| Spectrum               | Long life test category 2, bogie-mounted       |
| Frequency              | $f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$ |
| ASD level              | 6.12 (m/s <sup>2</sup> ) <sup>2</sup> /Hz      |
| Acceleration           | 3.12g  |
| Test duration per axis | 0.00138888888889 h                             |
| Test directions        | X-, Y- and Z-axis                              |
| Result                 | Test passed                                    |

### Shocks

|               |                                     |
|---------------|-------------------------------------|
| Specification | DIN EN 50155 (VDE 0115-200):2018-05 |
|---------------|-------------------------------------|

# PTFIX 6X1,5-NS15A VT - Distribution block



3002973

<https://www.phoenixcontact.com/us/products/3002973>

|                                |                                   |
|--------------------------------|-----------------------------------|
| Pulse shape                    | Half-sine                         |
| Acceleration                   | 30g                               |
| Shock duration                 | 18 ms                             |
| Number of shocks per direction | 3                                 |
| Test directions                | X-, Y- and Z-axis (pos. and neg.) |
| Result                         | Test passed                       |

## Ambient conditions

|  |  |
|--|--|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)  |
| Ambient temperature (assembly)           | -5 °C ... 70 °C  |
| Ambient temperature (actuation)          | -5 °C ... 70 °C  |
| Permissible humidity (operation)         | 20 % ... 90 %  |
| Permissible humidity (storage/transport) | 30 % ... 70 %  |

## Standards and regulations

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

## Mounting

|               |       |
|---------------|-------|
| Mounting type | NS 15 |
|---------------|-------|

# PTFIX 6X1,5-NS15A VT - Distribution block

3002973

<https://www.phoenixcontact.com/us/products/3002973>



## Drawings

Circuit diagram



# PTFIX 6X1,5-NS15A VT - Distribution block



3002973

<https://www.phoenixcontact.com/us/products/3002973>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3002973>

| <b>DNV</b><br>Approval ID: TAE00002TT-05 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| keine                                    |                       |                       |                   |                      |
|  | 500 V                 | 24 A                  | -                 | -                    |

| <b>CSA</b><br>Approval ID: 13631 |                       |                       |                   |                      |
|----------------------------------|-----------------------|-----------------------|-------------------|----------------------|
|                                  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| B                                |                       |                       |                   |                      |
|                                  | 300 V                 | 20 A                  | 26 - 12           | -                    |
| C                                |                       |                       |                   |                      |
|                                  | 150 V                 | 20 A                  | 26 - 12           | -                    |
| D                                |                       |                       |                   |                      |
|                                  | 300 V                 | 10 A                  | 26 - 12           | -                    |

| <b>IECEE CB Scheme</b><br>Approval ID: DE1-62701 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| keine  |                       |                       |                   |                      |
|  | 500 V                 | 17.5 A                | -                 | - 1.5                |

| <b>EAC</b><br>Approval ID: RU C-DE.BL08.B.00644 |  |  |  |  |
|---|--|--|--|--|
|---|--|--|--|--|

| <b>VDE Zeichengenehmigung</b><br>Approval ID: 40047797 |  |  |  |  |
|--|--|--|--|--|
|--|--|--|--|--|

| <b>cULus Recognized</b><br>Approval ID: E60425 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| B  |                       |                       |                   |                      |
|  | 300 V                 | 20 A                  | 26 - 12           | -                    |
| C  |                       |                       |                   |                      |
|  | 150 V                 | 20 A                  | 26 - 12           | -                    |
| F  |                       |                       |                   |                      |
|  | 500 V                 | 20 A                  | 26 - 12           | -                    |

# PTFIX 6X1,5-NS15A VT - Distribution block



3002973

<https://www.phoenixcontact.com/us/products/3002973>

|   |       |      |         |   |
|---|-------|------|---------|---|
| D |       |      |         |   |
|   | 300 V | 10 A | 26 - 12 | - |



**EAC**

Approval ID: KZ7500651131219505

# PTFIX 6X1,5-NS15A VT - Distribution block



3002973

<https://www.phoenixcontact.com/us/products/3002973>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250118 |
| ECLASS-15.0 | 27250118 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000897 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PTFIX 6X1,5-NS15A VT - Distribution block



3002973

<https://www.phoenixcontact.com/us/products/3002973>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)