

# UMK- 2 REL/KSR-G24/SO350 - Relay module



2976941

<https://www.phoenixcontact.com/us/products/2976941>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Customer-specific relay module, with plug-in bases for two miniature switching relays

## Commercial data

Item number	2976941
Packing unit	1 pc
Minimum order quantity	20 pc
Note	Made to order (non-returnable)
Product key	DK61Y1
GTIN	4017918281281
Weight per piece (including packing)	143.833 g
Weight per piece (excluding packing)	125.77 g
Country of origin	DE

# UMK- 2 REL/KSR-G24/SO350 - Relay module



2976941

<https://www.phoenixcontact.com/us/products/2976941>

## Technical data

### Product properties

Product type	Relay Module
Mechanical service life	5x 10 <sup>7</sup> cycles

### Insulation characteristics: Air clearances and creepage distances

Insulation	Functional insulation
Overvoltage category	II
Pollution degree	2

### Electrical properties

#### Air clearances and creepage distances

Rated insulation voltage	63 V
Rated surge voltage	0.6 kV (1.2/50 µs)

### Input data

Nominal input voltage U <sub>N</sub>	24 V DC
Input voltage range in reference to U <sub>N</sub>	0.8 ... 1.1
Input voltage range	19.2 V DC ... 26.4 V DC
Typical input current at U <sub>N</sub>	22 mA (per relay)
Typical response time	8 ms
Typical release time	10 ms
Protective circuit	Free running; Freewheeling diode

### Output data

#### Switching

Contact switching type	Single contact, 1 changeover contact (K1), 2 changeover contacts (K2)
Contact material	AgCdO
Maximum switching voltage	31 V DC (Limited by the built-in varistor)
Limiting continuous current	3 A
Interrupting rating (ohmic load) max.	72 W (24 V DC)

### Connection data

#### Input

Connection method	Screw connection
Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	26 ... 14

#### Output

Connection method	Screw connection
-------------------	------------------

# UMK- 2 REL/KSR-G24/SO350 - Relay module



2976941

<https://www.phoenixcontact.com/us/products/2976941>

Conductor cross-section rigid	0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section flexible	0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross-section AWG	26 ... 14

## Dimensions

Width	56.5 mm
Height	77 mm
Depth	61 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-20 °C ... 50 °C
Altitude	≤ 2000 m

## Standards and regulations

### Air clearances and creepage distances

Standards/regulations	DIN EN 50178: 1998-04
-----------------------	-----------------------

## Mounting

Mounting type	DIN rail mounting
Mounting position	any

# UMK- 2 REL/KSR-G24/SO350 - Relay module



2976941

<https://www.phoenixcontact.com/us/products/2976941>

## Classifications

### ECLASS

ECLASS-13.0	27371601
ECLASS-15.0	27371601

### ETIM

ETIM 10.0	EC001437
-----------	----------

### UNSPSC

UNSPSC 21.0	39122300
-------------	----------

# UMK- 2 REL/KSR-G24/SO350 - Relay module



2976941

<https://www.phoenixcontact.com/us/products/2976941>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	050d4f39-8a80-4671-8f6c-f591d37fc8f7

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)