

UK 35-1-PE/N - Installation protective conductor terminal block

3008067

<https://www.phoenixcontact.com/us/products/3008067>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Installation protective conductor terminal block, The NS 32... or NS 35... Cu DIN rail should be used for a connection cross section of 35 mm²/2 AWG. When aligned with a feed-through terminal block of the same shape, a cover must be used at insulation voltages > 630 V., PE/N block, consisting of a green-yellow protective conductor terminal block and a blue terminal block with screw bridge, nom. voltage: 630 V, nominal current: 125 A, Screw connection, cross section: 0.75 mm² - 35 mm², mounting type: NS 35/15-2,3, color: green-yellow-blue

The figure shows version UK
35 PE/N

Commercial data

Item number	3008067
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE12
Product key	BE1221
GTIN	4017918091583
Weight per piece (including packing)	163.22 g
Weight per piece (excluding packing)	155.973 g
Customs tariff number	85369010
Country of origin	DE

UK 35-1-PE/N - Installation protective conductor terminal block



3008067

<https://www.phoenixcontact.com/us/products/3008067>

Technical data

Product properties

Product type	Ground terminal block
Number of connections	4
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
---------------------	------

Connection data

PEN function	yes
Grounding foot	Yes
Number of connections per level	2

Level 1 above 1 below 1

Connection method	Screw connection
Screw thread	M6
Note	Please observe the current carrying capacity of the DIN rails.
Tightening torque	3.2 ... 3.7 Nm
Stripping length	16 mm
Connection in acc. with standard	IEC 60947-7-1/IEC 60947-7-2
Conductor cross-section rigid	0.75 mm ² ... 35 mm ²
Cross section AWG	18 ... 2 (converted acc. to IEC)
Conductor cross-section flexible	0.75 mm ² ... 35 mm ²
Conductor cross-section, flexible [AWG]	18 ... 2 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.75 mm ² ... 35 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.75 mm ² ... 35 mm ²
Nominal current	125 A
Maximum load current	125 A (with 35 mm ² conductor cross-section)
Nominal voltage	630 V (When aligned with a modular terminal block of the same shape, a separating disk must be used at voltages > 630 V.)
Nominal current	125 A
Maximum load current	125 A (with 35 mm ² conductor cross-section)
Nominal voltage	630 V (When aligned with a modular terminal block of the same shape, a separating disk must be used at voltages > 630 V.)

Dimensions

Width	30.1 mm
-------	---------

UK 35-1-PE/N - Installation protective conductor terminal block



3008067

<https://www.phoenixcontact.com/us/products/3008067>

Material specifications

Color	green-yellow-blue
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	125 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	27,5 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Electrical tests

Surge voltage test

Test voltage setpoint	9.8 kV
Result	Test passed

Temperature-rise test

Requirement temperature-rise test	Increase in temperature \leq 45 K
Result	Test passed
Short-time withstand current 35 mm ²	4.2 kA
Result	Test passed

Power-frequency withstand voltage

Test voltage setpoint	1.89 kV
Result	Test passed

Mechanical properties

General

Terminal block mounting	2.5 Nm ... 3 Nm (PE foot with mounting screw, M5)
-------------------------	---

Mechanical data

Open side panel	No
-----------------	----

Mechanical tests

Mechanical strength

Result	Test passed
--------	-------------

UK 35-1-PE/N - Installation protective conductor terminal block



3008067

<https://www.phoenixcontact.com/us/products/3008067>

Attachment on the carrier

DIN rail/fixing support	NS 35
Test force setpoint	10 N
Result	Test passed

Test for conductor damage and slackening

Rotation speed	10 rpm
Revolutions	135
Conductor cross-section/weight	0.75 mm ² / 0.4 kg 35 mm ² / 6.8 kg
Result	Test passed

Environmental and real-life conditions

Needle-flame test

Time of exposure	30 s
Result	Test passed

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1/IEC 60947-7-2
----------------------------------	-----------------------------

Mounting

Mounting type	NS 35/15-2,3
Terminal block mounting	2.5 Nm ... 3 Nm (PE foot with mounting screw, M5)


UK 35-1-PE/N - Installation protective conductor terminal block

3008067

<https://www.phoenixcontact.com/us/products/3008067>

Drawings

Circuit diagram



1 = separating plate

UK 35-1-PE/N - Installation protective conductor terminal block



3008067

<https://www.phoenixcontact.com/us/products/3008067>

Classifications

UNSPSC

UNSPSC 21.0	39121410
-------------	----------

UK 35-1-PE/N - Installation protective conductor terminal block



3008067

<https://www.phoenixcontact.com/us/products/3008067>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	4-Nonylphenol, branched and linear(CAS: n/a)
-------------------------------------	--

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com