

UKH 50 BU - High-current terminal block



3009105

<https://www.phoenixcontact.com/us/products/3009105>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



High-current terminal block, nom. voltage: 1000 V, nominal current: 150 A, number of connections: 2, number of positions: 1, connection method: Screw connection, Rated cross section: 50 mm², cross section: 16 mm² - 70 mm², mounting type: NS 35/7,5, NS 35/15, NS 32, NS 35/15-2,3, color: blue

Your advantages

- Reliable cable connection is ensured by three-point centering of the conductor in the prismatic sleeve base
- Low contact resistance of the contact surface due to ribbing
- Screw locking by means of spring-loaded elements in the clamping part

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3009105 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE13 |
| Product key | BE1311 |
| GTIN | 4017918091637 |
| Weight per piece (including packing) | 120.32 g |
| Weight per piece (excluding packing) | 115.1 g |
| Customs tariff number | 85369010 |
| Country of origin | IN |

UKH 50 BU - High-current terminal block



3009105

<https://www.phoenixcontact.com/us/products/3009105>

Technical data

Notes

General

| | |
|------|---|
| Note | For a reliable contact of multi stranded conductors it is recommended to untwist multi stranded conductors. |
|------|---|

Product properties

| | |
|-----------------------|-----------------------------|
| Product type | High current terminal block |
| Number of positions | 1 |
| Number of connections | 2 |
| Number of rows | 1 |
| Potentials | 1 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---|--------|
| Rated surge voltage | 8 kV |
| Maximum power dissipation for nominal condition | 4.73 W |

Connection data

| | |
|---|---|
| Number of connections per level | 2 |
| Nominal cross section | 50 mm ² |
| Rated cross section AWG | 1/0 |
| Connection method | Screw connection |
| Screw thread | M6 |
| Tightening torque | 6 ... 8 Nm |
| Stripping length | 24 mm |
| Internal cylindrical gage | B10 |
| Connection in acc. with standard | IEC 60947-7-1 |
| Conductor cross-section rigid | 16 mm ² ... 70 mm ² |
| Cross section AWG | 4 ... 2/0 (converted acc. to IEC) |
| Conductor cross-section flexible | 25 mm ² ... 70 mm ² |
| Conductor cross-section, flexible [AWG] | 2 ... 2/0 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 16 mm ² ... 50 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 16 mm ² ... 50 mm ² |
| 2 conductors with same cross section, rigid | 10 mm ² ... 16 mm ² |
| 2 conductors with same cross section, flexible | 10 mm ² ... 16 mm ² |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve | 10 mm ² ... 16 mm ² |
| Nominal cross section | 50 mm ² |
| Nominal current | 150 A |

UKH 50 BU - High-current terminal block



3009105

<https://www.phoenixcontact.com/us/products/3009105>

| | |
|----------------------|--|
| Maximum load current | 150 A (with 50 mm ² conductor cross-section) |
| Nominal voltage | 1000 V |
| Note | Note: Product releases, connection cross sections and notes on connecting aluminum cables can be found in the download area. |

Ex data

Rated data (ATEX/IECEX)

| | |
|--|--|
| Identification | ⊕ II 2 GD Ex eb IIC Gb |
| Operating temperature range | -60 °C ... 110 °C |
| Ex-certified accessories | 1205082 SZS 1,2X8,0 VDE 1201659 E/AL-NS 32 1201662 E/AL-NS 35 |
| List of bridges | Fixed bridge / FBI 2-20-EX / 0201113 Fixed bridge / FBI 3-20-EX / 0201812 |
| Bridge data | 130.5 A (50 mm ²) |
| Ex temperature increase for bridging with bridge | 40 K (133 A / 50 mm ²) |
| Rated insulation voltage output | 690 V (Permanent) |

Ex level General

| | |
|----------------------|--------|
| Rated voltage | 690 V |
| Rated current | 133 A |
| Maximum load current | 133 A |
| Contact resistance | 0.1 mΩ |

Ex connection data General

| | |
|---|---|
| Torque range | 6 Nm ... 8 Nm |
| Nominal cross section | 50 mm ² |
| Rated cross section AWG | 1/0 |
| Connection capacity rigid | 16 mm ² ... 50 mm ² |
| Connection capacity AWG | 6 ... 1/0 |
| Connection capacity flexible | 25 mm ² ... 50 mm ² |
| Connection capacity AWG | 4 ... 1/0 |
| 2 conductors with same cross section, solid | 10 mm ² ... 16 mm ² |
| 2 conductors with the same cross-section AWG rigid | 8 ... 6 |
| 2 conductors with same cross section, stranded | 10 mm ² ... 16 mm ² |
| 2 conductors with the same cross-section AWG flexible | 8 ... 6 |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing | |
|---------------------|--|

UKH 50 BU - High-current terminal block



3009105

<https://www.phoenixcontact.com/us/products/3009105>

| | |
|-------------------|---------|
| Width | 20 mm |
| Height | 70.5 mm |
| Depth | 75.8 mm |
| Depth on NS 32 | 81 mm |
| Depth on NS 35/15 | 83.5 mm |

Material specifications

| | |
|--|-----------------|
| Color | blue (RAL 5015) |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Electrical tests

Surge voltage test

| | |
|-----------------------|-------------|
| Test voltage setpoint | 9.8 kV |
| Result | Test passed |

Temperature-rise test

| | |
|---|-------------------------------------|
| Requirement temperature-rise test | Increase in temperature ≤ 45 K |
| Result | Test passed |
| Short-time withstand current 50 mm ² | 6 kA |
| Result | Test passed |

Power-frequency withstand voltage

| | |
|-----------------------|-------------|
| Test voltage setpoint | 2.2 kV |
| Result | Test passed |

Mechanical properties

Mechanical data

| | |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

Mechanical tests

Mechanical strength

| | |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

Attachment on the carrier

| | |
|-------------------------|-------------|
| DIN rail/fixing support | NS 32/NS 35 |
| Test force setpoint | 10 N |
| Result | Test passed |

Test for conductor damage and slackening

| | |
|--------------------------------|-----------------------------|
| Rotation speed | 10 (+/- 2) rpm |
| Revolutions | 135 |
| Conductor cross-section/weight | 16 mm ² / 2.9 kg |
| | 50 mm ² / 9.5 kg |
| | 70 mm ² /10.4 kg |
| Result | Test passed |

Environmental and real-life conditions

Needle-flame test

| | |
|------------------|-------------|
| Time of exposure | 30 s |
| Result | Test passed |

Oscillation/broadband noise

| | |
|------------------------|--|
| Specification | DIN EN 50155 (VDE 0115-200):2018-05 |
| Spectrum | Long life test category 2, bogie-mounted |
| Frequency | $f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$ |
| ASD level | 6.12 (m/s ²) ² /Hz |
| Acceleration | 3.12g |
| Test duration per axis | 5 h |
| Test directions | X-, Y- and Z-axis |
| Result | Test passed |

Shocks

| | |
|--------------------------------|-------------------------------------|
| Specification | DIN EN 50155 (VDE 0115-200):2022-06 |
| Pulse shape | Half-sine |
| Acceleration | 5g |
| Shock duration | 30 ms |
| Number of shocks per direction | 3 |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |
| Result | Test passed |

Ambient conditions

| | |
|---|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |

UKH 50 BU - High-current terminal block



3009105

<https://www.phoenixcontact.com/us/products/3009105>

| | |
|--|---------------|
| Permissible humidity (storage/transport) | 30 % ... 70 % |
|--|---------------|

Standards and regulations

| | |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-1 |
|----------------------------------|---------------|

Mounting

| | |
|---------------|--------------|
| Mounting type | NS 35/7,5 |
| | NS 35/15 |
| | NS 32 |
| | NS 35/15-2,3 |


UKH 50 BU - High-current terminal block

3009105

<https://www.phoenixcontact.com/us/products/3009105>

Drawings

Dimensional drawing



Schematic diagram



Connecting aluminum cables. Further notes can be found in the download area

UKH 50 BU - High-current terminal block

3009105

<https://www.phoenixcontact.com/us/products/3009105>



Circuit diagram



UKH 50 BU - High-current terminal block





3009105


<https://www.phoenixcontact.com/us/products/3009105>


Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3009105>

|  CSA Approval ID: 13631 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| B | 600 V | 150 A | 6 - 1/0 | - |
| C | 600 V | 150 A | 6 - 1/0 | - |

|  cULus Recognized Approval ID: E60425 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| B | 600 V | 150 A | 6 - 1/0 | - |
| Multi-conductor connection | 600 V | 150 A | 8 - 6 | - |
| C | 600 V | 150 A | 6 - 1/0 | - |
| Multi-conductor connection | 600 V | 150 A | 8 - 6 | - |

|  LR Approval ID: LR2420186TA | |
|---|--|
|---|--|

|  VDE Zeichengenehmigung Approval ID: 40036368 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | 1000 V | 150 A | - | - 50 |

|  IECEE CB Scheme Approval ID: DE1-62936_M1 | | | | |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | 1000 V | 150 A | - | - 50 |

| DNV Approval ID: TAE00001CT | |
|---------------------------------------|--|
|---------------------------------------|--|

UKH 50 BU - High-current terminal block



3009105

<https://www.phoenixcontact.com/us/products/3009105>



ATEX

Approval ID: KEMA98ATEX1786U



EAC Ex

Approval ID: KZ 7500525010101950



IECEX

Approval ID: IECEX KEM 06.0029U



CCC

Approval ID: 2020322313000623



UKCA-EX

Approval ID: DEKRA 21UKEX0307U

UL Comp Hazloc CA US

Approval ID: UL US CA L 192998

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine | | | | |
| | 600 V | 150 A | 6 - 1/0 | - |

UKH 50 BU - High-current terminal block



3009105

<https://www.phoenixcontact.com/us/products/3009105>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250101 |
| ECLASS-15.0 | 27250101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000897 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

UKH 50 BU - High-current terminal block



3009105

<https://www.phoenixcontact.com/us/products/3009105>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 0.78 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com