

FBS-PV PT 2,5-4L - Potential bridge

3012318

<https://www.phoenixcontact.com/us/products/3012318>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Vertical bridge between two levels



Commercial data

Item number	3012318
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE29
Product key	BE2Z2X
GTIN	4046356645942
Weight per piece (including packing)	0.468 g
Weight per piece (excluding packing)	0.419 g
Customs tariff number	85366990
Country of origin	PL

FBS-PV PT 2,5-4L - Potential bridge



3012318

<https://www.phoenixcontact.com/us/products/3012318>

Technical data

Notes

Note on application	Item is an accessory for: PT 2,5-4L/1P (3012300) PT 2,5-4L/2P (3012310) PT 2,5-PE/3L/2P (3012316) ST 2,5-4L/2P-Z (3041998)
---------------------	--

Product properties

Product type	Vertical bridge
Number of positions	1

Electrical properties

Maximum load current	10 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)
----------------------	---

Connection data

Maximum load current	10 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)
----------------------	---

Dimensions

Width	5 mm
Height	3 mm
Depth	30.6 mm
Length	3 mm

Material specifications

Color	black (RAL 9005)
Material	Copper
Flammability rating according to UL 94	V0
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

FBS-PV PT 2,5-4L - Potential bridge



3012318

<https://www.phoenixcontact.com/us/products/3012318>

Mounting

Mounting type

Plug-in mounting

FBS-PV PT 2,5-4L - Potential bridge



3012318

<https://www.phoenixcontact.com/us/products/3012318>

Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 10.0	EC000489
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FBS-PV PT 2,5-4L - Potential bridge



3012318

<https://www.phoenixcontact.com/us/products/3012318>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.018 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com