

FBS-PV PT 2,5-4L - Potential bridge

3012318

<https://www.phoenixcontact.com/us/products/3012318>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Vertical bridge between two levels



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3012318 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BE29 |
| Product key | BE2Z2X |
| GTIN | 4046356645942 |
| Weight per piece (including packing) | 0.468 g |
| Weight per piece (excluding packing) | 0.419 g |
| Customs tariff number | 85366990 |
| Country of origin | PL |

FBS-PV PT 2,5-4L - Potential bridge



3012318

<https://www.phoenixcontact.com/us/products/3012318>

Technical data

Notes

| | |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------------|
| Note on application | Item is an accessory for: PT 2,5-4L/1P (3012300) PT 2,5-4L/2P (3012310) PT 2,5-PE/3L/2P (3012316) ST 2,5-4L/2P-Z (3041998) |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------------|

Product properties

| | |
|---------------------|-----------------|
| Product type | Vertical bridge |
| Number of positions | 1 |

Electrical properties

| | |
|----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Maximum load current | 10 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.) |
|----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

Connection data

| | |
|----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Maximum load current | 10 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.) |
|----------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

Dimensions

| | |
|--------|---------|
| Width | 5 mm |
| Height | 3 mm |
| Depth | 30.6 mm |
| Length | 3 mm |

Material specifications

| | |
|----------------------------------------|------------------|
| Color | black (RAL 9005) |
| Material | Copper |
| Flammability rating according to UL 94 | V0 |
| Insulating material | PA |

Environmental and real-life conditions

Ambient conditions

| | |
|------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

FBS-PV PT 2,5-4L - Potential bridge



3012318

<https://www.phoenixcontact.com/us/products/3012318>

Mounting

Mounting type

Plug-in mounting

FBS-PV PT 2,5-4L - Potential bridge



3012318

<https://www.phoenixcontact.com/us/products/3012318>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250303 |
| ECLASS-15.0 | 27250303 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000489 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

FBS-PV PT 2,5-4L - Potential bridge



3012318

<https://www.phoenixcontact.com/us/products/3012318>

Environmental product compliance

EU RoHS

| | |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

China RoHS

| | |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.018 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com